



[illegible]

		3.600	3.500	35	72	3	102393	4
SUPERSEDED		3.500	3.400	34	70	3—		—3
		3.400	3.300	33	68	3—		—2
		3.300	3.200	32	66	3—		—1
		3.200	3.100	31	64	3—		—0
SUPERSEDED		3.100	3.000	30	62	2—		—9
		3.000	2.900	29	60	2—		—8
SUPERSEDED		2.900	2.800	28	58	2—		—7
SUPERSEDED		2.800	2.700	27	56	2—		—6
 9 OBSOLETE		2.700	2.600	26	54	2—		—5
SUPERSEDED		2.600	2.500	25	52	2—		—4
		2.500	2.400	24	50	2—		—3
SUPERSEDED		2.400	2.300	23	48	2—		—2
		2.300	2.200	22	46	2—		—1
		2.200	2.100	21	44	2—		—0
		2.100	2.000	20	42	1—		—9
		2.000	1.900	19	40	1—		—8
SUPERSEDED		1.900	1.800	18	38	1—		—7
SUPERSEDED		1.800	1.700	17	36	1—		—6
		1.700	1.600	16	34	1—		—5
 9 OBSOLETE		1.600	1.500	15	32	1—		—4
		1.500	1.400	14	30	1—		—3
 9 OBSOLETE		1.400	1.300	13	28	1—		—2
		1.300	1.200	12	26	1—		—1
 9 SUPERSEDED		1.200	1.100	11	24	1—		—0
 9 OBSOLETE		1.100	1.000	10	22			—9
		1.000	.900	9	20			—8
		.900	.800	8	18			—7
		.800	.700	7	16			—6
		.700	.600	6	14			—5
		.600	.500	5	12			—4
		.500	.400	4	10			—3
 9 SUPERSEDED		.400	.300	3	8			—2
		.300	.200	2	6		102393	—1
		C	B	A	NO OF POSN		ASSEMBLY PART NUMBER	

- | | | |
|---|--|---|
|  | .000030 GOLD IN THE CONTACT AREA, .000050—.000100 TIN—LEAD IN THE TERMINATION AREA, ALL OVER .000050 NICKEL. |  |
|  | TOLERANCE NON—CUMULATIVE. | |
|  | .000030 GOLD IN THE CONTACT AREA, .000050—.000100 TIN IN THE TERMINATION AREA, ALL OVER .000050 NICKEL. | |
|  | MOLDED CIRCUIT #1 IDENTIFIER IN LOCATION SHOWN. | |
|  | OBSOLETE PART NUMBER | |
| 6 | USE WITH 26—30 AWG WIRE SIZE, .050 MAX INSULATION DIA., .015 MAX INSULATION WALL THICKNESS. | |
|  | CONTACT IDENTIFICATION NUMBER "1" LOCATED IN THIS AREA. | |
|  | AMP TRADEMARK (EITHER SIDE). | |
|  | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI | |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	7-1-85
L.D.RINGLEY	
CHK	7-1-85
P.C.deJONG	
APVD	7-1-85
P.C.deJONG	
PRODUCT SPEC	

 **Tyco Electronics** Tyco Electronics Corporation
Harrisburg, PA 17105-3608

ASSEMBLY, MASS TERMINATION, AMPMODU,
DOUBLE ROW, .100 X .100 CL,
#26-#30 AWG WIRE SIZE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-102393	—

WEIGHT	—
--------	---

CUSTOMER DRAWING	SCALE 4:1	SHEET 1 OF 1	REV S1
------------------	-----------	--------------	--------