



IP67 RATED WATERPROOF DIE-CAST ENCLOSURE


The DCE series die cast aluminum enclosures from Laird are designed for extremely long life in outdoor environments. The powder coat paint over aluminum construction offers unsurpassed resistance to corrosion. The pole mount hardware includes heavy galvanized pole clamps and stainless steel U bolts and attachment nuts. The die cast enclosure has extra heavy duty mounting flanges for reliable mounting to poles or surface mounting to walls. The most unique feature is the inclusion of 7 engineered hole knockouts which allow for many different configurations of connectors and feedthru's without the need for drilling holes. The knockouts are easily removed using a flat blade screwdriver and hammer. The enclosures have Qty 4 threaded ¼" tall standoffs in the base for mounting a user plate (included), which in turn can hold the users electronics. This configuration provides universal mounting which is fully customizable by the user.

FEATURES

- Die cast aluminum with white epoxy powder coat paint
- Qty 7 engineered hole knockouts for many possible configurations. No drilling required!
- Qty 4 0.25" tall threaded standoffs and mounting plate for mounting of electronics inside enclosure
- Pole mount or wall mount
- IP67 rated for long term weatherproofing
- Fits common WiFi radio boards


MARKETS

- Wireless base stations
- Wireless client radios
- Direct burial equipment
- Repeater systems
- 802.11 a/b/g wireless systems
- Fiber-optic junction box




ANTENNA PATTERNS


2300-2700 MHz




2400-2500 MHz



3300-3800 MHz




5150-5850 MHz




VSWR GRAPHS


2300-2700 MHz




2400-2500 MHz



3300-3800 MHz



5150-5850 MHz



SPECIFICATIONS	2300-2700	2400-2500	3300-3800	4940-5850	2400-2485/ 5150-5850
Gain (integrated antenna)	14 dBi	12 dBi	16 dBi	18 dBi	12 / 15 dBi
VSWR (integrated antenna)	1.8:1	1.5:1	1.7:1	1.7:1	1.5:1
Impedance	50 OHM				
Input Power	100 W				
Wind Survivability	150 mph				
Weight (die-cast enclosure)	40 oz (1.13kg)				
Dimensions (inside)	7.125" x 6.125" x 2" (181 x 156 x 51mm) 10"				
Dimensions (outside)	x 7.1" x 2.25" (254 x 180 x 57 mm)				
Radome	ASA				
Operational Temperature	-30°C to +75°C				
Mount Style	Wall / Mast / Tilt				

COMPLETE UNITS

DCE-7x6x2	Die Cast Enclosure (No Antenna)
DCE-H-7x6x2	Die Cast Enclosure w/ Hinged Die Cast Door (No Antenna)
DCE-ANT2314-xxxx	Die Cast Enclosure w/ 2300-2700MHz, 14dBi Antenna Integrated Into
DCE-ANT2412-xxxx	Hinged Door Die Cast Enclosure w/ 2400-2500MHz, 12dBi Antenna
DCE-ANT3516-xxxx	Integrated Into Hinged Door Die Cast Enclosure w/ 3300-3800MHz, 16dBi
DCE-ANT5819-xxxx	Antenna Integrated Into Hinged Door Die Cast Enclosure w/
DCE-ANT2451-xxxx	4940-5850MHz, 19dBi Antenna Integrated Into Hinged Door Die Cast
	Enclosure w/ Dual-Band 2400-2485MHz/5150-5850MHz,
	12dBi/16dBi Antenna Integrated Into Hinged Door

(xxxx = connector type - MC, MMCX, RMMCX, RSMA, RTNC, SSMB, and UFL)

ACCESSORIES FOR DCE-7x6x2

DCE-HC-ASSY	Hinged Die Cast Door for DCE-7x6x2
DCE-ANT2314-ASSY	Hinged ASA Door w/2300-2700MHz, 14dBi
DCE-ANT2412-ASSY	Antenna Hinged ASA Door w/2400-2500MHz,
DCE-ANT3516-ASSY	12dBi Antenna Hinged ASA Door
DCE-ANT5819-ASSY	w/3300-3800MHz, 16dBi Antenna Hinged ASA
DCE-ANT2451-ASSY	Door w/4940-5850MHz, 19dBi Antenna
	Hinged ASA Door w/Dual-Band 2400-2485MHz/5150-5850MHz, 12dBi/16dBi Antenna

NOTES

- All shipments F.O.B. Schaumburg, IL 60173