




REVISIONS				DATE	APPD
LOC	DIST	P	ZONE	LTR	DESCRIPTION
G	14		B	REV, RDRW, & SM PKG PER 0720-0040-93	3-29-93



AMP WIRE RANGE		E13288 Listed	
22-16 AWG	SOLID OR STRANDED	22-16 AWG	SOLID OR STRANDED
22-16 AWG	SOLID OR STRANDED	22-16 AWG	SOLID OR STRANDED
22-16 AWG	SOLID OR STRANDED	22-16 AWG	SOLID OR STRANDED

STAMP 85 AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPECIFICATION
MIL-T-7928, COMMERCIAL WIRE RANGE IS 22-16
85 INDICATES STUD SIZE



QUANTITY	PACKAGING TYPE	PART NO
100	LOOSE PIECE, BOX	8-53831-1
5000	ON TAPE	53831-2
---	LOOSE PIECE	53831-1

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX		DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm (INCHES) TOLERANCES ON: 2 PLC DEC ± 3 PLC DEC ± ANGLES		DR 3-29-93 TA BRINKMAN CHK 3-29-93 DA PATTERSON APPD 3-29-93 DE MILLER APPD 3-29-93 JL MECKLEY PRODUCT SPEC		NAME AMP Incorporated Harrisburg, PA 17105-3608	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: NOT APPLICABLE		WIRE CROSS SECTIONAL AREA RANGE: 0.26-1.65mm² (509-3,260 CIR MILS SOLID OR STRANDED)		FINISH TIN PLATE 0.00254 [0.00100] MIN THK PER MIL-T-10727	
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		APPLICATION SPEC		SIZE 00779 CAGE CODE 00779 DRAWING NO C=53831	
FOR ORDER ENTRY		1-800-526-5142		WEIGHT		SCALE 10:1		SHEET 1 OF 1	