

74VHC125

Quad Buffer with 3-STATE Outputs

General Description

The VHC125 contains four independent non-inverting buffers with 3-STATE outputs. It is an advanced high-speed CMOS device fabricated with silicon gate CMOS technology and achieves the high-speed operation similar to equivalent Bipolar Schottky TTL while maintaining the CMOS low power dissipation.

An input protection circuit insures that 0V to 7V can be applied to the input pins without regard to the supply voltage. This device can be used to interface 5V to 3V systems and two supply systems such as battery backup. This circuit prevents device destruction due to mismatched supply and input voltages.

cuit prevents device destruction due to mismatched supply and input voltages.

Features


- High Speed: $t_{PD} = 3.8$ ns (typ) at $V_{CC} = 5V$
- Lower power dissipation: $I_{CC} = 4$ μA (max) at $T_A = 25^\circ C$
- High noise immunity: $V_{NIH} = V_{NIL} = 28\% V_{CC}$ (min)
- Power down protection is provided on all inputs
- Low noise: $V_{OLP} = 0.8V$ (max)

Ordering Code:


| Order Number | Package Number | Package Description |
|--------------|----------------|---|
| 74VHC125M | M14A | 14-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-120, 0.150 Narrow |
| 74VHC125SJ | M14D | 14-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide |
| 74VHC125MTC | MTC14 | 14-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide |
| 74VHC125N | N14A | 14-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300 Wide |

Surface mount packages are also available on Tape and Reel. Specify by appending the suffix letter "X" to the ordering code.

Logic Symbol



Connection Diagram



Pin Descriptions

| Pin Names | Description |
|------------------|-------------|
| \bar{A}_n, B_n | Inputs |
| O_n | Outputs |

Function Table

| Inputs | | Output |
|-------------|-------|--------|
| \bar{A}_n | B_n | O_n |
| L | L | L |
| L | H | H |
| H | X | Z |

H = HIGH Voltage Level
L = LOW Voltage Level
Z = HIGH Impedance
X = Immaterial

Absolute Maximum Ratings (Note 1)

| | |
|---|--------------------------|
| Supply Voltage (V_{CC}) | -0.5V to +7.0V |
| DC Input Voltage (V_{IN}) | -0.5V to +7.0V |
| DC Output Voltage (V_{OUT}) | -0.5V to $V_{CC} + 0.5V$ |
| Input Diode Current (I_{IK}) | -20 mA |
| Output Diode Current (I_{OK}) | ± 20 mA |
| DC Output Current (I_{OUT}) | ± 25 mA |
| DC V_{CC} /GND Current (I_{CC}) | ± 50 mA |
| Storage Temperature (T_{STG}) | -65°C to +150°C |
| Lead Temperature (T_L) (Soldering, 10 seconds) | 260°C |

Recommended Operating Conditions (Note 2)

| | |
|---|----------------|
| Supply Voltage (V_{CC}) | 2.0V to +5.5V |
| Input Voltage (V_{IN}) | 0V to +5.5V |
| Output Voltage (V_{OUT}) | 0V to V_{CC} |
| Operating Temperature (T_{OPR}) | -40°C to +85°C |
| Input Rise and Fall Time (t_r, t_f) | |
| $V_{CC} = 3.3V \pm 0.3V$ | 0 ~ 100 ns/V |
| $V_{CC} = 5.0V \pm 0.5V$ | 0 ~ 20 ns/V |

Note 1: Absolute Maximum Ratings are values beyond which the device may be damaged or have its useful life impaired. The databook specifications should be met, without exception, to ensure that the system design is reliable over its power supply, temperature, and output/input loading variables. Fairchild does not recommend operation outside databook specifications.

Note 2: Unused inputs must be held HIGH or LOW. They may not float.

DC Electrical Characteristics

| Symbol | Parameter | V _{CC} (V) | T _A = 25°C | | | T _A = −40°C to +85°C | | Units | Conditions | |
|-----------------|----------------------------------|------------------------|-----------------------------|-----|-----------------------------|---------------------------------|-----------------------------|-------|---|--|
| | | | Min | Typ | Max | Min | Max | | | |
| V _{IH} | HIGH Level Input Voltage | 2.0 3.0 – 5.5 | 1.50 0.7 V _{CC} | | | 1.50 0.7 V _{CC} | | V | | |
| V _{IL} | LOW Level Input Voltage | 2.0 3.0 – 5.5 | | | 0.50 0.3 V _{CC} | | 0.50 0.3 V _{CC} | V | | |
| V _{OH} | HIGH Level Output Voltage | 2.0 | 1.9 | 2.0 | | 1.9 | | V | V _{IN} = V _{IH} or V _{IL} | I _{OH} = −50 μA |
| | | 3.0 | 2.9 | 3.0 | | 2.9 | | | | |
| | | 4.5 | 4.4 | 4.5 | | 4.4 | | V | | I _{OH} = −4 mA I _{OH} = −8 mA |
| | | 3.0 | 2.58 3.94 | | | 2.48 3.80 | | | | |
| V _{OL} | LOW Level Output Voltage | 2.0 | | 0.0 | 0.1 | | 0.1 | V | V _{IN} = V _{IH} or V _{IL} | I _{OL} = 50 μA |
| | | 3.0 | | 0.0 | 0.1 | | 0.1 | | | |
| | | 4.5 | | 0.0 | 0.1 | | 0.1 | V | | I _{OL} = 4 mA I _{OL} = 8 mA |
| | | 3.0 | | | 0.36 0.36 | | 0.44 0.44 | | | |
| I _{OZ} | 3-STATE Output Off-State Current | 5.5 | | | ±0.25 | | ±2.5 | μA | V _{IN} = V _{IH} or V _{IL} V _{OUT} = V _{CC} or GND | |
| I _{IN} | Input Leakage Current | 0 – 5.5 | | | ±0.1 | | ±1.0 | μA | V _{IN} = 5.5V or GND | |
| I _{CC} | Quiescent Supply Current | 5.5 | | | 4.0 | | 40.0 | μA | V _{IN} = V _{CC} or GND | |

Noise Characteristics

| Symbol | Parameter | V_{CC} (V) | $T_A = 25^\circ\text{C}$ | | Units | Conditions |
|-----------------------|--|-----------------|--------------------------|--------|-------|-----------------------|
| | | | Typ | Limits | | |
| V_{OLP} (Note 3) | Quiet Output Maximum Dynamic V_{OL} | 5.0 | 0.5 | 0.8 | V | $C_L = 50 \text{ pF}$ |
| V_{OLV} (Note 3) | Quiet Output Minimum Dynamic V_{OL} | 5.0 | -0.5 | -0.8 | V | $C_L = 50 \text{ pF}$ |
| V_{IHD} (Note 3) | Minimum HIGH Level Dynamic Input Voltage | 5.0 | | 3.5 | V | $C_L = 50 \text{ pF}$ |
| V_{ILD} (Note 3) | Maximum HIGH Level Dynamic Input Voltage | 5.0 | | 1.5 | V | $C_L = 50 \text{ pF}$ |

Note 3: Parameter guaranteed by design.




AC Electrical Characteristics

| Symbol | Parameter | V _{CC} (V) | T _A = 25°C | | | T _A = −40°C to +85°C | | Units | Conditions | |
|-------------------|----------------------------------|------------------------|-----------------------|-----|------|---------------------------------|------|-------|------------------------|------------------------|
| | | | Min | Typ | Max | Min | Max | | | |
| t _{PLH} | Propagation Delay Time | 3.3 ± 0.3 | | 5.6 | 8.0 | 1.0 | 9.5 | ns | | C _L = 15 pF |
| t _{PHL} | | | | 8.1 | 11.5 | 1.0 | 13.0 | | | C _L = 50 pF |
| | | 5.0 ± 0.5 | | 3.8 | 5.5 | 1.0 | 6.5 | ns | | C _L = 15 pF |
| | | | | 5.3 | 7.5 | 1.0 | 8.5 | | | C _L = 50 pF |
| t _{PZL} | 3-STATE Output | 3.3 ± 0.3 | | 5.4 | 8.0 | 1.0 | 9.5 | ns | R _L = 1 kΩ | C _L = 15 pF |
| t _{PZH} | Enable Time | | | 7.9 | 11.5 | 1.0 | 13.0 | | | C _L = 50 pF |
| | | 5.0 ± 0.5 | | 3.6 | 5.1 | 1.0 | 6.0 | ns | | C _L = 15 pF |
| | | | | 5.1 | 7.1 | 1.0 | 8.0 | | | C _L = 50 pF |
| t _{PLZ} | 3-STATE Output | 3.3 ± 0.3 | | 9.5 | 13.2 | 1.0 | 15.0 | ns | R _L = 1 kΩ | C _L = 50 pF |
| t _{PHZ} | Disable Time | 5.0 ± 0.5 | | 6.1 | 8.8 | 1.0 | 10.0 | | | C _L = 50 pF |
| t _{OSLH} | Output to Output Skew | 3.3 ± 0.3 | | | 1.5 | | 1.5 | ns | (Note 4) | C _L = 50 pF |
| t _{OSHL} | | | 5.0 ± 0.5 | | | 1.0 | | | | 1.0 |
| C _{IN} | Input Capacitance | | | 4 | 10 | | 10 | pF | V _{CC} = Open | |
| C _{OUT} | Output Capacitance | | | 6 | | | | pF | V _{CC} = 5.0V | |
| C _{PD} | Power Dissipation Capacitance | | | 14 | | | | pF | (Note 5) | |

Note 4: Parameter guaranteed by design. $t_{OSLH} = |t_{PLHmax} - t_{PLHmin}|$; $t_{OSHL} = |t_{PHLmax} - t_{PHLmin}|$.




Note 5: C_{PD} is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load. Average operating current can be obtained by the equation: $I_{CC} (OPR.) = C_{PD} \cdot V_{CC} \cdot f_{IN} + I_{CC}/4$ (per bit).

Physical Dimensions inches (millimeters) unless otherwise noted




M14A (REV H)

**14-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-120, 0.150 Narrow
Package Number M14A**




M14D (REV B)

**14-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide
Package Number M14D**

Physical Dimensions inches (millimeters) unless otherwise noted (Continued)


Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

www.fairchildsemi.com