

| POSITIONS/<br>CONTACTS | A       |              | B       |              |
|------------------------|---------|--------------|---------|--------------|
|                        | MM±0.20 | [INCH±0.008] | MM±0.30 | [INCH±0.012] |
| 02/04                  | 1.00    | 0.039        | 2.00    | 0.079        |
| 03/06                  | 2.00    | 0.079        | 3.00    | 0.118        |
| 04/08                  | 3.00    | 0.118        | 4.00    | 0.157        |
| 05/10                  | 4.00    | 0.157        | 5.00    | 0.197        |
| 06/12                  | 5.00    | 0.197        | 6.00    | 0.236        |
| 07/14                  | 6.00    | 0.236        | 7.00    | 0.276        |
| 08/16                  | 7.00    | 0.276        | 8.00    | 0.315        |
| 09/18                  | 8.00    | 0.315        | 9.00    | 0.354        |
| 10/20                  | 9.00    | 0.354        | 10.00   | 0.394        |
| 11/22                  | 10.00   | 0.394        | 11.00   | 0.433        |
| 12/24                  | 11.00   | 0.433        | 12.00   | 0.472        |
| 13/26                  | 12.00   | 0.472        | 13.00   | 0.512        |
| 14/28                  | 13.00   | 0.512        | 14.00   | 0.551        |
| 15/30                  | 14.00   | 0.551        | 15.00   | 0.591        |
| 16/32                  | 15.00   | 0.591        | 16.00   | 0.630        |
| 17/34                  | 16.00   | 0.630        | 17.00   | 0.669        |
| 18/36                  | 17.00   | 0.669        | 18.00   | 0.709        |
| 19/38                  | 18.00   | 0.709        | 19.00   | 0.748        |
| 20/40                  | 19.00   | 0.748        | 20.00   | 0.787        |
| 21/42                  | 20.00   | 0.787        | 21.00   | 0.827        |
| 22/44                  | 21.00   | 0.827        | 22.00   | 0.866        |
| 23/46                  | 22.00   | 0.866        | 23.00   | 0.906        |
| 24/48                  | 23.00   | 0.906        | 24.00   | 0.945        |
| 25/50                  | 24.00   | 0.945        | 25.00   | 0.984        |
| 26/52                  | 25.00   | 0.984        | 26.00   | 1.024        |
| 27/54                  | 26.00   | 1.024        | 27.00   | 1.063        |
| 28/56                  | 27.00   | 1.063        | 28.00   | 1.102        |
| 29/58                  | 28.00   | 1.102        | 29.00   | 1.142        |
| 30/60                  | 29.00   | 1.142        | 30.00   | 1.181        |
| 31/62                  | 30.00   | 1.181        | 31.00   | 1.220        |
| 32/64                  | 31.00   | 1.220        | 32.00   | 1.260        |
| 33/66                  | 32.00   | 1.260        | 33.00   | 1.299        |
| 34/68                  | 33.00   | 1.299        | 34.00   | 1.339        |
| 35/70                  | 34.00   | 1.339        | 35.00   | 1.378        |
| 36/72                  | 35.00   | 1.378        | 36.00   | 1.417        |
| 37/74                  | 36.00   | 1.417        | 37.00   | 1.457        |
| 38/76                  | 37.00   | 1.457        | 38.00   | 1.496        |
| 39/78                  | 38.00   | 1.496        | 39.00   | 1.535        |
| 40/80                  | 39.00   | 1.535        | 40.00   | 1.575        |
| 41/82                  | 40.00   | 1.575        | 41.00   | 1.614        |
| 42/84                  | 41.00   | 1.614        | 42.00   | 1.654        |
| 43/86                  | 42.00   | 1.654        | 43.00   | 1.693        |
| 44/88                  | 43.00   | 1.693        | 44.00   | 1.732        |
| 45/90                  | 44.00   | 1.732        | 45.00   | 1.772        |
| 46/92                  | 45.00   | 1.772        | 46.00   | 1.811        |
| 47/94                  | 46.00   | 1.811        | 47.00   | 1.850        |
| 48/96                  | 47.00   | 1.850        | 48.00   | 1.890        |
| 49/98                  | 48.00   | 1.890        | 49.00   | 1.929        |
| 50/100                 | 49.00   | 1.929        | 50.00   | 1.969        |

NOTES:  
1. INSULATOR MATERIAL: L.C.P, UL 94V-0, BLACK COLOR.  
2. CONTACT MATERIAL: PHOSPHOR BRONZE.  
3. CONTACT PLATING: SEE PART NUMBER CODING.  
4. CURRENT RATING: 1 AMP.  
5. INSULATOR RESISTANCE: 1000 MEGA OHMS MIN.  
6. CONTACT RESISTANCE: 20 MILLI OHMS MAX.  
7. DIELECTRIC WITHSTANDING: AC 300V.  
8. OPERATING TEMPERATURE: -40° C TO +125° C.  
9. PROCESSING TEMP.: 260° C FOR 10 SECS MAX.  
(INDICATED TEMPERATURE AND TIME IS FOR COMPONENT INSULATOR.  
HIGHER PROCESSING TEMPERATURES MAY BE USED, PROVIDED HEAT IS  
APPLIED FROM BACK SIDE OF PCB, AND INSULATOR DOES NOT EXCEED  
INDICATED TEMPERATURE AND TIME.)

PART NUMBER CODING  
SMH100-LP\_E-D\_-\_-RA-BK

TERMINATION

RIGHT ANGLE



NUMBER OF POSITIONS

(CONTACTS PER ROW, 2 THRU 50)




PLATING

P = GOLD FLASH OVERALL.


S = 10u" GOLD OVERALL.



02-20, 0.20mm MAX.  
21-50, 0.30mm MAX.



RECOMMENDED PCB LAYOUT



RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED:

DIMENSIONS ARE IN MM[INCHES]

TOLERANCES:

ANGULAR: ± 5°

.X=± .30 [.012]

.XX=± .20 [.008]

.XXX=± .10 [.004]

SURFACE FINISH: 63 Ra


REMOVE ALL BURRS AND SHARP EDGES .010 MAX

INTERPRET DIMENSIONS AND GEOMETRIC

TOLERANCING PER: ANSI Y14.5M-1994

DRAWN 2/05/09 JH

THE INFORMATION HEREIN CONTAINS  
PROPRIETARY INFORMATION OF  
SULLINS ELECTRONICS AND IS NOT  
TO BE REPRODUCED, USED OR  
DISCLOSED TO OTHERS FOR ANY  
PURPOSE EXCEPT AS SPECIFICALLY  
AUTHORIZED IN WRITING BY AN  
OFFICER OF SULLINS ELECTRONICS.



SULLINS  
CONNECTOR SOLUTIONS

DESCRIPTION  
HEADER, MALE 1mm CC, 2 ROWS, RA

PART NUMBER

SMH100-LP\_E-D\_-\_-RA-BK

SIZE DWG. NO.

C 11194

SCALE: 10:1

SHEET 1 OF 1

A