



REV.	DATE	DESCRIPTION
NC	04/29/98	INITIAL RELEASE
A	07/20/05	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex									
7						DRAWN	G.R.S.	07/20/05											
6						CHECKED													
5	COVER	BRASS	NICKEL	1							PART DESCRIPTION								
4	FERRULE	BRASS	NICKEL	1							BNC R/A CRIMP PLUG (FOR RG-8/U, 213/U CABLE)								
3	CONTACT PIN	BRASS	GOLD	1							PART NO.								
2	INSULATOR	TEFLON	NATURAL	1							112594								
1	BODY	BRASS	NICKEL	1															
DESCRIPTION		MATERIAL	FINISH	QTY				CAD FILE		C:/112/112594.DWG		DWG. NO.	112594.DWG		REV.	A	SIZE	A	SCALE