

Vishay BCcomponents

Film Dielectric Trimmers



FEATURES

- High temperature type
- Housing dimensions:6 mm x 8 mm x 9 mm
- For a basic grid of 2.54 mm
- · Top and bottom adjustment
- · Round head
- · Mounting: radial
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

Pb-free e4




APPLICATIONS

- Antennas
- · Impedance matching circuits
- Medical
- RF
- For fine adjustment in professional applications


QUICK REFERENCE DATA				
Rated DC voltage		300 V _{DC}		
Test DC voltage for 1 min		600 V _{DC}		
Maximum contact resistance		5 mΩ		
Minimum insulation resistance betwee	n stator and rotor	10 000 MΩ		
Category temperature range		-40 °C to +125 °C		
Climatic category (IEC 60068)		40/125/21		
Minimum storage temperature		-55 °C		
Related specification		IEC 60418-1 and 4		
Effective angle of rotation		180° (rotation in 180° only, see "Life of trimmer")		
O	C _{max.} < 3.5 pF	1 mNm to 15 mNm		
Operating torque	C _{max.} ≥ 3.5 pF	1 mNm to 20 mNm		
Maximum axial thrust		2 N		
Capacitance range (C _{min.} / C _{max.})		1.2 pF / 3.5 pF to 2 pF / 18 pF		
Life of trimmer		Maximum 10 cycles: rotation in 180° only (the electrical and mechanical performance is not guaranteed if rotated beyond 10 cycles)		
Quality level		Sampling and data evaluation for quality level in accordance with "MIL-STD-105D" and "IEC 60410":		
		< 0.15 % major defects < 0.65 % minor defects		
		Each capacitor is tested for minimum $C_{\text{max.}}$ and is also subjected to the full test voltage.		



DIMENSIONS in millimeters




Trimmers BFC2 809 05... series, with round heads



ADJUSTMENT

For top adjustment a screwdriver or trimming key can be used; for bottom adjustment a key is required as shown below.



Bottom adjustment key



Vishay BCcomponents

ORDERING INFORMATION					
	CATALOG NUMBER BFC2 809 05				
C _{min.} / C _{max.}	TOP AND BOTTOM ADJUSTMENT				
(pF)	ROUND HEAD	ROUND HEAD AND FLUX GUARD			
1.2 / 3.5	215	001			
1.8 / 10	216	002			
2 / 18	217	003			

MOUNTING

The trimmer can be mounted on printed-circuit boards with a minimum hole diameter of 2.54 mm.

PACKAGING

Blister packs of 70 units each. For smallest packaging quantity (SPQ) see "Electrical Data" table.

ELECTRICAL DATA									
GUARANTEED MAX. C _{min.} / SHAPE			tan δ AT C _{max.} x 10 ⁻⁴		TEMP.	MIN. f _{res}	COL.		CATALOG
MIN. C _{max.} AT 200 kHz (pF)	OF HEAD	FIG.	1 MHz	100 MHz	COEFF. ⁽¹⁾ (10 ⁻⁶ /K)	AT C _{max.} OF DOT		SPQ	NUMBER BFC2
1.2 / 3.5	Round	1	≤ 10	≤ 20	-250 ± 350	850	Orange	700	809 05001
1.2 / 3.3	Hourid	'	≥ 10	≥ 20	-230 ± 330	830		700	809 05215
1.8 / 10	Round	-1	≤ 10	≤ 20	-250 + 350 	1200	None	700	809 05002
1.0 / 10	hourid	'	≥ 10	≥ 20		580	White	700	809 05216
0 / 10	Round	4	≤ 10	≤ 25	-250 ± 350	000	000 Ded	700	809 05217
2 / 18	Round	1 5	≥ 10	≤ 25	-230 ± 350	360 Red		700	809 05003

Note

SOLDERING CONDITIONS

For general soldering conditions and wave soldering profile, we refer to the application note "Soldering Guidelines for Film Capacitors": www.vishay.com/doc?28171

TEST PROCEDURES AND REQUIREMENTS						
IEC 60418-1 CLAUSE	IEC 60068 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS		
4.2		Method of mounting	Method A			
14		Capacitance drift	After TC measurement	Δ C/C: \leq 2.5 %; 4 % for 2 pF		
19		Thrust	Axial thrust of 2 N	ΔC/C: ≤ 0.3 %		
21		Robustness of terminations:				
21.1	Ua	Tensile	1 N	No damage		
21.2	Ub	Bending	1 cycle	No damage		
22	Na	Rapid change of temperature	1 cycle; 0.5 h at lower and 0.5 h at upper category temperature	ΔC/C: ≤ 2.5 %		
23	Т	Soldering:				
	Та	Solderability	Solder bath immersion 3 mm; 235 °C; 2 s	Good wetting, no mechanical damage		
	Tb	Resistance to heat	Solder bath: 260 °C; 10 s	No mechanical damage		

 $^{^{(1)}}$ C: 60 % to 80 % of C_{max.}; T_{amb}: from +20 °C to +125 °C



www.vishay.com

Vishay BCcomponents

IEC 60418-1 CLAUSE	IEC 60068 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS
24	Eb	Impact bump	4000 ± 10 bumps; 40 g; 6 ms	ΔC/C: ≤ 0.6 %; no mechanical damage
25	Fc	Vibration	Frequency 10 Hz to 55 Hz; amplitude 0.35 mm; 1.5 h	ΔC/C: ≤ 0.6 %; no mechanical damage
26		Climatic sequence:		ΔC/C: ≤ 2.5
26.1	В	Dry heat	16 h at upper category temperature	$tan \ \delta : \leq 10 \ x \ 10^{-4} \ for \ C_{max.} < 18 \ pF;$ $tan \ \delta : \leq 40 \ x \ 10^{-4} \ for \ C_{max.} \geq 18 \ pF$
				$R_{ins.}$: \geq 10 000 MΩ; rotor contact R: \leq 5 mΩ
26.2	D	Damp heat accelerated, first cycle	1 cycle; 24 h; +40 °C; 95 % to 100 % RH	Voltage proof: 600 V for 1 min
26.3	Aa	Cold	16 h; -40 °C	Visual examination: no mechanical damage
26.5		Damp heat accelerated, remaining cycles	1 cycle; 24 h; +40 °C; 95 % to 100 % RH	Operating torque: 1 mNm to 20 mNm
27	Ca	Damp heat steady state	21 days; +40 °C; 90 % to 95 % RH	$\begin{split} &\Delta C/C : \leq 2.5~\%\\ &\tan \delta : \leq 10~x~10^{-4}~for~C_{max.} < 18~pF;\\ &\tan \delta : \leq 25~x~10^{-4}~for~C_{max.} \geq 18~pF\\ &R_{ins.} : \geq 10~000~M\Omega;\\ &rotor~contact~R : \leq 5~m\Omega \end{split}$ $&Voltage~proof:\\ &600~V~for~1~min \end{split}$
				Visual examination: no mechanical damage Operating torque: 1 mNm to 20 mNm
29		Mechanical endurance	10 cycles Maximum 10 cycles: rotation in 180° only (the electrical and mechanical performance is not	Δ C/C: \leq 0.3 %; \leq 2.5 % for 2 pF Δ C/C after axial thrust: \leq 0.3 %; rotor contact R: \leq 5 m Ω Voltage proof:
			guaranteed if rotated beyond 10 cycles)	600 V for 1 min Visual examination: no mechanical damage
				Operating torque: 1 mNm to 20 mNm



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.