


Current Transducer

Hall Effect



Features:

- Highly reliable hall effect device.
- Compact and light weight.
- Fast response time.
- Excellent linearity of the output voltage over a wide input range.
- Excellent frequency response (> 50 KHz).
- Low power consumption (12 mA nominal).
- Capable of measuring both DC and AC, both pulsed and mixed.
- High isolation voltage between the measuring circuit and the current-carrying conductor (2.5 KV ac).
- Extended operating temperature range.
- Flame-Retardant plastic case and silicone encapsulate, using UL classified materials, ensures protection against environmental contaminants and vibration over a wide temperature and humidity range.

Applications

- UPS systems.
- Industrial robots.
- NC tooling machines.
- Elevator controllers.
- Process control devices.
- AC and DC servo systems.
- Motor speed controller.
- Electrical vehicle controllers.
- Inverter-controlled welding machines.
- General and special purpose inverters.
- Power supply for laser processing machines.
- Controller for traction equipment e.g. electric trains.
- Other automatic control systems.

Specification Table

Parameter	Symbol	Unit	TH3A thru TH30A
Nominal Input Current	I_{fn}	A dc	3 to 30
Linear Range	I_{fs}		± 9 to $\pm 150 = 3 \times I_{fn}$
Nominal Output Voltage	V_{hn}	V	4 V $\pm 1\%$ at $I_f = I_{fn}$ ($R_L = 10$ K Ω)
Offset Voltage	V_{os}	mV	Within ± 40 mV at $I_f = 0$, $T_a = 25^\circ\text{C}$
Output Resistance	R_{OUT}	Ω	< 100 Ω
Hysteresis Error	V_{oh}	mV	Within ± 15 mV at $I_f = I_{fn} \rightarrow 0$
Supply Voltage	V_{CC} / V_{EE}	V	± 15 V $\pm 5\%$
Linearity	ρ	%	Within $\pm 1\%$ of I_{fn}
Consumption Current	I_{CC}	mA	± 12 mA nominal, ± 16 mA Max.
Response Time (90% V_{hn})	T_r	μs	5 μs Max. at $d I_f / dt = I_{fn} / \mu\text{s}$
Frequency Bandwidth (-3 dB)	f_{BW}	Hz	DC to 50 KHz
Thermal Drift of Output	-	% / $^\circ\text{C}$	Within $\pm 0.1\%$ / $^\circ\text{C}$ at I_{fn}
Thermal Drift of Zero Current Offset		mV / $^\circ\text{C}$	Within ± 1.5 mV / $^\circ\text{C}$ at I_{fn}

Current Transducer


Hall Effect

Specification Table

Parameter	Symbol	Unit	TH3A thru TH30A
Dielectric Strength	-	V	2.5 KV ac × 60 s
Isolation Resistance at 1,000 V dc	R_{IS}	MΩ	> 1,000 MΩ
Operating Temperature	T_a	°C	-15°C to 80°C
Storage Temperature	T_s		-20°C to 85°C
Mass	W	g	10 g

Appearance, Dimensions and PIN Identification for TH3A thru TH30A

All dimensions in mm ± 0.2 , holes $-0, +0.2$ except otherwise noted



Current Transducer

Hall Effect



Pin Assignment	
①	-15 V
②	0 V
③	+15 V
④	Vout
⑤	I +
⑥	I -

Dimensions Table

Part Number	TH3A	TH5A	TH10A	TH15A	TH20A	TH30A
d (mm)	0.6	0.8	1.2	1.4	1.6	1.6
e (mm)	1.2	1.2	1.8	2.2	2.4	2.4

Dimensions : Millimetres

Part Number Table

Description	Part Number
Current Transducer	TH3A
Current Transducer	TH5A
Current Transducer	TH10A
Current Transducer	TH15A
Current Transducer	TH20A
Current Transducer	TH30A

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.