


Specifications



Type : Nickel-Metal Hydride Battery			Size : AA Consumer Type
Capacity ¹⁾	Typical		1850mAh
	Minimum		1750mAh
Nominal Voltage			1.2V
Charging Current x Time		Fast Charge ²⁾	1850 mA x about 1.1h
Ambient Temp.	Charge Condition	Fast Charge ²⁾	0°C - 40°C
	Discharge Condition		0°C - 50°C
	Storage Condition	- 30days	-20°C - 50°C
		30 - 90days	-20°C - 40°C
		90days - 1year	-20°C - 30°C
Internal Impedance ³⁾ (after discharge to E.V.=1.0V)			About 25m ohm(at
Weight ⁴⁾			About 28 g
Size ⁴⁾ : (Diameter) x (Height)			14.2(D) x 50.0(H) mm

1)Charge : 185mA×16h, Discharge : 370mA(E.V.=1.0V) at 20°C


2)Use recommended charging system.

3)After a few charge and discharge cycles under the above 1) condition.

4)With tube.

Typical Characteristics

Charge



Discharge

