


Space-saving 4-channel type Built-in input resistor

PhotoMOS®
RF SOP 4 Form A C×R10
Voltage-sensitive (AQS221F○2S)



RoHS compliant


FEATURES

1. Built-in input resistor means less man-hours when mounting

The voltage-sensitive type, which eliminates the need to mount an external input resistor, is now available in a small package. Man-hours spent mounting external input resistors are cut and board designing is simplified.

2. Saves space on PC board

Since the small package size remains the same while including a built-in input resistor, space on the PC board is saved. This makes it easier to incorporate space savings when designing miniature devices.



<Artistic impression of PC board space savings due to built-in resistor>
In case of SSOP.

3. Both low on-resistance (R type) and low capacitance (C type) available at excellent electrical characteristics of C×R10

- R type: On resistance Typ. 0.75Ω
Output capacitance Typ. 12.5pF
- C type: On resistance Typ. 9.5Ω
Output capacitance Typ. 1pF

TYPICAL APPLICATIONS

For multi-circuit switching;

1. Measuring and testing equipment

Semiconductor testing equipment, Probe cards, Datalogger, Board tester and other testing equipment

2. Telecommunication and broadcasting equipment

3. Medical equipment

4. Multi-point recorder

Data logger, Warping and Thermocouple, etc.

TYPES

	Type	Output rating*1		Package	Part No.*2			Packing quantity	
		Load voltage	Load current		Tube packing style	Tape and reel packing style		Tube	Tape and reel
						Picked from the 1/2/3/4/5/6/7/8-pin side	Picked from the 9/10/11/12/13/14/15/16-pin side		
AC/DC dual use	Low on resistance (R type)	40 V	0.16A	SOP16-pin	AQS221FR2S	AQS221FR2SX	AQS221FR2SZ	1 tube contains: 50 pcs.	1,000 pcs.
	Low capacitance (C type)	40 V	0.06A		AQS221FN2S	AQS221FN2SX	AQS221FN2SZ	1 batch contains: 1,000 pcs.	

Notes: *1 Indicate the peak AC and DC values.

*2 The packing style indicator "X" or "Z" is not marked on the device.

RATING

1. Absolute maximum ratings (Condition: ambient temperature 25°C 77°F)

Item		Symbol	AQS221FR2S	AQS221FN2S	Remarks
Input	Input voltage	V_{IN}	6V		
	Input reverse voltage	V_{RIN}	5V		
	Power dissipation	P_{in}	260mW		65mW for 1a
Output	Load voltage (peak AC)	V_L	40V	40V	
	Load current	I_L	0.16A	0.06A	Peak AC, DC
	Peak load current	I_{peak}	0.2A	0.12A	100ms (1shot), $V_L=DC$
	Power dissipation	P_{out}	600mW		
Total power dissipation		P_T	650mW		
I/O isolation voltage		V_{iso}	500Vrms		
Ambient temperature	Operating	T_{opr}	-40 to +85°C -40 to +185°F		(Non-icing at low temperatures)
	Storage	T_{stg}	-40 to +100°C -40 to +212°F		


2. Electrical characteristics (Condition: ambient temperature 25°C 77°F)

Item			Symbol	AQS221FR2S	AQS221FN2S	Condition
Input	Operate voltage	Typ.	V _{Fon}	1.3V		I _L = Max.
		Max.		4V		
	Turn off voltage	Min.	V _{Foff}	0.8V		
		Typ.		1.3V		
	Input current	Typ.	I _{IN}	8.5mA		
Output	On resistance	Typ.	R _{on}	0.75Ω	9.5Ω	V _{IN} = 5V I _L = Max. Within 1 s
		Max.		1.25Ω	12.5Ω	
	Output capacitance	Typ.	C _{out}	12.5pF	1pF	V _{IN} = 0V V _B = 0V f = 1MHz
		Max.		18pF	1.5pF	
	Off state leakage current	Typ.	I _{Leak}	0.02nA	0.01nA	V _{IN} = 0V V _L = Max.
		Max.		*10nA		
Transfer characteristics	Turn on time**	Typ.	T _{on}	0.07ms	0.02ms	AQS221FR2S: V _{IN} = 5V, V _L = 10V, R _L = 80Ω AQS221FN2S: V _{IN} = 5V, V _L = 10V, R _L = 500Ω
		Max.		0.5ms		
		Turn off time**		Typ.	T _{off}	
	Max.		0.2ms			
	I/O capacitance	Typ.	C _{iso}	0.8pF		f = 1MHz, V _B = 0V
		Max.		1.5pF		f = 1MHz, V _B = 0V
	Initial I/O isolation resistance	Min.	R _{iso}	1,000MΩ		500V DC

Note: If you wish to change the input voltage, rating or performance, please inquire with our sales.

*Available as custom orders (1 nA or less)

**Turn on/Turn off time



3. Recommended operating conditions (Ambient temperature: 25°C 77°F)

Please use under recommended operating conditions to obtain expected characteristics.

Item		Symbol	Min.	Max.	Unit
Input voltage		V_{IN}	4.5	5.5	V
AQS221FR2S	Load voltage (Peak AC)	V_L	—	15	V
	Continuous load current	I_L	—	0.16	A
AQS221FN2S	Load voltage (Peak AC)	V_L	—	15	V
	Continuous load current	I_L	—	0.06	A


■ These products are not designed for automotive use.

If you are considering to use these products for automotive applications, please contact your local Panasonic Corporation technical representative.

REFERENCE DATA


1. Load current vs. ambient temperature characteristics

Allowable ambient temperature: -40 to +85°C
-40 to +185°F




2. Load current vs. Load voltage characteristics

Ambient temperature: 25°C 77°F




3. On resistance vs. ambient temperature characteristics

Input voltage: 5V; Load voltage: 10V (DC);
Continuous load current: 160mA (DC) R type,
60mA (DC) C type




4. Turn on time vs. ambient temperature characteristics

Input voltage: 5V; Load voltage: 10V (DC);
Continuous load current: 125mA (DC) R type,
20mA (DC) C type




5. Turn off time vs. ambient temperature characteristics

Input voltage: 5V; Load voltage: 10V (DC);
Continuous load current: 125mA (DC) R type,
20mA (DC) C type




6. Operate voltage vs. ambient temperature characteristics

Load voltage: 10V (DC);
Continuous load current: 160mA (DC) R type,
60mA (DC) C type




7. Turn off voltage vs. ambient temperature characteristics

Load voltage: 10V (DC);
Continuous load current: 160mA (DC) R type,
60mA (DC) C type




8. Input current vs. ambient temperature characteristics

Sample: All types
Input voltage: 5V




9. Current vs. voltage characteristics of output at MOS portion


Ambient temperature: 25°C 77°F




10. Input current vs. input voltage characteristics
Sample: All types
Ambient temperature: 25°C 77°F
(Recommended input voltage: 5±0.5V)




11. Off state leakage current vs. load voltage characteristics
Ambient temperature: 25°C 77°F




12. Turn on time vs. input voltage characteristics
Load voltage: 10V (DC);
Continuous load current: 125mA (DC) R type,
20mA (DC) C type; Ambient temperature: 25°C 77°F




13. Turn off time vs. input voltage characteristics
Load voltage: 10V (DC);
Continuous load current: 125mA (DC) R type,
20mA (DC) C type; Ambient temperature: 25°C 77°F




14. Output capacitance vs. applied voltage characteristics
Frequency: 1 MHz, 30mVrms;
Ambient temperature: 25°C 77°F



15. Isolation vs. frequency characteristics (50Ω impedance)
Ambient temperature: 25°C 77°F



16. Insertion loss vs. frequency characteristics (50Ω impedance)
Ambient temperature: 25°C 77°F



"PhotoMOS®", "PhotoMOS" and "PHOTOMOS" are registered trademarks of Panasonic Corporation.

*Recognized in Japan, the United States, all member states of European Union and other countries.

Please contact

Panasonic Corporation

Electromechanical Control Business Division

■ 1006, Oaza Kadoma, Kadoma-shi, Osaka 571-8506, Japan
industrial.panasonic.com/ac/e/

Panasonic®

©Panasonic Corporation 2017