



DRG No. CP32943	ISSUE 1	TYPE No. OXL/CLH/100/P/FLxx/- OXL/CLH/100/P/CL/FLxx/-		DIM. IN: MILLIMETRES	ODC:QS:40077 ISSUE 1 DO NOT SCALE	THIS DRAWING AND THE COPYRIGHT AND DESIGN RIGHT THEREIN ARE THE PROPERTY OF OXLEY DEVELOPMENTS CO. Ltd. AND MUST NOT BE REPRODUCED OR DISCLOSED TO A THIRD PARTY WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.	ISS	MODIFICATION	DATE																																											
© COPYRIGHT OXLEY DEVELOPMENTS Co. Ltd. 2001																																																				
				<table><tr><th colspan="2">MATERIALS AND FINISHES</th></tr><tr><td>DESCRIPTION</td><td>MATERIAL, FINISH</td></tr><tr><td>BODY</td><td>ALUMINIUM ALLOY, MATT BLACK ANODISED</td></tr><tr><td>LENS</td><td>POLYCARBONATE</td></tr><tr><td>TERMINATIONS</td><td>FLYING LEADS : COLOUR RED AND BLACK WIRE INSULATION. LENGTH DEFINED IN PART No. (cm)</td></tr><tr><td>NUT</td><td>ALUMINIUM ALLOY</td></tr><tr><td>WASHER</td><td>BeCu. TIN PLATED</td></tr></table>			MATERIALS AND FINISHES		DESCRIPTION	MATERIAL, FINISH	BODY	ALUMINIUM ALLOY, MATT BLACK ANODISED	LENS	POLYCARBONATE	TERMINATIONS	FLYING LEADS : COLOUR RED AND BLACK WIRE INSULATION. LENGTH DEFINED IN PART No. (cm)	NUT	ALUMINIUM ALLOY	WASHER	BeCu. TIN PLATED																																
MATERIALS AND FINISHES																																																				
DESCRIPTION	MATERIAL, FINISH																																																			
BODY	ALUMINIUM ALLOY, MATT BLACK ANODISED																																																			
LENS	POLYCARBONATE																																																			
TERMINATIONS	FLYING LEADS : COLOUR RED AND BLACK WIRE INSULATION. LENGTH DEFINED IN PART No. (cm)																																																			
NUT	ALUMINIUM ALLOY																																																			
WASHER	BeCu. TIN PLATED																																																			
ELECTRICAL / OPTICAL CHARACTERISTICS				<table><tr><th></th><th>AlGaAs RED</th><th>YELLOW</th><th>GREEN</th><th>BLUE</th><th>WHITE</th></tr><tr><td>LUMINOUS INTENSITY TYPICAL (mcd AT RATED VOLTAGE)</td><td>1200</td><td>1000</td><td>1250</td><td>1200</td><td>1000</td></tr><tr><td>WAVELENGTH TYPICAL (nm)</td><td>637</td><td>585</td><td>525</td><td>470</td><td>N/A</td></tr><tr><td>FORWARD CURRENT (mA) TYP</td><td>20</td><td>20</td><td>20</td><td>20</td><td>20</td></tr><tr><td>FORWARD VOLTAGE (V)</td><td>1.9</td><td>1.9</td><td>3.6</td><td>3.6</td><td>3.6</td></tr><tr><td>REVERSE VOLTAGE (V) MAX</td><td colspan="5">5</td></tr></table>				AlGaAs RED	YELLOW	GREEN	BLUE	WHITE	LUMINOUS INTENSITY TYPICAL (mcd AT RATED VOLTAGE)	1200	1000	1250	1200	1000	WAVELENGTH TYPICAL (nm)	637	585	525	470	N/A	FORWARD CURRENT (mA) TYP	20	20	20	20	20	FORWARD VOLTAGE (V)	1.9	1.9	3.6	3.6	3.6	REVERSE VOLTAGE (V) MAX	5					<table><tr><th colspan="1">MOUNTING DETAILS</th></tr><tr><td>MOUNTING HOLE : Ø10.15±0.1</td></tr><tr><td>RECOMMENDED MOUNTING TORQUE : 1Nm</td></tr><tr><td>CHASSIS THICKNESS : 1.5mm (Min)</td></tr></table>			MOUNTING DETAILS	MOUNTING HOLE : Ø10.15±0.1	RECOMMENDED MOUNTING TORQUE : 1Nm	CHASSIS THICKNESS : 1.5mm (Min)			
	AlGaAs RED	YELLOW	GREEN	BLUE	WHITE																																															
LUMINOUS INTENSITY TYPICAL (mcd AT RATED VOLTAGE)	1200	1000	1250	1200	1000																																															
WAVELENGTH TYPICAL (nm)	637	585	525	470	N/A																																															
FORWARD CURRENT (mA) TYP	20	20	20	20	20																																															
FORWARD VOLTAGE (V)	1.9	1.9	3.6	3.6	3.6																																															
REVERSE VOLTAGE (V) MAX	5																																																			
MOUNTING DETAILS																																																				
MOUNTING HOLE : Ø10.15±0.1																																																				
RECOMMENDED MOUNTING TORQUE : 1Nm																																																				
CHASSIS THICKNESS : 1.5mm (Min)																																																				
ORDERING INFORMATION : WHEN ORDERING, STATE TYPE NUMBER, SPECIFYING FLYING LEAD LENGTH AND LED COLOUR e.g OXL/CLH/100/P/FL10/G FLYING LEAD LENGTH IN cm COLOUR (AL, Y, G, B or W) AlGaAs RED, RED, YELLOW, GREEN, BLUE or WHITE							MATERIAL AS STATED			DRAWN Simon Ryssam																																										
							FINISH AS STATED		CHECKED T. DAVIS																																											
							PLATING AS STATED		APPROVED DA01/351																																											
							TOLERANCE AS STATED		DATE 10 DEC 01																																											
							REMARKS																																													
							TITLE WIDE ANGLE HIGH BRIGHTNESS LED INDICATOR WITH PROMINENT LENS AND FLYING LEADS																																													
		Tel. 01229 582621 Fax. 01229 585090		OXLEY DEVELOPMENTS COMPANY LTD.		Ulverston Cumbria LA12 9QG ENGLAND	SCALE 2 : 1	TYPE No. OXL/CLH/100/P/FLxx/- OXL/CLH/100/P/CL/FLxx/-		DRG No. CP32943	ISSUE 1																																									