

RGSC-Series





The RGSC-Series Super Curvette rocker switches offer the Curvette styling in a double pole construction with higher electrical ratings and high inrush capabilities. These switches can handle up to 125 amp peak inrush current and can accommodate a wide range of panel cutouts due to the patented mounting ear construction. International ratings are available up to 20 amps.

Specifications

- Certifications*: UL, CSA, VDE
- Dielectric Strength: 1,000V (minimum)
- Insulation Resistance: 100 Megohms (minimum)
- Base Material: Nylon
- Actuator Material: Nylon

* Due to ongoing technological advances, consult factory for certification specifics.

Dimensional Specifications: in. [mm]



RGSC

SERIES

RGSC	STANDARD BASE
RGSB	METAL BRACKET
RGSE	EUROPEAN BASE

C

CIRCUIT¹

A	OFF-NONE-ON SINGLE POLE
B	ON-NONE-ON SINGLE POLE
C	OFF-NONE-ON DOUBLE POLE
D	ON-NONE-ON DOUBLE POLE
E	POLE 1 ON-NONE-ON POLE 2 OFF-NONE-ON
F	POLE 1 ON-NONE-OFF POLE 2 OFF-NONE-ON

70

1

RATING²

20	15A 250VAC 20A 125VAC 3/4HP 125-250VAC
21	15A 250 VAC 20A 125VAC
57	10A 250VAC 3/4HP 15A 125VAC 3/4HP 6A 277VAC 3/4HP
70	15A 250VAC 20A 125VAC 3/4HP 125-250VAC 16(6)A 250VAC T85
71	15A 250VAC 20A 125VAC 16(6)A 250VAC T85

TERMINATION

0	SOLDER LUG
1	.250TAB (QC)
5	WIRE LEAD

-

R

-

B

ACTUATOR STYLE

P	PADDLE
R	ROCKER

ACTUATOR COLOR³

B	BLACK
W	WHITE

-

B

-

BASE COLOR³

B	BLACK
W	WHITE

ROCKER FACE IMPRINTED LEGEND⁴

0	NO LEGEND
A	OFF-ON (VERTICAL)
B	OFF-ON (HORIZONTAL)
D	O-I (HORIZONTAL)
E	O-I (VERTICAL)
F	ON-OFF (VERTICAL)
G	ON-OFF (HORIZONTAL)

NOTES:

Shading indicates standard configurations.

Panel Cut-Out Recommendations: For sheet metal panels, switch must enter panel in same direction as the punch. (Burr on bottom.) Test cut hole in actual material.

1 Circuits E and F available with Rating Codes 20, 21 and 57 only.

2 Additional ratings are available. Consult factory.

3 Custom colors are available. Consult factory.

4 White is standard with dark actuators; black is standard with light actuators.