



Series 8 Elevator Socket w/Collet Contacts & Solder Pin Tails

FEATURES

- Ideal for Elevating Devices (Displays, Switches, etc.) to Desired Level with 0.240 to 1.250 [6.10 to 31.75] Height Extension

GENERAL SPECIFICATIONS

- STANDARD SOCKET BODY & SPACER: black UL 94V-0 glass-filled 4/6 Nylon
- PIN BODY: Brass 360 1/2-hard per UNS C36000 ASTM B16/B16M-05
- PIN BODY PLATING: 10 μ [0.25 μ] min. Au per MIL-G-45204 –OR– 200 μ [5.08] min. 93/7 Sn/Pb per ASTM B545 –OR– 200 μ [5.08 μ] min. Sn per ASTM B545 Type 1 over 100 μ [2.54 μ] min. Ni per SAE AMS-QQ-N-290B
- 4-FINGER COLLET CONTACT: BeCu per UNS C17200 ASTM B194-08
- CONTACT PLATING: 30 μ [0.76 μ] min. Au per MIL-G-45204 over 50 μ [1.27 μ] min. Ni per SAE AMS-QQ-N-290B
- CONTACT CURRENT RATING: 3 amps
- OPERATING TEMPERATURE: -67°F to 221°F [-55°C to 105°C]
- INSERTION FORCE: 180g/pin, based on 0.018 [0.46] dia. test lead
- WITHDRAWAL FORCE: 90g/pin, based on 0.018 [0.46] dia. test lead
- NORMAL FORCE: 140g/pin, based on 0.018 [0.46] dia. test lead
- ACCEPTS LEADS: 0.015-0.025 [0.38-0.64] dia., 0.110-0.150 [2.79-3.81] long

MOUNTING CONSIDERATIONS

- SUGGESTED PCB HOLE SIZE: 0.035 $\pm$ 0.002 [0.89 $\pm$ 0.05] dia.



ORDERING INFORMATION

XX-8 XXXX-X 10 C XX


- Optional Solder Pin Tail Plating
TL = Sn/Pb
- Collet Style
- Sn-plated Solder Pin Tail
- Row-to-Row Spacing
3 "Y" = 0.300 [7.62]
6 "Y" = 0.600 [15.24]
- Seating Plane Height
0.240 [6.10] to 1.250 [31.75]
Example: 0.240 height = "8240"
1.250 height = "81250"
- Series
- No. of Pins
(See Table)



"W" # PINS PER ROW x 0.100 [2.54]
"X" (# PINS PER ROW - 1) x 0.100 [2.54]



BODY STYLE B



BODY STYLE C

Centers "Y"	Dim. "Z"	Body Style	Available Sizes
0.300 [7.62]	0.400 [10.16]	C	6 thru 20
		B	22 thru 40
0.600 [15.24]	0.700 [17.78]	C	6 thru 40
		B	42 thru 48

ALL DIMENSIONS: INCHES [MILLIMETERS]

ALL TOLERANCES: $\pm$ 0.005 [0.13] UNLESS OTHERWISE SPECIFIED

FOR COLLET CONTACTS ON 0.200 [5.08] CENTERS, SEE DATA SHEET 13007

FOR BIFURCATED CONTACTS, SEE DATA SHEET 13006

CONSULT FACTORY FOR OTHER SIZES AND CONFIGURATIONS

CUSTOMIZATION: ARIES SPECIALIZES IN CUSTOM DESIGN AND PRODUCTION. SPECIAL MATERIALS, PLATINGS, SIZES, AND CONFIGURATIONS CAN BE FURNISHED, DEPENDING ON QUANTITY.

ARIES RESERVES THE RIGHT TO CHANGE PRODUCT GENERAL SPECIFICATIONS WITHOUT NOTICE

PRINTOUTS OF THIS DOCUMENT MAY BE OUT-OF-DATE AND SHOULD BE CONSIDERED UNCONTROLLED



ARIES
ELECTRONICS, INC.

2609 Bartram Road • Bristol, PA 19007-6810 USA
TEL 215-781-9956 • FAX 215-781-9845
WWW.ARIESELEC.COM • INFO@ARIESELEC.COM



13008
Rev. 1.3
1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Aries Electronics:

[10-81250-610C](#) [16-8438-310C](#) [16-8608-310C](#) [36-8750-310C](#) [28-8670-610C](#) [28-8600-610C](#) [28-8620-610C](#) [28-8250-610C](#) [28-8240-610C](#) [28-8800-610C](#) [28-8830-610C](#) [28-8400-610C](#) [28-8350-610C](#) [28-8370-610C](#) [28-8300-610C](#) [28-8750-610C](#) [28-8700-610C](#) [28-8500-610C](#) [18-8590-610C](#) [32-8724-310C](#) [08-8415-610C](#) [18-8406-310C](#) [08-8305-610C](#) [20-8400-610C](#) [20-8950-610C](#) [20-8500-610C](#) [32-8312-610C](#) [10-8335-610C](#) [10-8545-610C](#) [14-8385-310C](#) [40-8700-310C](#) [40-8300-310C](#) [30-8950-610C](#) [20-8724-610C](#) [24-8370-610C](#) [24-8700-610C](#) [24-8750-610C](#) [24-8500-610C](#) [24-8550-610C](#) [24-8900-610C](#) [24-8250-610C](#) [24-8600-610C](#) [16-8380-310C](#) [16-8990-310C](#) [16-8590-310C](#) [16-8480-310C](#) [24-8312-310C](#) [26-8450-310C](#) [26-8900-310C](#) [26-8500-310C](#) [26-8530-310C](#) [26-8350-310C](#) [12-8358-310C](#) [16-8561-310C](#) [14-8456-310C](#) [14-8606-310C](#) [14-8346-310C](#) [20-8685-310C](#) [28-8459-610C](#) [18-8355-610C](#) [18-8375-610C](#) [20-8385-310C](#) [18-8545-610C](#) [40-8785-610C](#) [20-750-310C](#) [22-81250-310C](#) [32-81000-310C](#) [28-81250-610C](#) [38-81250-610C](#) [28-81010-610C](#) [28-81000-610C](#) [38-81000-610C](#) [18-81180-610C](#) [08-8937-610C](#) [24-81000-310C](#) [24-81250-310C](#) [14-8501-310C](#) [22-8600-610C](#) [22-8850-610C](#) [32-8724-610C](#) [22-8500-610C](#) [32-81000-610C](#) [22-81250-610C](#) [32-81250-610C](#) [22-81150-610C](#) [40-8785-310C](#) [28-8472-610C](#) [10-8375-310C](#) [10-8575-310C](#) [20-8724-310C](#) [30-8940-310C](#) [24-8240-310C](#) [24-8600-310C](#) [24-8770-310C](#) [24-8300-310C](#) [24-8900-310C](#) [24-8500-310C](#) [16-8625-610C](#) [10-8433-610C](#) [10-8563-610C](#)