






	10	9	8	7	6	5	4	3	2	1
F	15									
	14									
	13									
	12									
	11									
	10	560123								
	9		505151							
	8	560123		502351						
	7									
	6	560123								
	5									
E	4									
	3	560123								
	2									
CKTS	ISL Receptacle	TPA Receptacle	Standard Receptacle							
Mate With Series										




A	2極 2CKT		RELEASED EC NO: JTR2016-0011 0		DRWN:YTAMAKI 2015/03/25 CHKD:HKOMATSU 2015/07/24 APPR:MAYAMAMOTO 2015/07/24	DESCRIPTION F ₁ =0 F ₂ =0 F ₃ =0	mm INCH 4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE ANGULAR ± ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWN BY YTAMAKI 2015/03/25 CHECKED BY HKOMATSU 2015/07/24 APPROVED BY MAYAMAMOTO 2015/07/24 MATERIAL NO. ---		TITLE 2.0MM PITCH W/B CONN. INTERFACE DRAWING	
	RECOMMENDED DIMENSIONS FOR CONNECTOR INTERFACE						molex					
							DOCUMENT NO. SD-502352-003-JP		SHEET NO. 2 OF 2			
							SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

tb_frame_A3_P_AM_T Rev. G 2012/01/11	9	8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---	---	---


RECOMMENDED DIMENSIONS
FOR CONNECTOR INTERFACE



7. 一般公差
GENERAL TOLERANCES
10 UNDER:0.2
10 OVER 30 UNDER:0.25
30 OVER:0.3
ANGULAR $\pm 1^{\circ}$



SECTION Z-Z




MATED DRAWING

注記
NOTES

- 材質
ウエハー: 耐熱性ナイロン UL94V-0
ピン: 銅合金、ニッケル下地、錫メッキ、金メッキ
フィッティングネール: 銅合金、ニッケル下地、錫メッキ
MATERIAL
WAFER: POLYAMIDE UL94V-0
PIN: COPPER ALLOY, GOLD OR TIN OVER NICKEL PLATE.
FITTING NAIL: COPPER ALLOY, TIN OVER NICKEL PLATE.
- 色: ナチュラル
COLOR: NATURAL
- 嵌合相手:
ハウジング: 502351-xx00
錫メッキ端子: 50212-8*00, 50372-8*00, 560085-0101
金メッキ端子: 56161-8*81
MATES WITH
HOUSING: 502351-xx00
SN PLATING TERMINAL: 50212-8*00, 50372-8*00, 560085-0101
AU PLATING TERMINAL: 56161-8*81
- エンボス梱包品の詳細はSD-560020-002参照
DETAILED TAPING PACKAGE, SEE SD-560020-002
- ELV及びRoHS適合
ELV AND ROHS COMPLIANT
- 半田付け面のコプラナリティ: 0.1mm MAX.
CO-PLANARITY OF SOLDER TAILS TO BE 0.1mm MAX.

REVISED		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO: JTR2015-0089						MM ONLY		5:1		METRIC			
DRAWN: YAMAKI		DESCRIPTION		mm INCH		DRAWN BY		DATE		2.0MM PITCH W/B CONN. WAFER ASSY ST. SMT molex			
2014/12/25				4 PLACES ± --- ± ---		SHSHIBATA		2009/02/18					
CHKD: HKOMATSU				3 PLACES ± --- ± ---		CHECKED BY		DATE					
APPR: MAYAMOTO				2 PLACES ± --- ± ---		HKOMATSU		2009/02/18					
				1 PLACE ± --- ± ---		APPROVED BY		DATE					
				0 PLACE ± --- ± ---		AKANESHIGE		2009/02/18					
				ANGULAR ± °		MATERIAL NO.				DOCUMENT NO.		SHEET NO.	
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART				SD-560020-001		1 OF 4	
						SIZE							
						A3							




2CKTS

3CKTS


4CKTS

5CKTS


6CKTS



7CKTS



9CKTS



10CKTS

REVISED EC NO: JTR2015-0089 TDRWN: YAMAKI 2014/12/25 CHKD: HKOMATSU 2014/12/25 APPR: MAYAMAMOTO 2015/04/28	DESCRIPTION REV	QUALITY SYMBOLS F₁ = 0 F₂ = 0 F₃ = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
					DRAWN BY SHSHIBATA	DATE 2009/02/18	TITLE 2.0MM PITCH W/B CONN. WAFER ASSY ST. SMT					
					CHECKED BY HKOMATSU	DATE 2009/02/18						
					APPROVED BY AKANESHIGE	DATE 2009/02/18	molex					
					MATERIAL NO.							DOCUMENT NO.
					SEE CHART		SD-560020-001		2 OF 4			
					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

