



CONTENTS:

6255 (m-f) Right Angle
6256 Type N (m) to DIN (m)
6257 Type N (f) to DIN (m)
6258 DIN (f-f)
6259 Type N (m) to DIN (f)
6260 Type N (f) to DIN (f)

FEATURES:

- Kit contains the most frequently needed adapters to fit between instruments or equipment with type N and DIN connectors
- Peak power rating of 40 kW
- Foam lined zipper case keeps adapters handy for instant use
- Replacement adapters are available individually

MATERIALS:

Pomona's 7/16 DIN adapters are made in the US and feature silver plated outer shells, Teflon insulation and silver plated, Beryllium Copper female and brass male center contacts.

RATINGS:

Impedance: 50 Ohms
Frequency Range: DC - 7.5 GHz
Insertion Loss: - .01 dB $\sqrt{\text{Frequency GHz}}$
VSWR (Max): < 1.10:1 @ DC - 7.5 GHz
Third Order IM: -dBc > -150 dBc

ORDERING INFORMATION: Model 6254

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90512 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

6254