


32Gb Mass Storage: MT29F32G08CBACAWP



Specifications

- Bits/Cell:** MLC
- Brand:** Micron
- Bus Width:** x8
- CE Chip Count:** 1
- Chip Enable:** Dual
- Component Density:** 32Gb
- Fab:** Micron
- Family:** NAND Flash
- Flash Voltage:** 1.8V
- Generation (primary):** First Generation
- I/O:** Common
- I/O Channels:** 1
- Interface:** Async
- Manufacturer:** Micron
- Mode Operation:** Dual Die
- NAND Interface:** Async Only
- Number of Die:** 1
- Operating Temp:** 0C to +70C
- Package:** TSOP
- Package Code:** WP
- Package Size:** 12 x 20 x 1.2
- Package Type:** Lead Free
- Part Status Code:** Production
- Pin Count:** 48-pin
- RoHS:** Yes
- Show External:** Yes
- Show WebDEV:** No
- Technology:** Mass Storage
- Voltage:** 3.3V

Data Sheets

- [Datasheet: NAND Flash, MLC, 32/64/128Gb, Async/Sync, L73A](#)
Rev. Date: 12/2011, File Size: 3.17 MB

Certifications

- [RoHS Certificate of Compliance.pdf](#)
- [China RoHS Certificate.pdf](#)

Orderable Part	Part Status	Buy Online
MT29F32G08CBACAWP:C	Production	Available

Please Note: Distributor inventory is an estimate and may not reflect actual available memory. Some links on this page will take you from the Micron web site. Micron does not control the content on these web sites.