





mat'l. code				surface		tolerance		projection		product family				
				ISO 1302 ✓		ISO 406 ISO 1101				CLINCHER				
ltr		ecn nodr		date		tolerances unless otherwise specified						title		
A	V03-0423	TAB	4/17/03	angles	linear	.XXX±.01/.XXX±0.3				INCH/MM				
B	M05-0087	MHT	6/15/05			.XXX±.005/.XXX±0.13								
C	M06-0001	MHT	1/03/06			.XXX±.0020/.XXX±0.051								
				0°±2°		scale 3:1				LATCHING CLINCHER™ RECEPTACLE ASSEMBLY				
D	M06-0233	AGS	06/12/06	dr	T. BRUNGARD	4/17/03				dwg no		sheet 1 of 6		size
E	M07-0170	MHT	3/30/07	engr	H. SUNDY	4/17/03				10022753		A3		
F	ELX-N-010491	ZK	06/03/12	chr	H. SUNDY	4/17/03								
				appd	H. SUNDY	4/17/03				type Product Customer Drawing				
sheet		revision		F	F	F	F	F						
index		sheet		1	2	3	4	5	6					

PLATING AVAILABLE

PLATING CODE	TERMINAL	SPRING
1	100u"/2.54u MIN. THICK PURE TIN	10u"/.25u MIN. THICK PURE TIN
2	30u"/.76u MIN. GOLD OR GXT STRIPE IN BOX AREA	3u"/.08u MIN. GOLD OVER 50u"/1.27u MIN. NICKLE

PRODUCT NUMBER
10022753-XXXLF

LEAD FREE OPTION
NOTE 7,8

NO OF POSITIONS
AND PLATING

BASE PART NUMBER

WINDOW

Q

.100
2.54
REF

CABLE TERMINATED
AND LID CLOSED
SCALE: 6/1

CABLE

NOTES:

- MOLDING MAT'L: THERMOPLASTIC, FLAME RETARDANT PER UL 94V-0.
COLOR: BLUE.
- TERMINAL MAT'L: 1/2 HARD CuNi ALLOY, UNS-C72500.
PLATING: SEE TABULATION AND PLATING TABLE.
- SPRING MAT'L: 1/2 HARD BeCu ALLOY, UNS-C17200.
PLATING: SEE TABULATION AND PLATING TABLE.
- LATCH SWINGS CLOSED AFTER TERMINATION MAINTAINING A MAX OVER
ALL HEIGHT OF .100/2.54
- LABEL IN THIS AREA P/N AND DATE LOT CODE (WEEK AND YEAR)
ON DASH No.-067 AND -167 ONLY.
- KNURL MARK INDICATES FOR USE WITH INK TERMINATION. CONSULT WITH
BERG ELECTRONICS TECHNICAL REPRESENTATIVE FOR SPECIFIC APPLICATIONS.
- ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR
LEAD FREE OPTION.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES
AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO
A MANUFACTURING SOLDER PROCESS
- PLATING OPTION
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.



INK
TERMINATION



CONVENTIONAL
TERMINATION

DETAIL Z
SCALE 6/1

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection INCH/MM		product family CLINCHER	
ltr ecn nodr date		tolerances unless otherwise specified		line		scale 1:1		title LATCHING CLINCHER™ RECEPTACLE ASSEMBLY	
F		angles	0°±2'	line	XXX±.005/0.0013			dwg no 10022753	
		dr	T. BRUNGARD	4/17/03			sheet 2 of 6		size A3
		engr	H. SUNDY	4/17/03			type		Product Customer Drawing
		chr	H. SUNDY	4/17/03					
		appd	H. SUNDY	4/17/03					
sheet index	revision sheet								

1				2		3						4		5		6	
PRODUCT NO.	NO. OF	DIM. L	DIM. L	DIM. M	DIM. M	DIM. C	DIM. C	PLATING		TERMINATION							
NOTE 7	POSITIONS	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	CODE		NOTE 6							
10022753-006	6	0.500	12.70	0.790	20.07	0.715	18.16	1		CONVENTIONAL							
10022753-007	7	0.600	15.24	0.890	22.61	0.815	20.70	1		CONVENTIONAL							
10022753-008	8	0.700	17.78	0.990	25.15	0.915	23.24	1		CONVENTIONAL							
10022753-009	9	0.800	20.32	1.090	27.69	1.015	25.78	1		CONVENTIONAL							
10022753-010	10	0.900	22.86	1.190	30.23	1.115	28.32	1		CONVENTIONAL							
10022753-011	11	1.000	25.40	1.290	32.77	1.215	30.86	1		CONVENTIONAL							
10022753-012	12	1.100	27.94	1.390	35.31	1.315	33.40	1		CONVENTIONAL							
10022753-013	13	1.200	30.48	1.490	37.85	1.415	35.94	1		CONVENTIONAL							
10022753-014	14	1.300	33.02	1.590	40.39	1.515	38.48	1		CONVENTIONAL							
10022753-015	15	1.400	35.56	1.690	42.93	1.615	41.02	1		CONVENTIONAL							
10022753-016	16	1.500	38.10	1.790	45.47	1.715	43.56	1		CONVENTIONAL							
10022753-017	17	1.600	40.64	1.890	48.01	1.815	46.10	1		CONVENTIONAL							
10022753-018	18	1.700	43.18	1.990	50.55	1.915	48.64	1		CONVENTIONAL							
10022753-019	19	1.800	45.72	2.090	53.09	2.015	51.18	1		CONVENTIONAL							
10022753-020	20	1.900	48.26	2.190	55.63	2.115	53.72	1		CONVENTIONAL							
10022753-021	21	2.000	50.80	2.290	58.17	2.215	56.26	1		CONVENTIONAL							
10022753-022	22	2.100	53.34	2.390	60.71	2.315	58.80	1		CONVENTIONAL							
10022753-023	23	2.200	55.88	2.490	63.25	2.415	61.34	1		CONVENTIONAL							
10022753-024	24	2.300	58.42	2.590	65.79	2.515	63.88	1		CONVENTIONAL							
10022753-025	25	2.400	60.96	2.690	68.33	2.615	66.42	1		CONVENTIONAL							
10022753-026	26	2.500	63.50	2.790	70.87	2.715	68.96	1		CONVENTIONAL							
10022753-027	27	2.600	66.04	2.890	73.41	2.815	71.50	1		CONVENTIONAL							
10022753-028	28	2.700	68.58	2.990	75.95	2.915	74.04	1		CONVENTIONAL							
10022753-029	29	2.800	71.12	3.090	78.49	3.015	76.58	1		CONVENTIONAL							
10022753-030	30	2.900	73.66	3.190	81.03	3.115	79.12	1		CONVENTIONAL							
10022753-031	31	3.000	76.20	3.290	83.57	3.215	81.66	1		CONVENTIONAL							
10022753-032	32	3.100	78.74	3.390	86.11	3.315	84.20	1		CONVENTIONAL							
10022753-033	33	3.200	81.28	3.490	88.65	3.415	86.74	1		CONVENTIONAL							
10022753-034	34	3.300	83.82	3.590	91.19	3.515	89.28	1		CONVENTIONAL							

mat'l. code				surface ☒ tolerance ☒		projection ☒		product family CLINCHER			
ltr ecn nodr				date		ISO 1302 ☒ ISO 406 ☒ ISO 1101 ☒					
F						tolerances unless otherwise specified		title			
						$XX \pm .01 / 0.XX \pm .03$ $XXX \pm .005 / 0.XX \pm .03$ $XXXX \pm .0020 / 0.XXX \pm .051$					
				angles		linear		$INCH/MM$			
				0°±2°				scale 1:1			
				dr		T. BRUNGARD		dwg no sheet 3 of 6 size			
				engr		H. SUNDY		10022753 A3			
				chr		H. SUNDY		type Product Customer Drawing			
				appd		H. SUNDY					
sheet index		revision sheet									

1

2

3

4

5

6

PRODUCT NO.	NO. OF	DIM. L	DIM. L	DIM. M	DIM. M	DIM. C	DIM. C	PLATING	TERMINATION	
NOTE 7	POSITIONS	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	CODE	NOTE 6	
10022753-106	6	0.500	12.70	0.790	20.07	0.715	18.16	1	INK	
10022753-107	7	0.600	15.24	0.890	22.61	0.815	20.70	1	INK	
10022753-108	8	0.700	17.78	0.990	25.15	0.915	23.24	1	INK	
10022753-109	9	0.800	20.32	1.090	27.69	1.015	25.78	1	INK	
10022753-110	10	0.900	22.86	1.190	30.23	1.115	28.32	1	INK	
10022753-111	11	1.000	25.40	1.290	32.77	1.215	30.86	1	INK	
10022753-112	12	1.100	27.94	1.390	35.31	1.315	33.40	1	INK	
10022753-113	13	1.200	30.48	1.490	37.85	1.415	35.94	1	INK	
10022753-114	14	1.300	33.02	1.590	40.39	1.515	38.48	1	INK	
10022753-115	15	1.400	35.56	1.690	42.93	1.615	41.02	1	INK	
10022753-116	16	1.500	38.10	1.790	45.47	1.715	43.56	1	INK	
10022753-117	17	1.600	40.64	1.890	48.01	1.815	46.10	1	INK	
10022753-118	18	1.700	43.18	1.990	50.55	1.915	48.64	1	INK	
10022753-119	19	1.800	45.72	2.090	53.09	2.015	51.18	1	INK	
10022753-120	20	1.900	48.26	2.190	55.63	2.115	53.72	1	INK	
10022753-121	21	2.000	50.80	2.290	58.17	2.215	56.26	1	INK	
10022753-122	22	2.100	53.34	2.390	60.71	2.315	58.80	1	INK	
10022753-123	23	2.200	55.88	2.490	63.25	2.415	61.34	1	INK	
10022753-124	24	2.300	58.42	2.590	65.79	2.515	63.88	1	INK	
10022753-125	25	2.400	60.96	2.690	68.33	2.615	66.42	1	INK	
10022753-126	26	2.500	63.50	2.790	70.87	2.715	68.96	1	INK	
10022753-127	27	2.600	66.04	2.890	73.41	2.815	71.50	1	INK	
10022753-128	28	2.700	68.58	2.990	75.95	2.915	74.04	1	INK	
10022753-129	29	2.800	71.12	3.090	78.49	3.015	76.58	1	INK	
10022753-130	30	2.900	73.66	3.190	81.03	3.115	79.12	1	INK	
10022753-131	31	3.000	76.20	3.290	83.57	3.215	81.66	1	INK	
10022753-132	32	3.100	78.74	3.390	86.11	3.315	84.20	1	INK	
10022753-133	33	3.200	81.28	3.490	88.65	3.415	86.74	1	INK	
10022753-134	34	3.300	83.82	3.590	91.19	3.515	89.28	1	INK	

FCIconnect.com

Copyright FCI

mat'l. code

surface
ISO 1302 ✓

tolerance
ISO 406
ISO 1101

projection
INCH/MM

product family
CLINCHER

ltr ecn nodr date

tolerances unless otherwise specified

angles
0°±2'

linear
XXX±.01/XXX±0.3
XXX±.005/XXX±0.13
XXX±.0020/XXX±0.051

dr T. BRUNGARD 4/17/03

engr H. SUNDY 4/17/03

chr H. SUNDY 4/17/03

appd H. SUNDY 4/17/03

sheet index

revision sheet

scale 1:1

FCI

title
LATCHING CLINCHER™
RECEPTACLE ASSEMBLY

dwg no 10022753

sheet 5 of 6

size A3

type Product Customer Drawing

1

2

3

4

5

6

Form: A3

PDS: Rev :F

STATUS: Released

Printed: Mar 07, 2012

1

2

3

4

5

6

PRODUCT NO.	NO. OF	DIM. L	DIM. L	DIM. M	DIM. M	DIM. C	DIM. C	PLATING	TERMINATION	
NOTE 7	POSITIONS	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	CODE	NOTE 6	
10022753-139	6	0.500	12.70	0.790	20.07	0.715	18.16	2	INK	
10022753-140	7	0.600	15.24	0.890	22.61	0.815	20.70	2	INK	
10022753-141	8	0.700	17.78	0.990	25.15	0.915	23.24	2	INK	
10022753-142	9	0.800	20.32	1.090	27.69	1.015	25.78	2	INK	
10022753-143	10	0.900	22.86	1.190	30.23	1.115	28.32	2	INK	
10022753-144	11	1.000	25.40	1.290	32.77	1.215	30.86	2	INK	
10022753-145	12	1.100	27.94	1.390	35.31	1.315	33.40	2	INK	
10022753-146	13	1.200	30.48	1.490	37.85	1.415	35.94	2	INK	
10022753-147	14	1.300	33.02	1.590	40.39	1.515	38.48	2	INK	
10022753-148	15	1.400	35.56	1.690	42.93	1.615	41.02	2	INK	
10022753-149	16	1.500	38.10	1.790	45.47	1.715	43.56	2	INK	
10022753-150	17	1.600	40.64	1.890	48.01	1.815	46.10	2	INK	
10022753-151	18	1.700	43.18	1.990	50.55	1.915	48.64	2	INK	
10022753-152	19	1.800	45.72	2.090	53.09	2.015	51.18	2	INK	
10022753-153	20	1.900	48.26	2.190	55.63	2.115	53.72	2	INK	
10022753-154	21	2.000	50.80	2.290	58.17	2.215	56.26	2	INK	
10022753-155	22	2.100	53.34	2.390	60.71	2.315	58.80	2	INK	
10022753-156	23	2.200	55.88	2.490	63.25	2.415	61.34	2	INK	
10022753-157	24	2.300	58.42	2.590	65.79	2.515	63.88	2	INK	
10022753-158	25	2.400	60.96	2.690	68.33	2.615	66.42	2	INK	
10022753-159	26	2.500	63.50	2.790	70.87	2.715	68.96	2	INK	
10022753-160	27	2.600	66.04	2.890	73.41	2.815	71.50	2	INK	
10022753-161	28	2.700	68.58	2.990	75.95	2.915	74.04	2	INK	
10022753-162	29	2.800	71.12	3.090	78.49	3.015	76.58	2	INK	
10022753-163	30	2.900	73.66	3.190	81.03	3.115	79.12	2	INK	
10022753-164	31	3.000	76.20	3.290	83.57	3.215	81.66	2	INK	
10022753-165	32	3.100	78.74	3.390	86.11	3.315	84.20	2	INK	
10022753-166	33	3.200	81.28	3.490	88.65	3.415	86.74	2	INK	
10022753-167	34	3.300	83.82	3.590	91.19	3.515	89.28	2	INK	

FCIconnect.com

Copyright FCI

mat'l. code

surface

ISO 1302

tolerance

ISO 406

ISO 1101

projection

product family

CLINCHER

title

LATCHING CLINCHER™

RECEPTACLE ASSEMBLY

dwg no

10022753

sheet 6 of 6

size

A3

type

Product Customer Drawing

sheet index

revision sheet

scale 1:1

FCI

1

2

3

4

5

6

PDS: Rev :F

STATUS: Released

Printed: Mar 07, 2012