

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0919991254

Status:

Active

Overview:

RAST 5 Connector System

Description:

Appli-Mate RAST 5 Header, Vertical, 4 Circuits, Tin (Sn) Plating, Glow-Wire Capable

Documents:

3D Model (PDF)

3D Model

Drawing (PDF)

Product Specification PS-99020-0037-001 (PDF)

Packaging Specification PK-90858-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

91999

Application

Power, Wire-to-Board

Comments

""""""""This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options. """"""""

Overview

RAST 5 Connector System

Product Name

RAST 5

UPC

800756829685

Physical

Breakaway

No

Circuits (Loaded)

4

Circuits (maximum)

4

Color - Resin

Natural

Durability (mating cycles max)

10

First Mate / Last Break

No

Flammability

94V-0

Glow-Wire Capable

Yes

Guide to Mating Part

No

Keying to Mating Part

Yes

Lock to Mating Part

Yes

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination


Nickel

Material - Resin

Nylon

Net Weight

4.374/g



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

91999 Series

Mates With

Appli-Mate RAST 5 IDT Housing [91778](#) ,
[91779](#)

Use With

RAST Standard Interface

Number of Rows	1
Orientation	Vertical
PC Tail Length	3.90mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.40mm
Packaging Type	Bag
Pitch - Mating Interface	5.00mm
Pitch - Termination Interface	5.00mm
Plating min - Mating	5.080µm
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-20° to +120°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	16.0A
Voltage - Maximum	250V AC
Material Info	
Engineering Number	WITH ZYTEL RM
Reference - Drawing Numbers	
Packaging Specification	PK-90858-001-001
Product Specification	PS-99020-0037-001

This document was generated on 07/17/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION