

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2006.

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DW

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

G

REVISED PER ECR-16-003830

14MAR16

FL

SY

8.7	GEN II & GEN III		2.30	71.35	70	73.15	89	71.65	164	BLACK	30u"	4-1734774-8
5.45				38.35	37	40.15	56	38.65	98	WHITE		4-1734774-7
3.85				21.35	20	23.15	39	21.65	64	BLACK		4-1734774-6
2.55				7.35	6	9.15	25	7.65	36	WHITE		4-1734774-5
8.7				71.35	70	73.15	89	71.65	164	BLACK		4-1734774-4
										WHITE		4-1734774-3
5.45				38.35	37	40.15	56	38.65	98	BLACK	4-1734774-2	
										WHITE	4-1734774-1	
3.85				21.35	20	23.15	39	21.65	64	BLACK	15u"	
										WHITE	G/F	
2.55				7.35	6	9.15	25	7.65	36	BLACK	15u"	
										WHITE	G/F	
8.7				71.35	70	73.15	89	71.65	164	BLACK	15u"	
										WHITE	G/F	
5.45				38.35	37	40.15	56	38.65	98	BLACK	15u"	
										WHITE	G/F	
3.85	21.35	20	23.15	39	21.65	64	BLACK	15u"				
							WHITE	G/F				
2.55	7.35	6	9.15	25	7.65	36	BLACK	15u"				
							WHITE	G/F				
8.7	71.35	70	73.15	89	71.65	164	BLACK	15u"				
							WHITE	G/F				
5.45	38.35	37	40.15	56	38.65	98	BLACK	15u"				
							WHITE	G/F				
3.85	21.35	20	23.15	39	21.65	64	BLACK	15u"				
							WHITE	G/F				
2.55	7.35	6	9.15	25	7.65	36	BLACK	15u"				
							WHITE	G/F				
WEIGHT(g)	PCI-E COMPLIANCE	HOUSING MATERIAL	DIM. L	DIM. E	DIM. D	DIM. C	DIM. B	DIM. A	POS.	HOUSING COLOR	MIN. GOLD THICKNESS	PART NUMBER

8.8	GEN II	PA46	2.30	71.35	70	73.15	89	71.65	164	BLACK	30u"	9-1734774-7
5.5				38.35	37	40.15	56	38.65	98	WHITE		9-1734774-6
3.9				21.35	20	23.15	39	21.65	64	BLACK		9-1734774-5
2.55				7.35	6	9.15	25	7.65	36	WHITE		9-1734774-4
8.8				71.35	70	73.15	89	71.65	164	BLACK		9-1734774-3
										WHITE		9-1734774-2
5.5				38.35	37	40.15	56	38.65	98	BLACK	9-1734774-1	
										WHITE	9-1734774-0	
3.9				21.35	20	23.15	39	21.65	64	BLACK	15u"	
										WHITE	G/F	
2.55				7.35	6	9.15	25	7.65	36	BLACK	15u"	
										WHITE	G/F	
8.8				71.35	70	73.15	89	71.65	164	BLACK	15u"	
										WHITE	G/F	
5.5				38.35	37	40.15	56	38.65	98	BLACK	15u"	
										WHITE	G/F	
3.9	21.35	20	23.15	39	21.65	64	BLACK	15u"				
							WHITE	G/F				
2.55	7.35	6	9.15	25	7.65	36	BLACK	15u"				
							WHITE	G/F				
8.8	71.35	70	73.15	89	71.65	164	BLACK	15u"				
							WHITE	G/F				
5.5	38.35	37	40.15	56	38.65	98	BLACK	15u"				
							WHITE	G/F				
3.9	21.35	20	23.15	39	21.65	64	BLACK	15u"				
							WHITE	G/F				
2.55	7.35	6	9.15	25	7.65	36	BLACK	15u"				
							WHITE	G/F				
WEIGHT(g)	PCI-E COMPLIANCE	HOUSING MATERIAL	DIM. L	DIM. E	DIM. D	DIM. C	DIM. B	DIM. A	POS.	HOUSING COLOR	MIN. GOLD THICKNESS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± 0.3

2 PLC ± 0.2

3 PLC ± 0.15

4 PLC ± -

ANGLES ± 3°

FINISH

MATERIAL

DWN

B. HSING

15JUL2009

CHK

S. CHIEN

15JUL2009

APVD

W. KODAMA

15JUL2009

PRODUCT SPEC

108-57871

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME

PCI EXPRESS CARD EDGE CONNECTOR
VERTICAL, DIP TYPE, 3GIO

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

©-1734774

SCALE

SHEET

1 OF 5

REV

G

AMP 1470-19 REV 31MAR2000

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2006.



COPYRIGHT

-

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

NOTES:

1. MATERIAL:

1.1 HOUSING: 1.PA46 WITH 40% G.F, UL94 V-0, COLOR: SEE TABLE.

2.PA9T WITH 30% GF, UL94 V-0, COLOR: SEE TABLE.

1.2 CONTACT: PHOSPHOR BRONZE

2. FINISH:

CONTACT: (SEE TABLE) GOLD PLATING ON CONTACT AREA.

2.54um [100u"] MIN. MATTE-TIN PALTING ON SOLDER TAIL AREA.

1.27um [50u"] MIN. NICKEL UNDERPLATING OVERALL.

3. CONNECTOR HAS MET THE REQUIREMENTS






PER PCI EXPRESS GEN 2 TECHNICAL DOCUMENT.

4. WEIGHT:


36 POS.: 2.55 GRAMS; 64 POS.: 3.90 GRAMS

98 POS.: 5.50 GRAMS; 164 POS.: 8.80 GRAMS

5. WAVE SOLDER CAPABLE TO 265°C PER TEST SPEC. 109-202 CONDITION B.

6. REFLOW SOLDER CAPABLE TO 260°C PER TEST SPEC. 109-201 CONDITION B.
(REFLOW SOLDERING PLEASE USE PN : 1734774-1 TO 4-1734774-8)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

MATERIAL

SEE NOTE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± 0.3
2 PLC ± 0.2
3 PLC ± 0.15
4 PLC ± -
ANGLES ± 3°

FINISH

SEE NOTE

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

PCI EXPRESS CARD EDGE CONNECTOR
VERTICAL, DIP TYPE, 3GIO

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1734774

SCALE

SHEET

2 OF 5

REV

G

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2006.


© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
DW		P	LTR	DESCRIPTION	DATE	APVD
				SEE SHEET 1.		


D

D



PN X-1 TO 4-X-8
(PA9T TYPE)


36 POS.




PN 5-X-0 TO 9-X-7
(PA46 TYPE)

C

C




64 POS.




B

B




98 POS.




A

A



164 POS.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		TE Connectivity	
		CHK			
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± -		PRODUCT SPEC	
		1 PLC ± 0.25		APPLICATION SPEC	
MATERIAL		2 PLC ± 0.25		WEIGHT	
		3 PLC ± 0.25		CUSTOMER DRAWING	
FINISH		4 PLC ± -		SIZE	
		ANGLES ± -		CAGE CODE	
				DRAWING NO	
				RESTRICTED TO	
				A300779C=1734774	
				SCALE	
				SHEET 3 OF 5	
				REV G	

4

3

2

1

LOC	DIST	REVISIONS				
DW		P	LTR	DESCRIPTION	DATE	DWN
				SEE SHEET 1.		
						APVD

D

D

C


C

B

B

A

A




RECOMMENDED PCB LAYOUT

TOLERANCE: ±0.05
FOR DIM.L=3.1mm PCB THICKNESS: 2.4mm
FOR DIM.L=2.3mm PCB THICKNESS: 1.6mm

ADD-IN CARD EDGE-FINGER DIMENSIONS

NOTES:
CHAMFER EDGE MUST BE FREE OF CUTTING BURRS



164	70.0	73.15	72.15	A1, B17, B31, B48, B81
98	37.0	40.15	39.15	A1, B17, B31, B48
64	20.0	23.15	22.15	A1, B17, B31
36	6.0	9.15	8.15	A1, B17
POS.	DIM. F	DIM. G	DIM. H	"K"

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity		
		CHK			
		APVD	NAME		
		PRODUCT SPEC	PCI EXPRESS CARD EDGE CONNECTOR VERTICAL, DIP TYPE, 3GIO		
		APPLICATION SPEC			
		WEIGHT	SIZE	CAGE CODE	DRAWING NO
		CUSTOMER DRAWING	A3	00779	C=1734774
			SCALE	SHEET	REV
				4 OF 5	G



4

3


2

1

LOC	DIST	REVISIONS					
DW	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1.			



- NOTES :
- MATERIAL :
TRAY : PVC, COLOR: TRANSPARENT.
CARTON: CORRUGATED FIBER
BOX: CORRUGATED FIBER
 - DIMENSION :
TRAY: SEE DRAWING
CARTON: SEE DRAWING
BOX : SEE DRAWING
 - QUANTITY : SEE TABLE
 - WEIGHT : SEE TABLE



10.2 Kg	8.2 Kg	30	10	3	900	164
9.0 Kg	7.0 Kg	40	10	3	1200	98
8.5 Kg	6.5 Kg	60	10	3	1800	64
7.6 Kg	5.6 Kg	70	10	3	2100	36
GROSS WEIGHT	NET WEIGHT	PCS/ TRAY	TRAY/ CARTON	CARTON/ BOX	PCS/ BOX	POS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity			
		CHK				
		APVD				
		PRODUCT SPEC				
DIMENSIONS: MM		APPLICATION SPEC		NAME		
		WEIGHT		SIZE		
MATERIAL		CUSTOMER DRAWING		CAGE CODE		
				DRAWING NO		
				RESTRICTED TO		
				SCALE		
				SHEET 5 OF 5		
				REV G		