

# NOTES:

±.001

① MAT'L: COPPER(STOCK TKN. 040 )


PLATING: ELECTRO-TIN(.0003 MIN.)  
② INSULATION: MOLDED PVC (YELLOW)

STUD SIZES:(±.005)

02 = .094  
04 = .119  
06 = .146  
08 = .173  
10 = .198  
14 = .265  
56 = .328  
38 = .390

"UL" LISTING #E32244  
"CSA" LISTING #18689

ALL DIMENSIONS =  $\frac{\text{INCHES}}{\text{MM}}$



MWID = MAXIMUM WIRE  
INSULATION DIAMETER  
WIRE SIZE: 12-10AWG  
40-60MM²

FILE NO.

C-CD-203-01

REV. ADDED 8X, 10X TO

A CHART UNDER PART#

C-2105 7670688 1/31/88

PART  
NUMBER

"W"  
±.010

"C"  
MIN.

"L"  
MAX.

AVAILABLE  
STUD SIZES

C-2102-

$\frac{415}{10.54}$

$\frac{305}{7.75}$

$\frac{1.075}{27.31}$

08X

C-2105-

$\frac{320}{8.13}$

$\frac{305}{7.75}$

$\frac{1.075}{27.31}$

06X, 08X, 10X

DIMENSIONAL TOLERANCES  
UNLESS OTHERWISE SPECIFIED

REFERENCE

SCALE:

NTS

DATE

TITLE

SPADE TONGUE  
TERMINAL

ETC  
INCORPORATED

FRAC. DEC. ANG.

CHKD. BY: GZ

APPRD. BY:

DWG.

A.

CUSTOMER  
DWG.