



DUAL-IN-LINE SOCKETS


SERIES 146 • SOLDERLESS PRESS-FIT, COMPLIANT TAIL • OPEN FRAME



- Unique compliant tail pins conform to a $.040" \pm .003"$ finished plated through hole diameter without stressing inner layers
- Two tails lengths are offered for .060"-.100" and .090"-.130" thick panels
- Series 146 uses MM #4612 or MM #4613 pins with a BeCu #30 contact, rated at 3 amps. See page 162 for details
- Insulators are high temperature thermoplastic
- For Electrical, Mechanical and Environmental Data, see page 264 for details




APPLICATION OF COMPLIANT TAIL PINS



Mill-Max's patented* precision-machined pins feature compliant tails that are hollow and slotted to conform to a $.040" \pm .003"$ diameter PTH. As the pin is inserted, the slot compresses to fit the PTH, thus avoiding damage (see illustration at left). The pin's tail has fine serrations that form a perfect "gas tight" connection that doesn't require soldering. And since the pin doesn't damage the hole, compliant tail sockets and connectors can be easily replaced.

*Patent No. 4,799,904.

Total number of pins				Quantity per tube	ORDERING INFORMATION								
	A	B	C		L = .120 (for .060"-.100" thick panel)	L = .175 (for .090"-.130" thick panel)							
6	0.3	0.3	0.4	67	146-XX-306-41-012000	146-XX-306-41-013000	 						
8	0.4	0.3	0.4	50	146-XX-308-41-012000	146-XX-308-41-013000							
14	0.7	0.3	0.4	28	146-XX-314-41-012000	146-XX-314-41-013000							
16	0.8	0.3	0.4	25	146-XX-316-41-012000	146-XX-316-41-013000							
18	0.9	0.3	0.4	22	146-XX-318-41-012000	146-XX-318-41-013000							
20	1.0	0.3	0.4	20	146-XX-320-41-012000	146-XX-320-41-013000							
24	1.2	0.3	0.4	16	146-XX-324-41-012000	146-XX-324-41-013000							
22	1.1	0.4	0.5	18	146-XX-422-41-012000	146-XX-422-41-013000							
24	1.2	0.6	0.7	16	146-XX-624-41-012000	146-XX-624-41-013000							
28	1.4	0.6	0.7	14	146-XX-628-41-012000	146-XX-628-41-013000							
32	1.6	0.6	0.7	12	146-XX-632-41-012000	146-XX-632-41-013000							
40	2.0	0.6	0.7	10	146-XX-640-41-012000	146-XX-640-41-013000							
SPECIFY PLATING CODE XX =						91		93		41 	43 		
Sleeve (Pin) 						200 μ" Sn/Pb		200 μ" Sn/Pb		200 μ" Sn	200 μ" Sn		
Contact (Clip) 						10 μ" Au		30 μ" Au		10 μ" Au	30 μ" Au		

