





Copyright FCI.




spec ref -				dr	Bill Lin	2010/02/02	projection 	mm 	size	A4	scale	21:10	
tolerance std ASME Y14.5 -	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Nickor Zuo	2011/06/21			ecn no				ELX-DG-003943-1
				chr	Alex Cao	2011/06/24			rel level				Released
				appr	Pei-Ming Zheng	2011/06/27			product family				GIG-Array
surface ✓ -	linear	0.X	±0.30		title GIG-Array - 5mm RECEPTACLE ASSY. 200 SIG. POS.				dwg no	10069344		rev D	
		0.XX	±0.10										
		0.XXX	±0.05										
	angular	0°	±2°	www.fci.com	cat. no.					Product - Customer Drw			sheet 2 of 5

PrintE File - REV C - 2009-06-09




Copyright FCI.




RECEPTACLE INTERFACE
DESCRIPTION


SCALE 6:1

spec ref -				dr Bill Lin 2010/02/02		projection 	mm 	size A4	scale 21:10	
tolerance std ASME Y14.5 -	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng Nickor Zuo 2011/06/21				ecn no ELX-DG-003943-1		
				chr Alex Cao 2011/06/24				rel level Released		
				appr Pei-Ming Zheng 2011/06/27						
surface 	linear	0.X	±0.30		title GIG-Array - 5mm RECEPTACLE ASSY. 200 SIG. POS.			dwg no 10069344	rev D	
		0.XX	±0.10							
		0.XXX	±0.05							
	angular	0°	±2°							www.fci.com

**FLAT AREA
FOR PICK-UP CAP**
SCALE 2:1



DIM "A" REF.
MATED HEIGHT
AFTER REFLOW
SEE NOTE 3.



END VIEW OF MATED CONNECTORS
SCALE 2:1

DIM. "A"	PLUG ASSEMBLY P/N
15	55737
17	10026802
18	10055142
20	55738
25	55739
30	10054783

spec ref		-		dr	Bill Lin	2010/02/02	projection 	mm 	size	A4	scale	11:10	
tolerance std ASME Y14.5 -	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Nickor Zuo	2011/06/21			ecn no		ELX-DG-003943-1		
				chr	Alex Cao	2011/06/24			rel level				Released
				appr	Pei-Ming Zheng	2011/06/27			product family		GIG-Array		
surface ✓ -	linear	0.X	±0.30		title GIG-Array - 5mm RECEPTACLE ASSY. 200 SIG. POS.				dwg no	10069344		rev D	
		0.XX	±0.10										
		0.XXX	±0.05										
	angular	0°	±2°	www.fci.com	cat. no.		Product - Customer Drw			sheet 4 of 5			

PRODUCT NUMBER	SOLDER BALL COMPOSITION	CONTACT PLATING PERFORMANCE LEVEL
10069344-001	STANDARD (EUTECTIC)	PERFORMANCE-BASED PLATING, QUALIFIED TO MEET THE REQUIREMENTS OF FCI PRODUCT SPECIFICATION GS-12-192, INCLUDING TELCORDIA CENTRAL OFFICE
10069344-001LF	LEADFREE	
10069344-201	STANDARD (EUTECTIC)	
10069344-201LF	LEADFREE	

NOTES:

① MATERIAL:

HOUSING: LCP
CONTACT: COPPER ALLOY
PLATING (CONTACT): Au OVER Ni.
UL RATING: 94 V-0
SOLDERBALL: (SEE TABLE) EUTECTIC
SnPb OR LEAD FREE 95.5 Sn/4Ag/0.5Cu.

② SOLDER BALLS WILL NOT BE PERFECT
SPHERICAL SHAPE DUE TO REFLOW ATTACHMENT.

③ MATED HEIGHT EFFECTED BY CUSTOMERS' PCB PAD SIZE, PLATING, SOLDER REFLOW PROFILE & SOLDER PASTE.

④ CONTACTS IN ROWS A,C,E,G,J,K,M,P,R AND T ARE SINGLE BEAM CONTACTS USED AS GROUND PINS.
(NOTE: CONTACTS IN ROWS J & K ARE TIED TOGETHER [COMMONED])

⑤ CONTACTS IN ROWS B,D,F,H,L,N,Q AND S ARE DUAL BEAM CONTACTS, TYPICALLY USED AS SIGNAL PINS.

⑥ SPECIFIED POSITIONAL TOLERANCE DEFINES PAD TO PAD LOCATION WITHIN LAND PATTERN. POSITIONAL TOLERANCE OF LAND PATTERN TO FUDICIAL MARKS OR PCB DATUMS SHALL BE DEFINED BY CUSTOMER. FOR RECOMMENDED PRODUCT APPLICATION AND PCB DESIGN DETAILS, SEE DOC. NO. GS-20-016.

⑦ FOR PROPER APPLICATION FOLLOW FCI APPLICATION SPECIFICATION GS-20-033. LEAD FREE SOLDER BALLS WILL NOT SOLDER PROPERLY IN A LEADED SOLDER PROCESS DUE TO A HIGHER REFLOW TEMPERATURE. LEADFREE PRODUCT IS THEREFORE NOT BACKWARDS COMPATIBLE WITH LEADED OR SOME SOLDERING APPLICATIONS. REFERENCE FCI APPLICATION SPECIFICATION.

⑧ THIS PRODUCT MEETS THE EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008. PRODUCT MEETING THIS DIRECTIVE IS IDENTIFIED IN THE CODE NUMBER MARKED ON EACH PART BY HAVING AN "X" IN THE SEVENTH CHARACTER POSITION.

spec ref -				dr Bill Lin		2010/02/02		projection				size A4		scale 21:10	
tolerance std ASME Y14.5 - TOLERANCES UNLESS OTHERWISE SPECIFIED				eng Nickor Zuo		2011/06/21						ecn no ELX-DG-003943-1			
				chr Alex Cao		2011/06/24									
				appr Pei-Ming Zheng		2011/06/27						product family GIG-Array			
				rel level Released											
surface ✓ - linear		0.X		±0.30				title GIG-Array - 5mm RECEPTACLE ASSY. 200 SIG. POS.		dwg no 10069344		rev D			
		0.XX		±0.10											
		0.XXX		±0.05											
		angular 0°		±2°		www.fci.com								cat. no.	