

Features

- Output voltage ranges: Fixed range of 1.8V, 2.5V, 2.85V, 3.3V, 5.0V or adjustable type.
- High accuracy: $\pm 2\%$
- Low voltage drop: 1.1V (typ.), $V_{OUT}=5.0V$ at 1A
- Guaranteed output current: 1A
- Low quiescent current: 8mA (typ.)
- Integrated current limit & thermal protection circuits
- SOT-223 package

Applications

- Active SCSI terminations
- Post regulator for switching power supplies
- Low voltage microcontrollers
- Motherboard clock supplies
- Battery chargers

General Description

The HT1117 devices are a series of three-terminal high current low voltage regulators. They can deliver an output current of 1A and can accept input voltages up to 12V. The devices are available in both adjustable and


fixed output voltage type with a range of 1.8V to 5.0V. Internal current limit and thermal protection circuits provide protection against overload conditions that could create excessive junction temperatures.

Selection Table

Part No.	Output Voltage	Package	Marking
HT1117-ADJ	Adjust	SOT-223	HT1117-ADJ HT1117-18 HT1117-25 HT1117-28 HT1117-33 HT1117-50
HT1117-18	1.8V		
HT1117-25	2.5V		
HT1117-28	2.85V		
HT1117-33	3.3V		
HT1117-50	5.0V		



Note: For lead free devices, a "#" mark is suffixed at the end of the date code.

Block Diagram



Pin Assignment

SOT-223



Absolute Maximum Ratings*

Input Supply Voltage $V_{SS}-0.3V$ to $V_{SS}+13V$ Storage Temperature $-50^{\circ}C$ to $125^{\circ}C$

Note: These are stress ratings only. Stresses exceeding the range specified under "Absolute Maximum Ratings" may cause substantial damage to the device. Functional operation of this device at other conditions beyond those listed in the specification is not implied and prolonged exposure to extreme conditions may affect device reliability.

"**" Absolute maximum ratings indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is intended to be functional, but do not guarantee specific performance limits. The guaranteed specifications apply only for the test conditions listed.

Recommended Operating Conditions

Input Supply Voltage $V_{SS}-0.3V$ to $V_{SS}+12V$ Ambient Temperature $-40^{\circ}C$ to $85^{\circ}C$

Thermal Information

Symbol	Parameter	Package	Max.	Unit
θ_{JA}	Thermal Resistance (Junction to Ambient)	SOT-223	134	$^{\circ}C/W$
P_D	Power Dissipation	SOT-223	0.75	W

Note: P_D is measured at $T_a = 25^{\circ}C$

Electrical Characteristics
 $T_J = 25^{\circ}\text{C}$, $V_{IN} = V_{OUT} + 1.5\text{V}$, $I_O = 10\text{mA}$, unless otherwise specified (see note 1)


Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
V_{REF}	Reference Voltage	$2.75\text{V} \leq V_{IN} \leq 12\text{V}$	1.225	1.250	1.275	V
V_{OUT}	Output Voltage	HT1117-18	1.764	1.800	1.836	V
		HT1117-25	2.45	2.50	2.55	V
		HT1117-28	2.793	2.850	2.907	V
		HT1117-33	3.234	3.300	3.366	V
		HT1117-50	4.90	5.00	5.10	V
ΔV_{LOAD}	Load Regulation (see note 2)	$10\text{mA} \leq I_{OUT} \leq 1\text{A}$	1	—	30	mV
ΔV_{LINE}	Line Regulation	$2.75\text{V} \leq V_{IN} \leq 12\text{V}$	—	0.015	0.150	%/V
V_{DIF}	Dropout Voltage (see note 3)	$\Delta V_{OUT} = 2\%$, $I_{OUT} = 1\text{A}$	—	1.1	1.3	V
I_{LIMIT}	Current Limit (see note 4)	$\Delta V_{OUT} = 10\%$	1	2.3	—	A
I_{ADJ}	Adjust Pin Current (Variable Version)	$2.75\text{V} \leq V_{IN} \leq 12\text{V}$	—	55	120	μA
I_{SS}	Quiescent Current (Fixed Version)	$2.75\text{V} \leq V_{IN} \leq 12\text{V}$	—	8	13	mA
RR	Ripple Rejection	120Hz input ripple $C_{OUT} = 22\mu\text{F}$	—	60	—	dB
$\frac{\Delta V_{OUT}}{\Delta T_a}$	Temperature Coefficient	$-40^{\circ}\text{C} < T_a < 85^{\circ}\text{C}$	—	± 0.4	—	mV/ $^{\circ}\text{C}$

- Note:
- Specifications are production tested at room temperature, T_a . Specifications within the -40°C to 85°C operating temperature range are assured by design, characterization and correlation with Statistical Quality Controls (SQC).
 - Load regulation is measured at a constant junction temperature, using pulse testing with a low ON time and is guaranteed up to the maximum power dissipation. Power dissipation is determined by the input/output differential voltage and the output current. Guaranteed maximum power dissipation will not be available over the full input/output range. The maximum allowable power dissipation at any ambient temperature is $P_D = (T_{J(MAX)} - T_a) / \theta_{JA}$.
 - Dropout voltage is defined as the input voltage minus the output voltage that produces a 2% change in the output voltage from the value at $V_{IN} = V_{OUT} + 1.5\text{V}$ with a fixed load.
 - Current limit is measured by pulsing for a short time.

Application Circuits

Basic Circuits


- Variable voltage type



$$V_{OUT} = V_{REF} \left(1 + \frac{R2}{R1} \right) + I_{ADJ} R2$$

Note: C1 is required if the needed if the device is located far from filter capacitors, the recommended value is 10µF.
C2 is required for stability, the recommended value is 10µF.
R1 is required for regulation, the recommended value is 125Ω.


- Fixed voltage type




Note: C1 is required if the needed if the device is located far from filter capacitors, the recommended value is 10µF.
C2 is required for stability, the recommended value is 10µF.

Typical Application Circuits


- 1.25V~10.5V regulator




- Digitally selected outputs




- High output current positive voltage regulator




- Increased Output voltage Circuit




• Dual Supply Circuit




• Tracking Voltage Regulator




Package Information
3-pin SOT-223 Outline Dimensions


Symbol	Dimensions in mm		
	Min.	Nom.	Max.
A	—	—	1.8
A1	0.02	—	0.10
A2	1.50	—	1.70
b	0.66	—	0.84
C	0.23	—	0.35
D	6.30	—	6.70
E	6.70	—	7.30
E1	3.30	—	3.70
e	—	2.3	—
e1	—	4.6	—
L	0.75	—	—
θ	0°	—	10°

Product Tape and Reel Specifications
Reel Dimensions

SOT-223

Symbol	Description	Dimensions in mm
A	Reel Outer Diameter	330±1
B	Reel Inner Diameter	62±1.5
C	Spindle Hole Diameter	12.75±0.15
D	Key Slit Width	2+0.6
T1	Space Between Flange	12.4+0.2
T2	Reel Thickness	16.4-0.4

Carrier Tape Dimensions

SOT-223

Symbol	Description	Dimensions in mm
W	Carrier Tape Width	12±0.3
P	Cavity Pitch	8±0.1
E	Perforation Position	1.75±0.1
F	Cavity to Perforation (Width Direction)	5.5±0.05
D	Perforation Diameter	1.5+0.1
D1	Cavity Hole Diameter	1.5+0.1
P0	Perforation Pitch	4±0.1
P1	Cavity to Perforation (Length Direction)	2±0.05
A0	Cavity Length	6.9±0.1
B0	Cavity Width	7.5±0.1
K0	Cavity Depth	2.1±0.1
t	Carrier Tape Thickness	0.3±0.05
C	Cover Tape Width	9.3

Holtek Semiconductor Inc. (Headquarters)

No.3, Creation Rd. II, Science Park, Hsinchu, Taiwan
Tel: 886-3-563-1999
Fax: 886-3-563-1189
<http://www.holtek.com.tw>

Holtek Semiconductor Inc. (Taipei Sales Office)

4F-2, No. 3-2, YuanQu St., Nankang Software Park, Taipei 115, Taiwan
Tel: 886-2-2655-7070
Fax: 886-2-2655-7373
Fax: 886-2-2655-7383 (International sales hotline)

Holtek Semiconductor Inc. (Shanghai Sales Office)

7th Floor, Building 2, No.889, Yi Shan Rd., Shanghai, China 200233
Tel: 86-21-6485-5560
Fax: 86-21-6485-0313
<http://www.holtek.com.cn>

Holtek Semiconductor Inc. (Shenzhen Sales Office)

5/F, Unit A, Productivity Building, Cross of Science M 3rd Road and Gaoxin M 2nd Road, Science Park, Nanshan District, Shenzhen, China 518057
Tel: 86-755-8616-9908, 86-755-8616-9308
Fax: 86-755-8616-9722

Holtek Semiconductor Inc. (Beijing Sales Office)

Suite 1721, Jinyu Tower, A129 West Xuan Wu Men Street, Xicheng District, Beijing, China 100031
Tel: 86-10-6641-0030, 86-10-6641-7751, 86-10-6641-7752
Fax: 86-10-6641-0125

Holtek Semiconductor Inc. (Chengdu Sales Office)

709, Building 3, Champagne Plaza, No.97 Dongda Street, Chengdu, Sichuan, China 610016
Tel: 86-28-6653-6590
Fax: 86-28-6653-6591

Holtek Semiconductor (USA), Inc. (North America Sales Office)

46729 Fremont Blvd., Fremont, CA 94538
Tel: 1-510-252-9880
Fax: 1-510-252-9885
<http://www.holtek.com>

Copyright © 2007 by HOLTEK SEMICONDUCTOR INC.

The information appearing in this Data Sheet is believed to be accurate at the time of publication. However, Holtek assumes no responsibility arising from the use of the specifications described. The applications mentioned herein are used solely for the purpose of illustration and Holtek makes no warranty or representation that such applications will be suitable without further modification, nor recommends the use of its products for application that may present a risk to human life due to malfunction or otherwise. Holtek's products are not authorized for use as critical components in life support devices or systems. Holtek reserves the right to alter its products without prior notification. For the most up-to-date information, please visit our web site at <http://www.holtek.com.tw>.