


RECOMMENDED CUTOUT

MOUNTING HOLES
AS REQUIRED




SCI
52-257-004
XXXX - DATE CODE

MARKING:



NOTES:

- 1) VOLTAGE: 250 VAC
- 2) CURRENT: 20 AMPS.
- 3) OPERATING TEMPERATURE: -55°C TO +105°C.
- 4) MATERIAL: BLACK THERMOPLASTIC OR EQUIV.
- 5) SCREW TYPE: #6-32 PHILSLOT HD.
- 6) GROUND PLANE: .032" FLAT WITHIN .012".
- 7) MARKING: 4 PT. CHARACTERS, WHITE INK - CURE @ 65°C, 4Hrs.
- 8) CAPACITANCE: 2000pF MIN/5200pF MAX.
- 9) SEE ROUTING FOR PAKAGING LABELS.
- 10) ALL SHIPPING TRAYS MUST HAVE A LABEL CONTAINING THE FOLLOWING INFORMATION SCI 52-257-004 DATE CODE 250VAC, 20A, 12-22 AWG, UL LOGO/CSA LOGO



TEST SEQUENCE				
STEP 0100	94-1002-00	CAP./D.F.	PASS	FAIL
PER IT 38-0245 CAP: 2000pF TO 5200pF DF. ≤4% MAX COMMENTS: 100%		OPER:		
STEP 0200	94-2005-00	DWV	PASS	FAIL
PER IT 38-0245 DWV: 1500 VAC 25°C 1 MINUTE MINIMUM COMMENTS: 100%		OPER:		
STEP 0300	94-2015-00	I.R.	PASS	FAIL
PER IT 38-0245 IR: 350VDC, 1000 Mohms MIN. 2 MINUTES MAX. COMMENTS: 100%		OPER:		
STEP 0400	94-4033-00	VISUAL/MECH.	PASS	FAIL
PER IT 38-0468 INSPECT DIMENSIONS AND WORKMANSHIP. PER MIL-STD-105, LEVEL II, 1%ACL COMMENTS: 100%		OPER:		

7	6	5	4	3	2	1	0	REV. NO.	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. (MILLIMETERS)	TOLERANCES UNLESS OTHERWISE SPECIFIED Fractions ± 1/64 Dec. .xx± .03 Dec. .xxx± .020 Angles ±0° 30'	FAIRVIEW PENNSYLVANIA
CN 46316-ENG	CN 44747-ENG	CN 201640	CN 201129	CN 200925	CN 199165	CN 181531	CN 180445	CHANGE NOTICE	DD NOT SCALE.	CODE IDENT. NO. OLSP2	SPECTRUM CONTROL INC.
									Description FILTER TERMINAL BLOCK		
									52-257-004		
									Sheet 1 of 1		

Quality Products From The Specialists In Electro-Magnetic Compatibility