

# Thick Film Chip Resistors



## CR63 Series

### Features:

- 1) Rated power 1.0W.
- 2) Nominal resistor values from  $1\Omega$  to  $1M\Omega$ .
- 3) EIA chip size 2512.

### How To Order:

#### CR 63 – 562 J – UE

##### Packaging

B = Bulk (100 pcs/bag)  
UE = 7" Reel/Embossed Plastic Tape (4,000 pcs/reel)

##### Resistance Tolerance

K =  $\pm 10\%$   
J =  $\pm 5\%$

##### Resistance Code

For J and K Tolerances  
3 digit code (E-24)  
2 significant digits plus  
number of zeros  
Examples:  
 $2.2\Omega = 2R2$   
 $10\Omega = 100$   
 $100\Omega = 101$   
 $1k\Omega = 102$



##### Case Size

63 = 2512

##### Style

CR = Chip Resistor

### Dimensions:

|                                                                                     | CR63     |                                   |
|-------------------------------------------------------------------------------------|----------|-----------------------------------|
|  | <b>L</b> | $6.30 \pm 0.20$ (.248 $\pm$ .008) |
|                                                                                     | <b>W</b> | $3.20 \pm 0.20$ (.126 $\pm$ .008) |
|  | <b>T</b> | $0.60 \pm 0.20$ (.024 $\pm$ .008) |
|                                                                                     | <b>C</b> | $0.45 \pm 0.20$ (.018 $\pm$ .008) |
|                                                                                     | <b>D</b> | $0.45 \pm 0.20$ (.018 $\pm$ .008) |

mm (inches)

### Chip Resistor Ratings

| Spec \ Style               | CR63 (2512)                                 |                     |
|----------------------------|---------------------------------------------|---------------------|
| <b>Power</b>               | 1.0W                                        |                     |
| <b>Voltage</b>             | 200V max.                                   |                     |
| <b>Tolerance</b>           | J<br>( $\pm 5\%$ )                          | K<br>( $\pm 10\%$ ) |
| <b>Value Range</b>         | $1.0\Omega$<br>1 $M\Omega$                  |                     |
| <b>Working Temperature</b> | $-55^\circ\text{C} \sim +125^\circ\text{C}$ |                     |

### Marking

Marking available as follows:

Series: CR63


3 digit indication

Example: 473 =  $47 \times 10^3 = 47000\Omega = 47k\Omega$

100 :  $10\Omega$


102 :  $1k\Omega$

105 :  $1M\Omega$



### Derating Curve

Under high temperature, power must not exceed derating curve.



## Specifications and Test Methods for Chip Resistors and Arrays

### Mechanical Characteristics

| Item                         |                   | Specification                                        |                    | Test Method                                                                                                                                                                                                                                                      |
|------------------------------|-------------------|------------------------------------------------------|--------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                              |                   |                                                      | Jumpers            |                                                                                                                                                                                                                                                                  |
| Terminal Strength            | $\Delta R/R$      | $\leq \pm (1\% + 0.05\Omega)$ of initial value       | $R \leq 50m\Omega$ | Apply the load as shown:<br>Measure resistance during load application.<br>PC board: glass-epoxy (T=1.6M)<br>CR/CJ32: 3mm<br>CR/CJ21: 3mm<br>CR/CJ10: 3mm<br>CR/CJ05: 3mm<br> |
|                              | Visual            | No evidence of mechanical damage after loading       |                    |                                                                                                                                                                                                                                                                  |
|                              | Breaking strength | Lead Pull > 0.5kg                                    |                    | <br>Except for CRA, CR05                                                                                                                                                      |
| Resistance to Soldering Heat | $\Delta R/R$      | $\leq \pm (1 + 0.05\Omega)$ of the initial value     |                    | Immerse into molten solder at $260\pm 5^{\circ}\text{C}$ for $10\pm 1$ sec.<br>Stabilize at room temperature for 60 min.<br>Measure resistance.                                                                                                                  |
|                              | Visual            | Visual: no evidence of leaching                      |                    |                                                                                                                                                                                                                                                                  |
| Solderability                |                   | Coverage $\geq 95\%$ Each termination end            |                    | Immerse for $2 \pm 0.5$ sec. in Sn62 solder at $235 \pm 5^{\circ}\text{C}$                                                                                                                                                                                       |
| Anti-vibration Test          | $\Delta R/R$      | $\leq \pm (1\% + 0.1\Omega)$ of the initial value    | $R \leq 50m\Omega$ | 2 hrs. each in x, y and z axis.<br>(total 6 hrs.)<br>10 to 55Hz sweep in 1 min at 1.5mm amplitude.                                                                                                                                                               |
|                              | Visual            | No evidence of mechanical damage                     |                    |                                                                                                                                                                                                                                                                  |
| Solvent Resistance           | $\Delta R/R$      | $\leq \pm (0.5\% + 0.05\Omega)$ of the initial value | $R \leq 50m\Omega$ | Immerse in static state trichloroethylene at $20^{\circ}$ to $25^{\circ}\text{C}$ for $30\pm 5$ sec. Dry in air @ $25^{\circ}\text{C}$ for 30 minutes. Measure resistance.                                                                                       |
|                              | Visual            | No evidence of mechanical damage                     |                    |                                                                                                                                                                                                                                                                  |

### Environmental Characteristics

| Item                              |        | Specification                        |          | Test Method                                                                                                                                                             |
|-----------------------------------|--------|--------------------------------------|----------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                   |        |                                      | Jumpers  |                                                                                                                                                                         |
| Low Temperature Storage           | ΔR/R   | ≤ ± (2% + 0.1Ω) of the initial value | R ≤ 50mΩ | Dwell in -65°C chamber without loading for 1000 +48/-0 hrs<br>Stabilize at room temperature for 60 min.<br>Measure resistance value.                                    |
|                                   | Visual | No evidence of mechanical damage     |          |                                                                                                                                                                         |
| High Temperature Exposure         | ΔR/R   | ≤±(3% + 0.1Ω) of the initial value   | R ≤ 50mΩ | Dwell in 125°C chamber for 1,000 +48/-0 hrs. without loading.<br>Stabilize at room temperature for 60 minutes.<br>Measure resistance value                              |
|                                   | Visual | No evidence of mechanical damage     |          |                                                                                                                                                                         |
| Temperature Cycle                 | ΔR/R   | ≤±(1%+0.05Ω) of the initial value    | R ≤ 50mΩ | ① Perform 5 cycles as follows: -55±3°C for 30 min. →room temp. for 10~15 min. ⇄125±3° for 30 min.<br>② Stabilize at room temperature for 1 hr, then measure value.      |
|                                   | Visual | No evidence of mechanical damage     |          |                                                                                                                                                                         |
| Moisture Resistance               | ΔR/R   | ≤±(3% + 0.1Ω) of the initial value   | R ≤ 50mΩ | Dwell in test chamber at +65°C, and 90-95% RH for 1000 +48/-0 hours<br>Stabilize at room temperature for 60 min.<br>Measure resistance value.                           |
|                                   | Visual | No evidence of mechanical damage     |          |                                                                                                                                                                         |
| Salt Spray                        | ΔR/R   | ≤±(3%+0.1Ω) of the initial value     | R ≤ 50mΩ | Dwell in temp. 35±2°C<br>Salt density 5% for 24 ±2 hrs.                                                                                                                 |
|                                   | Visual | No evidence of mechanical damage     |          |                                                                                                                                                                         |
| Voltage Cycle in High Temperature | ΔR/R   | ≤±(3% + 0.1Ω) of the initial value   | R ≤ 50mΩ | ① Perform 1,000 +48/-0 hrs. in chamber (70±3°C) ON: 90 min. at rated voltage; OFF: 30 min.<br>② Stabilize at room temperature for 1 hr., then measure value.            |
|                                   | Visual | No evidence of mechanical damage     |          |                                                                                                                                                                         |
| Voltage Cycle in High Humidity    | ΔR/R   | ≤±(3% + 0.1Ω) of the initial value   | R ≤ 50mΩ | ① Perform 1,000 +48/-0 hrs. in chamber (40 ±2°C, 90~95%RH) ON: 90 min. at rated voltage; OFF: 30 min.<br>② Stabilize at room temperature for 1 hr., then measure value. |
|                                   | Visual | No evidence of mechanical damage     |          |                                                                                                                                                                         |

## Specifications and Test Methods for Chip Resistors and Arrays

### Electrical Characteristics

| Item                                  |        | Specification                                                                                                                                                 |                                                                                                                                                               | Test Method                                                                                                                                                                                                                                                                                                                                        |                               |
|---------------------------------------|--------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------|
|                                       |        |                                                                                                                                                               | Jumpers                                                                                                                                                       |                                                                                                                                                                                                                                                                                                                                                    |                               |
| DC Resistance                         |        | Within initial tolerance                                                                                                                                      | R≤50mΩ                                                                                                                                                        | Test Voltage                                                                                                                                                                                                                                                                                                                                       | (20°C, 65% RH)                |
|                                       |        |                                                                                                                                                               |                                                                                                                                                               | Range of resistance (Ω)                                                                                                                                                                                                                                                                                                                            | Maximum voltage to be applied |
|                                       |        |                                                                                                                                                               |                                                                                                                                                               | R<10                                                                                                                                                                                                                                                                                                                                               | 0.1 (V)                       |
|                                       |        |                                                                                                                                                               |                                                                                                                                                               | 10≤R<100                                                                                                                                                                                                                                                                                                                                           | 0.3 (V)                       |
|                                       |        |                                                                                                                                                               |                                                                                                                                                               | 100≤R<1K                                                                                                                                                                                                                                                                                                                                           | 1.0                           |
|                                       |        |                                                                                                                                                               |                                                                                                                                                               | 1K≤R<10K                                                                                                                                                                                                                                                                                                                                           | 3                             |
|                                       |        |                                                                                                                                                               |                                                                                                                                                               | 10K≤R<100K                                                                                                                                                                                                                                                                                                                                         | 10                            |
|                                       |        |                                                                                                                                                               |                                                                                                                                                               | 100K≤R<1M                                                                                                                                                                                                                                                                                                                                          | 35                            |
|                                       |        |                                                                                                                                                               |                                                                                                                                                               | 1M≤R                                                                                                                                                                                                                                                                                                                                               | 50                            |
| Resistance Temperature Characteristic |        | CR Series<br>See Page 2<br><br>CRA Series<br>See Page 6                                                                                                       |                                                                                                                                                               | Test temperature: - 55°C ~ 125°C<br><br>$\Delta R/R = \frac{R_2 - R_1}{R_1} \times \frac{1}{T_2 - T_1} \times 10^6$<br><br>$\Delta R/R$ : Temp. coefficient (ppm/°C)<br>T <sub>1</sub> : 25 °C<br>T <sub>2</sub> : 125 °C<br>R <sub>1</sub> : Resistance at T1 (Ω)<br>R <sub>2</sub> : Resistance at T2 (Ω)                                        |                               |
|                                       |        |                                                                                                                                                               |                                                                                                                                                               |                                                                                                                                                                                                                                                                                                                                                    |                               |
| Short-time Overload                   | ΔR/R   | ≤± (2.0% + 0.1Ω)<br>of the initial value                                                                                                                      | R ≤50mΩ                                                                                                                                                       | <div>① Apply 2.5 x rated voltage (rated current: Jumper Chip) for 5 sec.</div> <div>② Wait 30 minutes</div> <div>③ Measure resistance</div> <div><div>CR32: 400V Max</div><div>CR21: 200V Max</div><div>CR10: 100V Max</div><div>CR05: 50V Max</div><div>CRA: 50V Max</div></div>                                                                  |                               |
|                                       | Visual | No evidence of mechanical damage                                                                                                                              |                                                                                                                                                               |                                                                                                                                                                                                                                                                                                                                                    |                               |
| Intermittent Overload                 | ΔR/R   | ≤± (5% + 0.1Ω) of the<br>of the initial value                                                                                                                 | R ≤50mΩ                                                                                                                                                       | <div>① Perform 10000 voltage cycles as follows<br/>ON (2.5 x rated voltage or current ) 1 sec.<br/>OFF 25 sec.</div> <div>② Stabilization time 30 min. without loading</div> <div>③ Measure resistance</div> <div><div>CR32: 400V Max</div><div>CR21: 200V Max</div><div>CR10: 100V Max</div><div>CR05: 50V Max</div><div>CRA: 50V Max</div></div> |                               |
|                                       | Visual | No evidence of mechanical damage                                                                                                                              |                                                                                                                                                               |                                                                                                                                                                                                                                                                                                                                                    |                               |
| Dielectric Withstanding Voltage       |        | No evidence of mechanical damage                                                                                                                              |                                                                                                                                                               | For CR32 & CR21 apply 500VAC for 1 min.<br>For CRA and CR05 apply 300VAC for 1 sec.<br>For CR10 apply 300VAC for 1 min.                                                                                                                                                                                                                            |                               |
| Insulation Resistance                 |        | •CR05: 10 <sup>8</sup> Ω Min<br>•CR10: 10 <sup>9</sup> Ω Min<br>•CR21: 10 <sup>10</sup> Ω Min<br>•CR32: 10 <sup>12</sup> Ω Min<br>•CRA: 10 <sup>9</sup> Ω Min | •CJ05: 10 <sup>8</sup> Ω Min<br>•CJ10: 10 <sup>9</sup> Ω Min<br>•CJ21: 10 <sup>10</sup> Ω Min<br>•CJ32: 10 <sup>12</sup> Ω Min<br>•CJA: 10 <sup>9</sup> Ω Min | For CR32, CR21, CR10<br>CJ32, CJ21, CJ10 apply 500VDC<br>For CRA, CR05<br>CJA, CJ05 apply 100VDC                                                                                                                                                                                                                                                   |                               |
| Noise Level                           |        | Resistance                                                                                                                                                    | Noise                                                                                                                                                         | Refer to JIS C5202 5.9 Measurement<br>method of noise level<br>Except CR05, CRA                                                                                                                                                                                                                                                                    |                               |
|                                       |        | R<100Ω                                                                                                                                                        | -10dB (0.32μV/V)                                                                                                                                              |                                                                                                                                                                                                                                                                                                                                                    |                               |
|                                       |        | 100Ω≤R<1KΩ                                                                                                                                                    | 0dB (1.0μV/V)                                                                                                                                                 |                                                                                                                                                                                                                                                                                                                                                    |                               |
|                                       |        | 1KΩ≤R<10KΩ                                                                                                                                                    | 10dB (3.2μV/V)                                                                                                                                                |                                                                                                                                                                                                                                                                                                                                                    |                               |
|                                       |        | 10KΩ≤R<100KΩ                                                                                                                                                  | 15dB (5.6μV/V)                                                                                                                                                |                                                                                                                                                                                                                                                                                                                                                    |                               |
|                                       |        | 100KΩ≤R<1MΩ                                                                                                                                                   | 20dB (10μV/V)                                                                                                                                                 |                                                                                                                                                                                                                                                                                                                                                    |                               |
|                                       |        | 1MΩ≤R                                                                                                                                                         | 30dB (32μV/V)                                                                                                                                                 |                                                                                                                                                                                                                                                                                                                                                    |                               |

## Automatic Insertion Packaging

### Tape & Reel Quantities (Punched Paper Tape)

| Style                  | CR05   | CR10, CR21, CR32 |
|------------------------|--------|------------------|
| Punched Carrier        | 8mm    | 8mm              |
| Pieces/7" Reel         | 10,000 | 5,000            |
| Pieces/10" or 13" Reel | NA     | 10,000           |

### Reel Dimensions (Metric dimensions will govern)



| Tape Size | A Max.      | B Min.        | C                        | D Min.         | N Min.        | W                       | T Max.        |
|-----------|-------------|---------------|--------------------------|----------------|---------------|-------------------------|---------------|
| 8mm       | 178<br>(7)  | 1.5<br>(.059) | 13.0±0.50<br>(.512±.020) | 20.2<br>(.795) | 50<br>(1.969) | 10.0±1.5<br>(.394±.060) | 2.5<br>(.098) |
|           | 260<br>(10) |               |                          |                |               |                         |               |
|           | 330<br>(13) |               |                          |                |               |                         |               |

Metric dimensions will govern.

English measurements rounded and for reference only.

mm (inch)

### Punched Tape Configuration

#### 8mm Tape Only (Metric dimensions will govern, inches are in parentheses)


##### Constant Dimensions

| Tape Size | D <sub>0</sub>                                                                    | E                        | P <sub>0</sub>          | P <sub>2</sub>          | W                      | F                       |
|-----------|-----------------------------------------------------------------------------------|--------------------------|-------------------------|-------------------------|------------------------|-------------------------|
| 8mm       | 1.5 <sup>+0.1</sup> <sub>-0.0</sub><br>(.059 <sup>+0.004</sup> <sub>-.000</sub> ) | 1.75±0.10<br>(.069±.004) | 4.0±0.10<br>(.157±.004) | 2.0±0.05<br>(.079±.002) | 8.0±0.2<br>(.315±.008) | 3.5±0.05<br>(.138±.002) |

##### Variable Dimensions

| Style                   | P <sub>1</sub>                                   | A <sub>0</sub>           | B <sub>0</sub>           | T <sub>MAX.</sub> |
|-------------------------|--------------------------------------------------|--------------------------|--------------------------|-------------------|
| CR/CJ05                 | 2.0±0.1<br>(.079±.004)                           | 0.65±0.10<br>(.026±.004) | 1.15±0.10<br>(.045±.004) | 0.6<br>(.024)     |
| CR/CJ/FR10              | 4.0±0.1 (.157±.004)<br>or<br>2.0±0.1 (.079±.004) | 1.1±0.20<br>(.043±.008)  | 1.9±0.20<br>(.075±.008)  | 1.1<br>(.043)     |
| CR/CJ/FR21              | 4.0±0.10<br>(.157±.004)                          | 1.65±0.20<br>(.065±.008) | 2.4±0.20<br>(.094±.008)  |                   |
| CR/CJ/FR32              |                                                  | 2.0±0.20<br>(.079±.008)  | 3.6±0.20<br>(.142±.008)  |                   |
| CRA3A<br>CRB3A<br>CRC3A |                                                  |                          |                          |                   |
| CRA1A<br>CRB1A<br>CRC1A |                                                  | 1.9±0.20<br>(.079±.008)  | 1.9±0.20<br>(.079±.008)  |                   |
| CRB2A                   | 2.0±0.1<br>(.079±.004)                           | 1.25±0.2<br>(.049±.008)  | 2.5±0.2<br>(.098±.008)   |                   |

### Punched Carrier



### Bulk Packaging

- 1) Package: 100 × 60mm Plastic bag
- 2) Unit: 1,000 pcs/bag
- 3) Label includes the following:
  - Part Number
  - Quantity
  - Lot Number