







Copyright FCI.

A


B

C

D



PC card drilling dimensions(after plating)
(thickness 2.40±0.20mm)



TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24B.GV00
15	39.14	33.32	25.18	24.54	19.18	D15S24B.GV00
25	53.03	47.04	39.12	38.25	33.12	D25S24B.GV00
37	69.32	63.50	55.68	54.71	49.68	D37S24B.GV00

Plating: 4 --> flash AU

Plating: 6 --> 0.76µ AU

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24B.GV00LF
15	39.14	33.32	25.18	24.54	19.18	D15S24B.GV00LF
25	53.03	47.04	39.12	38.25	33.12	D25S24B.GV00LF
37	69.32	63.50	55.68	54.71	49.68	D37S24B.GV00LF

Plating: 4 --> flash AU

Plating: 6 --> 0.76µ AU

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0000

European Views

www.fciconnect.com			surface ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection 		mm 		
TOLERANCES UNLESS OTHERWISE SPECIFIED											
Dr	LELEON	1992/09/16	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 2			
Eng	PESSON	1992/09/16			0.XX	±0.1					
Chr	LEGARE	1992/09/16			0.XXX	±0.1		ECN LS06-0097			
Appr	LEGARE	1992/09/16	Product family				D-SUB	Spec ref -			
			title FEMALE CONNECTOR STD EURO straight solder type for				dwg no C01-8646-0124			Rev F	
catalog no			-				CUSTOMER			sheet 1 of 1	

rev	ecn no	dr	date
B	-	-	1996/09/09
D	LS05-001	MPE	2005/03/10
E	LS05-0056	MPE	2005/06/24
F	LS06-0097	LGO	2006/07/29
-	-	-	-
-	-	-	-
-	-	-	-

REV F - 2006-04-17