

T30RSF0M4



Article Number: 126-00702

Push Mount Tie, 6.3" Long, 30lb Tensile, Panel Thickness 0.19"- 0.22", PA66HS, Black, 1,000/pkg

 RoHS

 Download drawing

 Download spec sheet

Base Data

Local Order Number	T30RSF0M4
Type	T30RSF(U)
Color	Black (BK)
Features and Benefits	• Push Mount design provides quick and easy mounting. • Push mount style creates low insertion and high extraction force. • Ties "clicks" into place upon final installation signaling installer insertion is complete.
Product Description	Push Mount Ties provide a one piece, all plastic tie for quick and simple cable mounting.
Short Description	Push Mount Tie, 6.3" Long, 30lb Tensile, Panel Thickness 0.19"- 0.22", PA66HS, Black, 1,000/pkg

Product Dimensions

Minimum Tensile Strength (Imperial)	30.0 lbs
Minimum Tensile Strength (Metric)	135 N
Length L (Imperial)	6.3 "
Length L (Metric)	161.0 mm
Fixation Method	Arrowhead
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.14 "
Width W (Metric)	3.6 mm
Height H (Imperial)	0.2 "
Height H (Metric)	5.7 mm
Bundle Diameter Min. (Imperial)	0.06 "
Bundle Diameter Min. (Metric)	1.6 mm
Bundle Diameter Max. (Imperial)	1.3 "
Bundle Diameter Max. (Metric)	31.0 mm
Panel Thickness Max. (Imperial)	0.09 "
Panel Thickness Max. (Metric)	2.4 mm
Panel Thickness Min. (Imperial)	0.04 "
Panel Thickness Min. (Metric)	0.9 mm
Mounting Hole Diameter D (Imperial)	0.19 - 0.22 "
Mounting Hole Diameter D (Metric)	4.7 - 5.5 mm

Mounting Hole Diameter D Min. (Imperial)	0.19 "	Mounting Hole Diameter D Max. (Imperial)	0.22 "	Thickness T (Imperial)	0.05 "
Mounting Hole Diameter D Max. (Metric)	5.6 mm	Mounting Hole Diameter D Min. (Metric)	4.8 mm		
Thickness T (Metric)	1.2 mm				

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	1000
Carton Quantity	5000

Material and Specifications

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL94 V2
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
ROHS Compliant	Yes
Certification/Specification	UL
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes