

Customer Information Sheet

DRAWING No.: M20-106XX00

SHEET 2 OF 2

IF IN DOUBT - ASK

(C)


NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

ORDER CODE:
M20-106XX00

No. OF WAYS
01 TO 12



SPECIFICATIONS:

ELECTRICAL:

CURRENT RATING = 3A AC/DC

VOLTAGE RATING = 250V AC MAX



CONTACT RESISTANCE = 20 MILLIOHMS MAX

INSULATION RESISTANCE = 5,000 MEGOHMS MIN

DIELECTRIC STRENGTH = 1,500V AC FOR 1 MINUTE

ENVIRONMENTAL:

TEMPERATURE RANGE = -40°C TO +105°C



SECTION A-A

NOTES:

1. CONTACT No. 1 MARKER SYMBOL.
2. FOR USE WITH CRIMP CONTACTS:
M20-11600XX (REELED CONTACTS),
M20-11800XX (LOOSE CONTACTS).
3. THE ABOVE SPECIFICATIONS APPLY
WHEN THIS MOULDING IS USED
WITH THE SPECIFIED CONTACTS.
4. FOR COMPLETE ELECTRICAL AND
MECHANICAL SPECIFICATIONS, SEE
COMPONENT SPECIFICATION C001XX
(LATEST ISSUE).

WJB	5	19.06.01	5994
NAME	ISS.	DATE	C/NOTE
APPROVED: <i>[Signature]</i>			
CHECKED: <i>[Signature]</i>			
DRAWN: K. LIOTTA			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

HARWIN INC U.S.A.	HARWIN PLC U.K.	HARWIN PTE SINGAPORE
TEL: (812) 285 0055	TEL: 023 9237 0451	TEL: 65 7794909
FAX: (812) 285 0056	FAX: 023 9231 4590	FAX: 65 7793868

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:
MODIFIED PPO
UL94V-1 BLACK

FINISH: CLEAN

S/AREA: mm²

TITLE:
2.54mm PITCH SIL
CRIMP MOULDING

DRAWING NUMBER:
M20-106XX00

SHT
2
OF
2