

Delivery Program

Product Category:	Pressure Transducers
Model:	S
Order Code(s):	BP357 – BP358

USE THE CHART BELOW TO DETERMINE LEAD TIMES¹

The range or option code with the longest lead time dictates the shipping time. Categories shaded in grey are required selections. For example (reference only):

If you build this:	The order configuration is this:	The delivery class is:
BP357 + 200 psi pressure range (CL), 60 °F to 160 °F (1a), Unamplified, mV/V output (2u), 3/8-24 UNF pressure port, and four twisted leads 1.83 m termination	BP357 – CL – 1a – 2u	Quick ship, ships in 1 to 5 days
BP357 + 200 psi pressure range (CL), 30 °F to 130 °F (1b), Unamplified, mV/V output (2u), 3/8-24 UNF pressure port, and four twisted leads 1.83 m termination	BP357 – CL – 1b – 2u	Fast-track manufacture, ships within 4 weeks
BP357 + 750 psi pressure range (CT), 60 °F to 160 °F (1a), Unamplified, mV/V output (2u), 3/8-24 UNF, and Teflon integral cable termination (6e)	BP357 – CT – 1a – 2u – 6e	Build-to-order, call Honeywell for lead time

	Quick-ship (Ships in 1-5 days)	Fast track manufacture (Ships within 4 weeks)	Build-to-order (Call Honeywell 1-800-848-6564 or +1 614-850-5000)
Pressure ranges	200 (CL), 500 (CR), 1000 (CV), 2000 (DL), 3000 (DN), 5000 (DR), 10000 (DV) psig	100 (BR), 150 (CJ), 300 (CP)	750 (CT), 1500 (DJ), 7500 (DT) psig, 15000 (EJ) psig
Temperature compensation	1a. 60 °F to 160 °F * 1b. 30 °F to 130 °F 1c. 0 °F to 185 °F 1d. -20 °F to 130 °F 1e. -20 °F to 200 °F 1f. 70 °F to 250 °F 1i. -65 °F to 250 °F		1g. 70 °F to 325 °F 1h. 70 °F to 400 °F
Internal amplifiers	2u. Unamp., mV/V output*		
Pressure ports	3/8-24 UNF *		7/16-20 UNF (BP358)
Electrical termination	Four twisted leads 1.83 m [5 ft] *		6e. Integral cable: Teflon 6h. Integral cable: Silicone 6d. Microtec DR-4S-4H 4-pin (max 250 °F) 6i. Integral underwater cable: (max 180 °F)
Special calibration		9a. 10 point (5 up/5 down) 20 % increments @ 70 °F 9b. 20 point (10 up/10 down) 10 % increments @ 70 °F	
Wetted diaphragm			10e. Inconel X-750
Shock and vibration			44a. Shock and vibration

¹ LEAD/SHIPPING TIMES ARE APPROXIMATIONS AND MAY VARY DEPENDING ON PRODUCT AVAILABILITY AND OTHER FACTORS. IN NO EVENT SHALL HONEYWELL BE LIABLE FOR ANY SPECIAL, INDIRECT, INCIDENTAL, CONSEQUENTIAL, EXEMPLARY, OR PUNITIVE DAMAGES, EVEN WHERE HONEYWELL HAS BEEN ADVISED OF, OR IS OTHERWISE AWARE OF, THE POSSIBILITY OF SUCH DAMAGES, FOR FAILURE TO MEET SUCH LEAD / SHIPPING TIMES.

* Default options.

Note: Before selecting option/s, please refer to the Test and Measurement catalog or product data sheet for special application notes and compatibility. A catalog can be ordered on-line at <https://home.honeywell-online.com/newTMcatalog>. Product data sheets are available on Honeywell's web site at <http://content.honeywell.com/sensing/sensotec/catpages.asp>.