

THIS DRAWING IS UNPUBLISHED.
DIFFUSION RESTREINTE

RELEASED FOR PUBLICATION
LIBRE A LA DIFFUSION

20

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.
TOUS DROITS RESERVES

FILS ADMISSIBLES (ACCEPTABLES WIRES)

LOC
F

DIST
7

REVISIONS

P	LTR	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
	A	REDESSINE	06/90	AC	-
	B	REDESSINE SUR (REDRAWN ON) PRO/ENG	13SEP2002	CC	YP
	C	UPDATED	28MAR2007	TC	YP

JAUGE (AWG)
SECTION / 7 BRINS (7 STRANDS)

26-24
0.12-0.22mm²

ISOLANT: Ø MAX / MATIERE
(INSUL.: Ø MAX / MAT'L)

Ø 1/ PVC

VOIE N°1
(POSITION NUMBER 1)

2.54

DIM A

17.8±0.2

4

X.XHE1302

REPERE VOIE N°1
(IDENTIFIER POSITION NUMBER 1)

"C"±0.4

"B"+0.12
0

9.34⁰_{-0.3}

1.8±0.2

4.5⁰_{-0.1}

8.9 MIN

5.94⁰_{-0.1}

7.04⁰_{-0.1}

1

CES CONNECTEURS SONT PREVUS POUR ETRE ACCOUPLES AVEC LES EMBASES 'HE1302' DOUBLE RANGEE

(THESE CONNECTORS ARE DESIGNED TO BE MATED WITH 'HE1302' HEADERS DOUBLE ROW)

2

LES REFERENCES SUIVIES D'UN ' * ' SONT LES VERSIONS NORMALISEES SELON LA 'CEI 603-8'

(THE PART-Nº FOLLOWED BY ' * ' ARE COVERED BY THE INTERNATIONAL STANDARD 'IEC603-8')

3

REVETEMENT DES CONTACTS: 0.38µm D'OR DANS LA ZONE DE CONTACT, ETAIN SUR LA SORTIE C.A.D., SOUS-COUCHE NICKEL

(CONTACTS PLATING: 0.38µm GOLD ON CONTACT AREA, TIN ON I.D. BARREL, NICKEL UNDERPLATING)

4

"X.X" EST REMPLACE PAR LES DEUX DEUXIEME CHIFFRES DU COUPLE DES JAUGES AWG

("X.X" REPLACED BY THE TWO SECOND DIGIT OF AWG RANGE AS DEFINED IN TABLE)

5

MATIERES - BOITIER: PBT UL94V0
- CONTACTS: BRONZE PHOSPHOREUX.

(MATERIALS - HOUSING : PBT UL94V0
- CONTACTS: PHOSPHOR BRONZE)

ECHELLE 4:1
SCALE

ECHELLE 4:1
SCALE

46.52	43.18	2x 18	1- 281790-8 *
38.90	35.56	2x 15	1- 281790-5 *
31.28	27.94	2x 12	1- 281790-2 *
26.20	22.86	2x 10	1- 281790-0 *
21.12	17.78	2x 8	0- 281790-8 *
16.04	12.70	2x 6	0- 281790-6 *
13.50	10.16	2x 5	0- 281790-5 *
10.96	7.62	2x 4	0- 281790-4 *
8.42	5.08	2x 3	0- 281790-3 *
5.88	2.54	2x 2	0- 281790-2
"C"	"A,B"	Nº DE POS.	REFERENCES (PART N°)
DIMENSIONS			

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.
CE PLAN EST UN DOCUMENT CONTRÔLÉ PAR AMP INCORPORATED.
IL EST SUSCEPTIBLE D'ÊTRE RÉVISÉ, CONTACTER LE SERVICE
TECHNIQUE D'AMP DE FRANCE POUR OBTENIR LA DERNIÈRE RÉVISION.

DIMENSIONS:
mm

MATERIAL/MATIERE

5

TOLERANCES UNLESS OTHERWISE SPECIFIED:
(SUIV NB DE DECIMALES)
0 PLC/DEC: ±
1 PLC/DEC: ±0.3
2 PLC/DEC: ±
3 PLC/DEC: ±
4 PLC/DEC: ±
ANGLES ±5°

FINISH/FINITION

3

DWN/DESSINE
C. COMBEDOUZON
CHK/VERIFIE
T. CORRIEU
APVD/APPROUVE
Y. PETRONIN
PRODUCT SPEC
SPEC, PRODUIT
108-15053
APPLICATION SPEC
SPEC, APPLICATION
114-15031
WEIGHT
MASSE APPROX.
-
CUSTOMER DRAWING /PLAN CLIENT

UNIQUEMENT POUR REFERENCE

SCALE
ECHELLE 5:1

SHEET
FEUILLE

OF
DE

REV
C

AMP DE FRANCE
95301 PONTOISE

HE 1302 PLUG,
180° IDC DOUBLE ROW
-

SIZE
FORMAT
A2

CAGE CODE
00779

DRAWING NO
No PLAN
C=281790

RESTRICTED TO
RESERVE A
-