


Specifications




Type : Nickel-Metal Hydride Battery			Size : AAA Consumer Type	
Capacity ①	Typical		800mAh	
	Minimum		740mAh	
Nominal Voltage			1.2V	
Charging Current × Time		Fast Charge ③	800 mA × about 1.1h	
Ambient Temp.	Charge Condition	Fast Charge ③	0°C - 40°C	
	Discharge Condition		0°C - 50°C	
	Storage Condition	Less than 30days	-20°C - 50°C	
		Less than 90days	-20°C - 40°C	
		Less than 1year	-20°C - 30°C	
Internal Impedance ② (after discharge to E.V. =1.0V)			Approx. 40mΩ(at 1000Hz)	
Weight ④			Approx. 13 g	
Size ⑤ : (Diameter) × (Height)			10.5(D) × 44.0(H) mm	

- 1)Single cell capacity under the following condition.
Charge : 80mA×16h, Discharge : 160mA(E.V.=1.0V) at 20°C
- 2)Use recommended charging system.
- 3)After a few charge and discharge cycles under the above 1) condition.
- 4)With tube.

Typical Characteristics

Charge



Discharge

