


EPC2038 – Enhancement Mode Power Transistor with Integrated Reverse Gate Clamp Diode

 $V_{DS}, 100\text{ V}$
 $R_{DS(on)}, 3300\text{ m}\Omega$
 $I_D, 0.5\text{ A}$


RoHS




Halogen-Free

Gallium Nitride is grown on Silicon Wafers and processed using standard CMOS equipment leveraging the infrastructure that has been developed over the last 60 years. GaN's exceptionally high electron mobility and low temperature coefficient allows very low $R_{DS(on)}$, while its lateral device structure and majority carrier diode provide exceptionally low Q_G and zero Q_{RR} . The end result is a device that can handle tasks where very high switching frequency, and low on-time are beneficial as well as those where on-state losses dominate.

Maximum Ratings

V_{DS}	Drain-to-Source Voltage (Continuous)	100	V
	Drain-to-Source Voltage (up to 10,000 5ms pulses at 150°C)	120	
I_D	Continuous ($T_A = 25^\circ\text{C}$, $R_{\theta JA} = 100^\circ\text{C/W}$)	0.5	A
	Pulsed (25°C , $T_{PULSE} = 300\text{ }\mu\text{s}$)	0.5	
V_{GS}	Gate-to-Source Voltage	6	V
T_J	Operating Temperature	-40 to 150	$^\circ\text{C}$
T_{STG}	Storage Temperature	-40 to 150	



EPC2038 eGaN® FETs are supplied only in passivated die form with solder bumps. Die size: 0.9 mm x 0.9 mm

Applications

Synchronous Bootstrap for:

- High Speed DC-DC Conversion
- Wireless Power Transfer
- High Frequency Hard-Switching and Soft-Switching Circuits
- LiDAR/Pulsed Power Applications
- Class-D Audio

Benefits

- Ultra High Efficiency
- Ultra Low $R_{DS(on)}$
- Ultra low Q_G
- Ultra Small Footprint

www.epc-co.com/epc/Products/eGaNfets/EPC2038.aspx

Static Characteristics ($T_J = 25^\circ\text{C}$ unless otherwise stated)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
BV_{DS}	Drain-to-Source Voltage	$V_{GS} = 0\text{ V}$, $I_D = 125\text{ }\mu\text{A}$	100			V
I_{DSS}	Drain Source Leakage	$V_{DS} = 80\text{ V}$, $V_{GS} = 0\text{ V}$		20	100	μA
I_{GSS}	Gate-to-Source Leakage	$V_{GS} = 5\text{ V}$		0.1	1	mA
V_F	Source-Gate Forward Voltage	$I_F = 0.2\text{ mA}$, $V_{DS} = 0\text{ V}$			2.7	V
$V_{GS(TH)}$	Gate Threshold Voltage	$V_{DS} = V_{GS}$, $I_D = 0.1\text{ mA}$	0.8	1.7	2.5	V
$R_{DS(on)}$	Drain-Source On Resistance	$V_{GS} = 5\text{ V}$, $I_D = 0.05\text{ A}$		2100	3300	$\text{m}\Omega$
V_{SD}	Source-Drain Forward Voltage	$I_S = 0.1\text{ A}$, $V_{GS} = 0\text{ V}$		2.9		V

All measurements were done with substrate shorted to source.

Thermal Characteristics

		TYP	UNIT
$R_{\theta JC}$	Thermal Resistance, Junction to Case	27	$^\circ\text{C/W}$
$R_{\theta JB}$	Thermal Resistance, Junction to Board	91	$^\circ\text{C/W}$
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient (Note 1)	100	$^\circ\text{C/W}$

Note 1: $R_{\theta JA}$ is determined with the device mounted on one square inch of copper pad, single layer 2 oz copper on FR4 board. See http://epc-co.com/epc/documents/product-training/Appnote_Thermal_Performance_of_eGaN_FETs.pdf for details.

Dynamic Characteristics ($T_J = 25^\circ\text{C}$ unless otherwise stated)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
C_{ISS}	Input Capacitance	$V_{DS} = 50\text{ V}, V_{GS} = 0\text{ V}$		7	8.4	pF
C_{RSS}	Reverse Transfer Capacitance			0.02		
C_{OSS}	Output Capacitance			1.6	2.4	
$C_{OSS(ER)}$	Effective Output Capacitance, Energy Related (Note 2)	$V_{DS} = 0\text{ to }50\text{ V}, V_{GS} = 0\text{ V}$		2.2		
$C_{OSS(TR)}$	Effective Output Capacitance, Time Related (Note 3)			2.7		
R_G	Gate Resistance			4.8		Ω
Q_G	Total Gate Charge	$V_{DS} = 50\text{ V}, V_{GS} = 5\text{ V}, I_D = 0.05\text{ A}$		44		pC
Q_{GS}	Gate to Source Charge	$V_{DS} = 50\text{ V}, I_D = 0.05\text{ A}$		20		
Q_{GD}	Gate to Drain Charge			4		
$Q_{G(TH)}$	Gate Charge at Threshold			18		
Q_{OSS}	Output Charge	$V_{DS} = 50\text{ V}, V_{GS} = 0\text{ V}$		134		
Q_{RR}	Source-Drain Recovery Charge			0		

Note 2: $C_{OSS(ER)}$ is a fixed capacitance that gives the same stored energy as C_{OSS} while V_{DS} is rising from 0 to 50% BV_{DSS} .

Note 3: $C_{OSS(TR)}$ is a fixed capacitance that gives the same charging time as C_{OSS} while V_{DS} is rising from 0 to 50% BV_{DSS} .


Figure 1: Typical Output Characteristics at 25°C 

Figure 2: Transfer Characteristics




Figure 3: $R_{DS(on)}$ vs. V_{GS} for Various Drain CurrentsFigure 4: $R_{DS(on)}$ vs. V_{GS} for Various Temperatures

Figure 5a: Capacitance (Linear Scale)




Figure 5b: Capacitance (Log Scale)




Figure 6: Gate Charge




Figure 7: Reverse Drain-Source Characteristics




Figure 8: Normalized On-State Resistance vs. Temperature





Figure 9: Normalized Threshold Voltage vs. Temperature



All measurements were done with substrate shorted to source.

Figure 10: Gate-Source Characteristics




Figure 11: Transient Thermal Response Curves







Figure 12: Safe Operating Area



TAPE AND REEL CONFIGURATION

4mm pitch, 8mm wide tape on 7" reel




Die is placed into pocket
solder bump side down
(face side down)

EPC2038 (note 1)			
Dimension (mm)	target	min	max
a	8.00	7.90	8.30
b	1.75	1.65	1.85
c (see note)	3.50	3.45	3.55
d	4.00	3.90	4.10
e	4.00	3.90	4.10
f (see note)	2.00	1.95	2.05
g	1.5	1.5	1.6

Note 1: MSL 1 (moisture sensitivity level 1) classified according to IPC/JEDEC industry standard.
Note 2: Pocket position is relative to the sprocket hole measured as true position of the pocket, not the pocket hole.


DIE MARKINGS



Part Number	Laser Markings	
	Part # Marking Line 1	Lot_Date Code Marking line 2
EPC2038	AD	YYY


DIE OUTLINE

Solder Bump View



DIM	MIN	Nominal	MAX
A	870	900	930
B	870	900	930
c	450	450	450
d	450	450	450
e	210	225	240
f	210	225	240
g	187	208	229

Side View


**RECOMMENDED
LAND PATTERN**(measurements in μm)

The land pattern is solder mask defined
Solder mask is $10\mu\text{m}$ smaller per side than bump

Pad 1 is Gate;

Pad 3 is Drain;

Pads 2, 4 are Source

**RECOMMENDED
STENCIL DRAWING**(measurements in μm)

Recommended stencil should be 4mil ($100\mu\text{m}$) thick, must
be laser cut, openings per drawing.

Intended for use with SAC305 Type 4 solder, reference 88.5%
metals content.

Additional assembly resources available at
<http://epc-co.com/epc/DesignSupport/AssemblyBasics.aspx>

Efficient Power Conversion Corporation (EPC) reserves the right to make changes without further notice to any products herein to improve reliability, function or design. EPC does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

eGaN® is a registered trademark of Efficient Power Conversion Corporation.

EPC Patent Listing: epc-co.com/epc/AboutEPC/Patents.aspx

Information subject to
change without notice.

Revised April, 2017