


General specifications

Layout



Components

Material

- Case : glass-filled polyamide (self-extinguishing version to UL 94 VO and IEC 695-2-1 850° C - available on request)
- Button : polyamide
- Contacts : nickel silver or gold alloy (dual-current)


Actuators

- flat : stainless steel
- roller : stainless steel, glass-filled polyamide roller
- other types of polyamide


Approvals: NF - UL/cUL

Operating curve


For type 83 161 1 3




For type 83 161 5 - 5 SP 4136



For type 83 161 8



For type 83 161 9 SP 4136



For types 83 161 8 - 9 SP 4136 dual-current

Models 83 161 8 and 83 161 9 SP 4136 are designed to operate equally well on dual-current (1 mA 4 V minimum) or medium-current (5 A maximum) circuits. However, a given product should only be used to switch one type of circuit during its working life.

Types

Part numbers for standard products with connections of type

2
3
6

Features

Electrical characteristics

Current rating at 125/250 V	Current	A
	Horsepower	HP

Mechanical characteristics

Operating force - max.	N (oz.)
Release force - min.	N (oz.)
Total travel force - max.	N (oz.)
Permitted overtravel force - max.	N (oz.)
Rest position - max.	mm (in.)
Tripping point	mm (in.)
Differential travel	mm (in.)
Overtravel - min. (OT)	mm (in.)
Ambient operating temperature	°C (°F)
Mechanical durability (for 2/3 OT)	Operations
Contact gap	mm (in.)
Weight	g (oz.)

Contact type

C (Form C) SPDT

B (Form B) SPNC

A (Form A) SPNO

Connections



2 solder



3 for 1/4" Quick Connects

Actuators and mounting positions

Part numbers for standard actuators

A 79 215 740

Actuators-Length mm (in.) Flat 161A R14.2 (.56)



Mounting positions	A	B
Coefficient	2	1
Tripping point (except 83 161 6)	15.2 ± 1 (.6 ± 0.04)	15.2 ± 0.45 (.6 ± 0.018)
Tripping point 83 161 6	14.8 ± 1 (.59 ± 0.04)	15 ± 0.45 (.59 ± 0.018)

Part numbers for standard actuators

H 79 218 651

Actuators-Length mm (in.) Dummy roller 161G R21.8 (.86)




Mounting positions	A	B
Coefficient	3	1.8
Tripping point (except 83 161 6)	21.7 ± 2 (.85 ± 0.08)	21.7 ± 0.7 (.85 ± 0.03)
Tripping point 83 161 6	21.5 ± 2 (.85 ± 0.08)	21.5 ± 0.7 (.85 ± 0.03)

Other information


For other forces, actuators, connections and temperatures, please consult us.

Normally stocked items

Catalog products produced to order



1						
83161.1(10.1A)	83161.2(15.1A)	83161.3(10.1A)	83161.5(4A) 83161.9(0.1A)	83161.5SP4136 83161.9SP4136	83161.6	83161.8(0.1A)
831611C2.0	831612C2.0	831613C2.0	831615C2.0	•	831616C2.0	831618C2.0
831611C3.0	831612C3.0	831613C3.0	831615C3.0	•	831616C3.0	831618C3.0
831611C6.0	831612C6.0	831613C6.0	831615C6.0	•	831616C6.0	831618C6.0
High Force	High Current	Standard	Low Force	Ultra Light Force	Wide Gap	Dual Current
10.1	15.1	10.1	4	4	6.1	0.1
1/2	1/2	1/2	1/10	1/10	1/3	N/A
3 (10.5)	0.8 (2.8)	0.8 (2.8)	0.25 (0.9)	0.15 (0.54)	5 (18)	0.8 (2.8)
1 (3.5)	0.2 (0.7)	0.2 (0.7)	0.05 (0.18)	0.04 (0.14)	0.5 (1.8)	0.2 (0.7)
4.5 (15.8)	2 (7.0)	2 (7.0)	0.35 (1.2)	0.2 (0.72)	6 (21.6)	0.2 (.07)
20 (70.5)	20 (70.5)	20 (70.5)	20 (70.5)	20 (70.5)	20 (70.5)	20 (70.5)
16.1 (0.63)	16.2 (0.64)	16.2 (0.64)	16.3 (0.64)	16.3 (0.64)	16.1 (0.63)	16.2 (0.64)
14.7 ^{+0.4} (.58 ^{+0.16})	14.7 ^{+0.3} (.58 ^{+0.16})	14.7 ^{+0.3} (.58 ^{+0.16})	14.7 ^{+0.4} (.58 ^{+0.16})	14.7 ^{+0.3} (.58 ^{+0.16})	14.5 ^{+0.4} (.58 ^{+0.16})	14.7 ^{+0.4} (.58 ^{+0.16})
0.35 (0.014)	0.35 (0.014)	0.35 (0.014)	0.35 (0.014)	0.35 (0.014)	0.8 (0.03)	0.35 (0.014)
1.1 (0.05)	1.2 (0.05)	1.2 (0.05)	1.1 (0.05)	1.2 (0.05)	0.9 (0.035)	1.2 (0.05)
-20 +125 (-4 +257)	-20 +125 (-4 +257)	-20 +125 (-4 +257)	-20 +125 (-4 +257)	-20 +125 (-4 +257)	-20 +125 (-4 +257)	-20 +125 (-4 +257)
10 ⁷	2 x 10 ⁷	2 x 10 ⁷	5 x 10 ⁷	5 x 10 ⁷	5 x 10 ⁴	2 x 10 ⁷
0.4 (0.016)	0.4 (0.016)	0.4 (0.016)	0.4 (0.016)	0.4 (0.016)	3.2 (0.126)	0.4 (0.016)
5.6 (.2)	5.6 (.2)	5.6 (.2)	5.6 (.2)	5.6 (.2)	5.6 (.2)	5.6 (.2)
2						
C	C	C	C	C	C	C
B	B	B	B	B	B	B
A	A	A	A	A	A	A
3						



5 screw



6 for 3/16 Quick Connects



7 for .11 Quick Connects

4			
B 70 507 524	E 79 215 742	G 70 507 529	F 70 507 528
Flat 161A R25.4 (1)	Roller 161E R13.6 (.54)	Roller 161E R24.1 (.95)	Dummy 161F roller R22.2 (.84)
A	A	A	A
B	B	B	B
C	C	C	C
4	2	4	3
15.2 ^{+2.5} (.6 ⁺¹)	20.5 ^{+1.5} (.81 ^{+0.06})	20.5 ^{+2.0} (.81 ^{+0.11})	20.4 ⁺² (.8 ^{+0.08})
14.4 ^{+2.5} (.56 ⁺¹)	20.1 ^{+1.5} (.79 ^{+0.06})	19.7 ^{+2.0} (.76 ^{+0.11})	20.2 ⁺² (.79 ^{+0.08})
15.2 ⁺¹ (.6 ^{+0.04})	20.5 ^{+0.8} (.81 ^{+0.03})	20.5 ^{+1.5} (.81 ^{+0.06})	20.5 ^{+0.7} (.81 ^{+0.03})
14.8 ⁺¹ (.58 ^{+0.04})	20.3 ^{+0.8} (.80 ^{+0.03})	20.1 ^{+1.5} (.79 ^{+0.06})	20.2 ⁺² (.79 ^{+0.08})
15.2 ^{+0.8} (.6 ^{+0.03})		20.5 ^{+1.2} (.81 ^{+0.05})	
14.9 ^{+0.8} (.59 ^{+0.03})		20.2 ^{+1.2} (.79 ^{+0.05})	
4			
L	V 161V	C 70 507 526	D 79 215 835
** Telescopic plunger Manual action 161L		Flat 161A R50 (1.9)	Flat 161A R60 (2.39)
D Factory Mount only	D Factory Mount only	A	A
1	1	B	B
21.5 ⁺¹ (.85 ^{+0.04})	18.35 ^{+0.45}	6	7
21.5 ⁺¹ (.85 ^{+0.04})		15.2 ^{+0.3}	15.2 ^{+0.9}
		15.2 ^{+0.3}	15.2 ^{+2.5}
		15.2 ^{+0.3}	15.2 ^{+2.3}
** For 83 161 1, 83 161 3, 83 161 6, 83 161 8, mounted in factory (supplied without nut)			


For factory mounting, specify fixing position A, B or C

To order, please specify :

1	Switch Type	2	Contact Type	3	Connection	Example : 831612 C 3 • C A	4	Actuators	5	Actuator Position
831612	831619	A		2			Ø			A B (std) C D
831613	831616	B		3			A			
831615	831611	C		5			B			
831618				6			C			
				7			D			
To order actuators separately, use the 8 digit P/N				Example switch is 831612, SPDT, 1/4" Q.C., C actuator mounted in A position						
				Ø = No actuator						

Dimensions


83 161




mm (in)

Connections


2 Solder




3 (6.3x0.8 (1/4x.03)) Quick Connects




5 Screw



6 (4.8x0.5 (.3/16x.02)) Quick Connects




7 (2.5x0.5 (.11x.02)) Quick Connects



Actuators

mm (in)



Force calculation : divide the switch forces by the coefficient in the table.

Travel calculation : multiply the switch travel by the same coefficient.


Example :

83 161 3 with B Flat 161A actuator R 25.4 (1) position A (coef. 4)

Operating force : $0.8 \div 4 = 0.2$ N


Pre-travel: $1.4 \times 4 = 5.6$ mm (.055 x 4 = .22 in)

Actuator Mounting Positions




Actuators


E - G




A - B - C - D




L




V



F



H



Nut depth	Torque max.
1.5mm (.06)	5Cm N (7 in oz.)
2mm (.08)	7Cm N (10 in. oz)
2.5mm (.1)	10Cm N (14 in. oz)

Accessories

Nuts 70 602 118 for L type actuator

