










REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A2		Released as per ECR-07-012890	10-07-07	SK	TS
A3		Released as per ECO-09-027197	15DEC09	KK	AEG
A4		Released as per ECR-17-014011	16JAN18	RSM	MKO

- NOTES
- 1 Material: Housing: aluminium diecasting alloy
 - 2 Surface:- Powder varnish-grey
Varnish black
 - 3 Varnish on the inside not necessarily
 - 4 Packaging
quantity: 5 pieces
 - 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER
D.RENAUD/D.SINISI



SCALE 1:2



SCALE 1:2		SCALE 1:2		SCALE 1:2		SCALE 1:2	
2-7	1-7	1-1	2-6	1-6			
OBSOLETE		OBSOLETE	OBSOLETE	OBSOLETE			
-	1	1	1		HUT-Gland fitting PG29	Brass	Nickel plated
-	2	-	-	-	PG-Gland fitting PG29	Brass	Nickel plated
-	2	-	-	-	LB-Locking clip	Stainless steel	-
-	-	2	-	-	LB-Clip bolt	Steel	Zinc plated
-	-	-	4	-	VS-Locking clip	Steel	Zinc plated
-	-	-	-	4	VS-Clip bolt	Stainless steel	-
-	1	-	1	-	VS-Clip bolt	Steel	Zinc plated
-	1	1	-	1	Hood HD.40.PG29	Aluminium	Aluminium oxide
-	1	1	-	1	Hood HD.40.PG29	Aluminium	-
					DESCRIPTION	MATERIAL	SURFACE
							COLOR
							ITEM NO
							NOTES
ORDERING TEXT							
HD-40.STO.1.29							
HD-K.40.STO.1.29							
HD-40.STO-VS.1.29							
HD-40.STO-GR.1.29							
HD-K.40.STO-GR.1.29							

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm 1991-102

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

DWN Schneider 15.03.2001

CHK M. Schweiger 15.03.2001

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME HOOD HD.40.STO.1.29

SIZE A1

CAGE CODE 00779

DRAWING NO 1102571

RESTRICTED TO

SCALE 1:1

SHEET 1 OF 1

REV A4

TE

TE Connectivity