


3M™ WIREMOUNT SOCKET, 3000 SERIES
.100" X .100" FOR .050" PITCH CABLE, (OPTIONAL PLASTIC OR METAL STRAIN RELIEF)



- * INDUSTRY STANDARD IDC SOCKET.
- * POSITIVE LOCKING METAL "J" CLIPS PROVIDE HIGH COVER RETENTION.
- * MATES WITH 3M HEADERS, PLUGS AND PIN STRIPS FOR QUICK CONNECT/DISCONNECT CAPABILITY.
- * OPEN OR CLOSED END COVERS AVAILABLE.
- * ACCEPTS FLAT CABLE OR DISCRETE WIRE.
- * MILITARY POLARIZATION, WITH OR WITHOUT CENTER BUMP.
- * TRANSFER ADHESIVE ON COVERS PROVIDES PRECISION ALIGNMENT BETWEEN CONNECTOR AND CABLES RESULTING IN HIGH YIELD TERMINATIONS.
- * AVAILABILITY OF PULL TAB TO FACILITATE PROPER UNPLUGGING.
- * AVAILABILITY OF 2 TYPES OF STRAIN RELIEF (STANDARD AND LOW PROFILE) TO ISOLATE THE IDC INTERFACE.
- * SET THE STANDARD FOR MIL SPEC AND IEC STANDARDIZATION.
- * AVAILABILITY OF MILITARY AND CENTER BUMP POLARIZATION.

2 PHYSICAL :

INSULATION: GLASS FILLED POLYESTER (PBT)
MATERIAL: UL94V-0
FLAMMABILITY: GRAY
COLOR: COPPER ALLOY
CONTACT: J-CLIP: STAINLESS STEEL
PLATING: UNDER PLATING AND U-SLOT: 100μ" [2.54μm] AVG. NICKEL-OVERALL
WIPING AREA: 30μ" [0.76μm] AVG. GOLD
WIRE ACCOMMODATION: 26 AND 28 AWG SOLID AND STRANDED
MARKINGS: 3M LOGO, PART IDENTIFICATION NUMBER, ORIENTATION TRIANGLE

2 ELECTRICAL :

CURRENT RATING:

	1 LINE	6 ADJACENT LINES	ALL LINES
28 AWG	4.50	1.75	1.00
26 AWG	4.75	2.00	1.00

RATING CONDITIONS: EIA-364-070 METHOD 2, 30°C MAXIMUM TEMPERATURE RISE, 20% DERATED. REFERENCE APPROPRIATE 3M PRODUCT SPECIFICATION FOR CURRENT DERATING CURVES.

INSULATION RESISTANCE: >1 X 10⁹Ω AT 500 V_{DC}
WITHSTANDING VOLTAGE: 1,000V_{RMS} AT SEA LEVEL

2 ENVIRONMENTAL :

TEMPERATURE RATING: -55°C TO +105°

ORDERING INFORMATION
SOCKETS

XXXX-XXXX

SOCKET SERIES:
(SEE TABLE 1)

STRAIN RELIEF:
00 = NO STRAIN RELIEF
XX = CONTACT QUANTITY FOR
PLASTIC STRAIN RELIEF
10 THRU 60 POSITION
(I.E. 50 FOR A 50 POS)
05 = PLASTIC STRAIN RELIEF
6 AND 8 POSITION
06 = METAL STRAIN RELIEF
10 THRU 60 POSITION

POLARIZATION:
0 = MILITARY (DUAL SLOT)
6 = CENTER BUMP AND MILITARY

COVER:
6 = OPEN END
(FOR DAISY CHANING OR BUSSING)
7 = CLOSED END
(FOR END CABLE TERMINATION)
(10 TO 60 POSITION ONLY)

3M ELECTRONICS MATERIALS SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
<http://www.3M.com/interconnect>

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

UL
UL FILE NO: E68080

(ORDER SEPARATELY)
SEE TS-0720

ORDERING INFORMATION
STRAIN RELIEF

3448-X0XX

TYPE:
2 = METAL, LOW PROFILE
10 THRU 60 POSITION
(SEE NOTE 3)
3 = PLASTIC

XX = CONTACT QUANTITY
SEE TABLE 1
(I.E. 50 FOR A
50 POSITION STRAIN
RELIEF)

ORDERING INFORMATION
KEYING PLUG

3435-0000

ORDERING INFORMATION
PULL TABS

3490-X


NOTE:
ASSEMBLY TOOLS:
3M PRESS (OR EQUIVALENT): 3640
3M LOCATOR PLATE: 3443-94
3M PLATTN: 3442-9

- NOTES
1. REGULATORY INFORMATION:
VISIT 3M.com/regs
 2. UNLESS OTHERWISE NOTED,
REFERENCES TO INDUSTRY
SPECIFICATIONS ARE INTENDED
TO INDICATE SUBSTANTIAL
COMPLIANCE TO THE MATERIAL
ELEMENTS OF THE SPECIFICATION.
SUCH REFERENCES SHOULD NOT BE
CONSTRUED AS A GUARANTEE OF
COMPLIANCE TO ALL REQUIREMENTS
IN A GIVEN SPECIFICATION.
 3. THIS POLARIZING GROOVE IS
NON-EXISTENT ON 3863, 3868,
3385 AND 3473 SERIES.
 4. THIS POLARIZING GROOVE IS
NON-EXISTENT ON 3863 SERIES
FOR POLARIZATION OPTION 6.
 5. THE LOW PROFILE STRAIN RELIEF
CAN BE USED WITH THE 4600 SERIES
PLUG AND .100 X .100 HEADERS
WITH EJECTOR LATCHES. THE LATCHES
WILL ONLY FUNCTION AS AN EJECTOR.
 6. TAPERED PIN TIP CONFIGURATION
RECOMMENDED.
 7. DIMENSION MEASURED AT TIP OF
PINS.



DIMENSIONS: INCHES [MM]
[MM] IS REF. ONLY

DESIGN REFERENCE	NEXT ASSEMBLY	REV	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXX	XXXX	ECO	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
DIVISION	DIVISION CODE	DATE	DATE	DATE	DATE	DATE
DO NOT SCALE DRAWING	SCALE	TOLERANCES EXCEPT AS NOTED	INCHES	MILLIMETERS	MAX. SURFACE ROUGHNESS	MARKED ONLY
THIRD ANGLE PROJECTION	INTERPRET PER ASME Y14.5 - 2018	MAX. SURFACE ROUGHNESS	MARKED ONLY	ANGLES	ANGLES	ANGLES
3M	3M Center St. Paul, MN 55144	© 3M COPYRIGHT 2021	3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.	TITLE	CAGE NUMBER	SIZE
WIREMOUNT SOCKET, .100" X .100", .050" PITCH CABLE	78-5100-0718-6	D	3000	REV.	LISTS	YES
MODEL	3000	LISTS	YES	NO	SHT	1 OF 4



3M™ WIREMOUNT SOCKET, 3000 SERIES
.100" X .100" FOR .050" PITCH CABLE, (OPTIONAL PLASTIC OR METAL STRAIN RELIEF)





COVER ASSEMBLY




CONTACT QTY.	SOCKET SERIES	DIM. "A"	DIM. "B"
06	3863	0.48 [12.2]	0.34 [8.6]
08	3868	0.58 [14.7]	0.44 [11.2]
10	3473	0.68 [17.3]	0.54 [13.7]
14	3385	0.88 [22.4]	0.74 [18.8]
16	3452	0.98 [24.9]	0.84 [21.3]
20	3421	1.18 [30.0]	1.04 [26.4]
24	3626	1.38 [35.1]	1.24 [31.5]
26	3399	1.48 [37.6]	1.34 [34.0]
30	3419	1.68 [42.7]	1.54 [39.1]
34	3414	1.88 [47.8]	1.74 [44.2]
36	9436	1.98 [50.3]	1.84 [46.7]
40	3417	2.18 [55.4]	2.04 [51.8]
44	9444	2.38 [60.5]	2.24 [56.9]
50	3425	2.68 [68.1]	2.54 [64.5]
60	3334	3.18 [80.8]	3.04 [77.2]

G		97305		JUN 21, 2021		JNC		SAN	
REVISED AND REDRAWN									
REV		ECO		ISSUE DATE AND DESCRIPTION		DRFT		CHKD	
REV		ECO		DATE		MFG		DATE	
				JUN 21, 2021		APPL		JUN 22, 2021	
CHGD				DATE		S. NEU			
DIVISION		DIVISION CODE							
		EMSD							
DO NOT SCALE DRAWING		SCALE		TOLERANCES EXCEPT AS NOTED					
		6 1							
THIRD ANGLE PROJECTION		INCHES		TITLE					
		.0000 ± .0005 .0000 ± .0002		WIRE MOUNT SOCKET, .100" X .100", .050" PITCH CABLE					
INTERPRET PER ASME Y14.5 2018		MILLIMETERS		CAGE NUMBER					
MAX. SURFACE ROUGHNESS		.0000 ± .0005 .0000 ± .0002		SIZE					
		.0000 ± .0005 .0000 ± .0002		DRAWING NO.					
✓ ALL SURFACES MARKED ONLY		ANGLES		5100-0718-6					
				REV. C					
				MODEL					
				3000					
				DET. LISTS					
				YES YES NO SHT 2 OF 4					


3M™ WIREMOUNT SOCKET, 3000 SERIES
.100" X .100" FOR .050" PITCH CABLE, (OPTIONAL PLASTIC OR METAL STRAIN RELIEF)




RECOMMENDED PIN PATTERN
FOR STACKED CONFIGURATIONS



ASSEMBLED HEIGHT
WITH METAL PROFILE
STRAIN RELIEF



ASSEMBLED HEIGHT
WITHOUT STRAIN RELIEF



ASSEMBLED HEIGHT
WITH PLASTIC
STRAIN RELIEF

DESIGN REFERENCE		NEXT ASSEMBLY		REV		ECO		ISSUE DATE AND DESCRIPTION		DRFT		CHKD	
XREFS		XREFS		DRFT		CHKD		DATE		DATE		DATE	
DIVISION		DIVISION CODE		DATE		DATE		DATE		DATE		DATE	
DO NOT SCALE DRAWING		SCALE		TOLERANCES EXCEPT AS NOTED		TOLERANCES EXCEPT AS NOTED		TOLERANCES EXCEPT AS NOTED		TOLERANCES EXCEPT AS NOTED		TOLERANCES EXCEPT AS NOTED	
THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 2018		INCHES		MILLIMETERS		MILLIMETERS		MILLIMETERS		MILLIMETERS	
MAX. SURFACE ROUGHNESS		ALL SURFACES		MARKED ONLY		MARKED ONLY		MARKED ONLY		MARKED ONLY		MARKED ONLY	
CAGE NUMBER		SIZE		DRAWING NO.		REV.		REV.		REV.		REV.	
MODEL		3000		D78-5100-0718-6		G		G		G		G	
LISTS		YES		NO		SHT 3 OF 4		SHT 3 OF 4		SHT 3 OF 4		SHT 3 OF 4	

3M™ WIREMOUNT SOCKET, 3000 SERIES

.100" X .100" FOR .050" PITCH CABLE, (OPTIONAL PLASTIC OR METAL STRAIN RELIEF)

Regulatory: For regulatory information about this product, visit 3M.com/regs or contact your 3M representative.

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer: Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OR TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

3M Company
Electronics Materials Solutions Division
13011 McCallen Pass, Bldg. C
Austin, TX 78753-5380
1-800-225-5373
www.3M.com/interconnect

						G	97305	JUN 21, 2021				JNC	SAN
						REVISED AND REDRAWN							
DESIGN REFERENCE		NEXT ASSEMBLY		REV		ECO		ISSUE DATE AND DESCRIPTION				DRFT	CHKD
ACCESS CODES				DRFT CAST IGL ONE		DATE JUN 21, 2021		MFG				DATE	
				CHGD		DATE		APPRV S. NEU				DATE JUN 22, 2021	
DIVISION				DIVISION CODE EWSO				© 3M COPYRIGHT 2021 This document contains information that is confidential to 3M property and may not be reproduced or further distributed without the prior written permission of 3M. All rights reserved.					
DO NOT SCALE DRAWING		SCALE B / I		TOLERANCES EXCEPT AS NOTED		3M St. Paul, MN 55114							
		THIRD ANGLE PROJECTION		INCHES .00 ± .01 .000 ± .005 .0000 ± .0002		TITLE WIREMOUNT SOCKET 100'' X 100'' x .050'' PITCH CABLE							
INTERPRET PER ASME Y14.5 - 2018		MILLIMETERS 0 ± .00 0 ± .00 0 ± .00		MAX SURFACE ROUGHNESS ALL SURFACES MARKED ONLY		CASE NUMBER D 78-5100-0718-6		SIZE DRAWING NO.		REV. G			
		ANGLES ±		MODEL 3000		DET. YES YES YES NO		SHT 4 OF 6					