


Phone Jack SMD/SMT 2.5mm w/ Switch

161-232VS-E



Phone Jack SMD/SMT 2.5mm w/ Switch



DIMENSIONS: mm

ELECTRICAL SPECIFICATIONS

Contact Resistance:	30mΩ Max.
Insulation Resistance:	100MΩ Min. at DC 500V
Dielectric Withstand Voltage:	AC 500V for 1 minute
RoHS Compliant	

No.	Description	Q'ty	Material	Finish
1	Earth Terminal	1	0.2T Phosphor Copper	Silver Plated
2	Ring Spring	1	0.2 Phosphor Copper	Silver Plated
3	Break Terminal	1	0.3T Brass	Silver Plated
4	Tip Spring	1	0.3T Phosphor Copper	Silver Plated
5	Housing	1	PA9T	Black Color

Date Last Revised: 07/18/12

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301425

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-232VS-E](#)