



Part Number: 1280P

RGB Video, Mini Hi-Res, #25-6 Coax Solid TC, CMP



Product Description

RGB Video Coax, Plenum-CMP, 6-25 AWG tinned copper conductors, FPFA insulation, Duobond® foil + 95% tinned copper interlocked serve shield, inner PVDF jackets, PVC jacket

Technical Specifications

Product Overview

Environmental Space:	Indoor - Plenum
Suitable Applications:	RGB Projectors, LCD Projectors, Video Distribution, Component Video, Graphic Displays, Special Effects Editing, Animation, Video Post Production, Home Theater, Offices, Boardrooms, Auditoriums, Teleconferencing, Theaters

Physical Characteristics (Overall)

Conductor				
AWG	Stranding	Material	Nominal Diameter	No. of Coax
25	Solid	TC - Tinned Copper	0.018 in	6
Conductor Count:			6	
Conductor Size:			25 AWG	

Material	Nominal Diameter
FPFA - Foam Perfluoroalkoxy	0.074 in

Color Chart

Number	Color
1	Red
2	Green
3	Blue
4	Yellow
5	Black
6	White

Inner Shield Material				
Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Aluminum Foil-Poly Tape-AluminumLightly bonded to dielectric	Duobond®	100 %
Interlocked Serve	2	TC - Tinned Copper		95 %

Material	Nominal Diameter
PVDF - Fluorocopolymer	0.111 in

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.369 in

Construction and Dimensions

Filler
Cross Spline Filler

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Inner Shield DCR	Outer Conductor DCR
34 Ohm/1000ft	34 Ohm/1000ft	5.4 Ohm/1000ft	5.4 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
16.8 pF/ft

Shielding:	Other / Specialty
------------	-------------------

Inductance

Nominal Inductance
0.087 µH/ft

Impedance

Nominal Characteristic Impedance
75 Ohm

Return Loss (RL)

Frequency [MHz]	Minimum Return (RL)
5-850 MHz	20 dB

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.5 dB/100ft
5 MHz	1.2 dB/100ft
50 MHz	3.8 dB/100ft
100 MHz	5.2 dB/100ft
200 MHz	7.1 dB/100ft
400 MHz	10 dB/100ft
750 MHz	14.3 dB/100ft
1000 MHz	16.9 dB/100ft
2250 MHz	25.5 dB/100ft
3000 MHz	33.9 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.26 ns/ft	81 %

Voltage

Non-UL Voltage Rating	UL Voltage Rating
300 V RMS	300 V RMS

Temperature Range

Non-UL Temp Rating:	75°C
UL Temp Rating:	60°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	72 lbs/1000ft
Max Recommended Pulling Tension:	100 lbs
Min Bend Radius (Overall):	4 in
Min Bend Radius (Each Coax):	1.1 in

Standards

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
RG Type:	Sub-miniature 59/U Type
RG / Series Type:	Sub-miniature 59/U Type

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LS0H, Toxicity Testing

UL Flammability:	NFPA 262
UL Voltage Rating:	300V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Part Number

Non-Plenum Number:	1280R
Suggested Connectors:	ADC - BNC-16; KINGS - 2065-25-9; TROMPETER - 105-2053-0; BELDEN 1B25A (BNC); BELDEN 1R25A (RCA)
Footnote:	C - CRATE REEL PUT-UP.

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be instock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.