





LOC	DIST	REVISIONS					
AG	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	ECR-11-018212	26MAR2012	DZ	AC
			B		18JUN2013	CW	SH


1. MATERIAL:
HOUSING: BLACK, THERMOPLASTIC, RATED UL 94V-0.
SHIELD: COPPER ALLOY WITH NICKEL PLATING.
CONTACTS: PHOSPHER BRONZE.
CONTACT PLATING: 0.05um MIN GOLD OVER
0.76um MIN PALLADIUM-NICKEL, AT MATING
INTERFACE CONTACT AREA.
2. DATE CODE SHOWN APPROXIMATE AREA.
3. LIGHT PIPE MATERIAL: CLEAR POLYCARBONATE
4. RECOMMENDED MIN PCB THICKNESS 1.5mm (.062").
5. DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER
6. FOR HOLE SIZE AND PLATINGS, SEE SHEET 3.
7. ISOLATION VOLTAGE: 2250VDC(MAX) FOR 60 SECONDS WITH
A RISE TIME OF 500V/SEC.
8. RECOMMENDED SMT LED MANUFACTURERS AND PN:
EVERLIGHT P/N: 18-225/R6G6C-A01/3T OR
PARALIGHT P/N: L-CI85KFKGWT



SCALE 6:1




SCALE 6:1




2170129-1 P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.ZHU 15MAY2011	 TE Connectivity			
		CHK MANOJIAN.W 15MAY2011				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD MANOJIAN.W 15MAY2011	NAME RECEPTACLE ASSEMBLY 1X2 OFFSET, NON MAGNETICS RJ POINT FIVE			
		PRODUCT SPEC				
	0 PLC ± 1 PLC ± 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ±2° FINISH	108-60097	SIZE CAGE CODE DRAWING NO RESTRICTED TO			
		APPLICATION SPEC				
MATERIAL		114-60014	A100779C=2170129			
		WEIGHT				
		Customer Drawing		SCALE 1:1	SHEET 1 OF 3	REV B




LOC		DIST		REVISES			
AG	00	P	LTR	DESCRIPTION	DATE	OWN	APVD
		-		SEE SHEET 1	-	-	-




THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN D. ZHU 15MAY2011	STE TE Connectivity	
DIMENSIONS: mm		CHK MANOJAN.W 15MAY2011		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD MANOJAN.W 15MAY2011	NAME RECEPTACLE ASSEMBLY 1X2 OFFSET, NON MAGNETICS RJ POINT FIVE	
0 PLC ± 1 PLC ± 2 PLC ±0.25 3 PLC ± 4 PLC ±		PRODUCT SPEC 108-60097 APPLICATION SPEC 114-60014	SIZE A100779	
MATERIAL		FINISH	DRAWING NO. C=2170129	
Customer Drawing		WEIGHT	RESTRICTED TO	
SCALE 1:1		SHEET 2 OF 3		REV B

LOC		DIST		REVISIONS					
AG		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
				-	-	SEE SHEET 1	-	-	-



RECOMMENDED HOLE DIMENSIONS
FOR SIGNAL CONTACTS



RECOMMENDED HOLE DIMENSIONS
FOR SHIELD PINS

THICKNESS	PLATING
0.004-0.010	HOT AIR SOLDER LEVELING (HASL) TIN-LEAD (Sn Pb)
0.0005-0.001	IMMERSION TIN (Sn)
0.0002-0.0005	ORGANIC SOLDERABILITY PRESERVATIVE (OSP)
0.0001-0.0005 Au, 0.004-0.0076 Ni	IMMERSION GOLD (Au) OVER NICKEL (Ni) (ENIG)
0.010-0.025	TIN LEAD PLATING (Sn Pb)
0.0001-0.00015	IMMERSION SILVER (Ag)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
D. ZHU
15MAY2011

CHK
MANOJAN.W
15MAY2011

APVD
MANOJAN.W
15MAY2011

DIMENSIONS:
mm

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

±
±
±0.25
±
±
±2°
1

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

PRODUCT SPEC
108-60097
APPLICATION SPEC
114-60014
WEIGHT
-

MATERIAL
1

Customer Drawing

TE Connectivity

NAME
RECEPTACLE ASSEMBLY 1X2 OFFSET,
NON MAGNETICS
RJ POINT FIVE

SIZE
A1

CAGE CODE
00779

DRAWING NO.
2170129

RESTRICTED TO
-

SCALE
4:1

SHEET
3

OF
3

REV
B

4805 (3/11)