


NOTE:

- 1.) ALL DIMENSIONS
APPLY BEFORE PLATING
- 2.) THDS SHALL BE TO GAUGE FIT AFTER
PLATING OR OTHER FINISH
- 3.) SURFACE SHALL BE SMOOTH, AND FREE OF TOOL MARKS
- 4.) BREAK ALL SHARP CORNERS AND REMOVE BURRS

REVISIONS			
SYM	DESCRIPTION	REVISED BY	DATE APPR

FULL SECTION



STANDOFF		
PART NO.	LENGTH	C
8255	1.125	.375
8256	1.250	.375
8257	1.375	.375
8258	1.500	.375
8259	1.625	.375
8260	1.750	.375
8261	2.000	.375
8262	2.500	.375
8263	3.000	.375

MATERIAL: BRASS 360 1/2 HARD			FINISH: NICKEL CODE 10		
DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED			TITLE: 8255-8263 BRASS HEX MALE/FEMALE STANDOFF		
.XX	.XX	.XXX			
---	---	---			
FRACTIONS	ANGLES	SCALE			
---	---	4X	DRAWN: T. LORD DATE: 01/08/03		
HEAT TREAT: ---			CHECKED: T. LORD DATE: 01/08/03		
PLOT SCALE: 1=1			APPROVED: T. LORD DATE: 01/08/03		
			SIZE: B	DRAWING NUMBER: SD: 8255-8263	ISSUE: P

ABBATRON

Electronic Connectors and Hardware
632 Arch Street, Meadville, Pa. 16335