



+ TERMINALS & SPLICES

SPLICES



✓ Active

TE CONNECTIVITY (TE)

D-436-82

Raychem

650126-000  
TE Internal Number: 650126-000  
Mil-Spec: M81824/6-1  
Alias ID: 9-1195132-6

EU RoHS Compliant

EU ELV Compliant

Product Type Splice System Crimp

Terminal & Splice Style Splice

Wire Size (AWG) 26 – 20

Wire Size (mm²) .15 – .75

Barrel Inside Diameter 2.16 mm [ .085 in ]

↓ PRODUCT DRAWING  
English

DOCUMENTATION

Product Drawings

Nickel Plated Crimps In-Line Splice Sealing System, 1 To 1

PDF

English

Catalog Pages/Data Sheets

1654025\_Sec8\_D-436

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

**Product Type** Splice System Crimp  
**Splice Type** Inline Crimp Splice Sealing System

Body Features

**Insulation Material** Modified Polyvinylidene

Contact Features

**Terminal & Splice Style** Splice

Dimensions

**Wire Size (AWG)** 26 – 20  
**Wire Size (mm²)** .15 – .75  
**Barrel Inside Diameter** 2.16 mm [ .085 in ]  
**Wire Size (CMA)** 304 – 1510

Usage Conditions

**Operating Temperature Range (°C)** 150

Industry Standards

**Government Qualified** No

PRODUCT COMPLIANCE



Statement of Compliance

**Statement of Compliance**  
PDF