


HSL-DI16DO16-DB-NN/-NP/-PN/-PP

16-CH Discrete Input 16-CH Discrete Output Daughter Board Modules



Specifications

■ Slave ID Consumption	I
■ Interface	NN: for NPN sinking type sensor input or dry contact and NPN sinking type output NP: for NPN sinking type sensor input or dry contact and PNP sourcing type output PN: for PNP sourcing type sensor input or wet contact and NPN sinking type output PP: for PNP sourcing type sensor input or wet contact and PNP sourcing type output
■ Photo Couple Isolation Voltage	2500 VRMS
■ Input Impedance	4.7 K Ω
■ Input Current	± 10 mA (max.), ± 12.5 mA (peak)
■ Input Voltage	± 40 V (max.)
■ Output Switching Capacity	Single channel 400 mA; Full channels 50 mA at 100% duty cycle
■ LED Indicator	Power, Link and I/O status
■ Power Supply	22 V to 26 Vdc
■ Operating Temperature	0°C to +60°C
■ Storage Temperature	-20°C to +80°C
■ Power Consumption	1.8 W



HSL-DI32-DB-N/-P

32-CH Discrete Input Daughter Board Modules



Specifications

■ Slave ID Consumption	2 consecutive from odd
■ Interface	N: for NPN sinking type sensor input or dry contact P: for PNP sourcing type sensor input or wet contact
■ Photo Couple Isolation Voltage	2500 VRMS
■ LED Indicator	Power, Link and Input status
■ Power Supply	22 V to 26 Vdc
■ Operating Temperature	0°C to +60°C
■ Storage Temperature	-20°C to +80°C
■ Power Consumption	1.8 W
■ CE Certificate	Ready
■ Input Impedance	4.7 K Ω
■ Input Current	± 10 mA (max.), ± 12.5 mA (peak)
■ Input Voltage	± 40 V (max.)



HSL-DO32-DB-N/-P

32-CH Discrete Output Daughter Board Modules



Specifications

■ Slave ID Consumption	2 consecutive from odd
■ Interface	N: for NPN sinking type sensor input or dry contact P: for PNP sourcing type sensor input or wet contact
■ Photo Couple Isolation Voltage	2500 VRMS
■ LED Indicator	Power, Link and Input status
■ Power Supply	22 V to 26 Vdc
■ Operating Temperature	0°C to +60°C
■ Storage Temperature	-20°C to +80°C
■ Power Consumption	1.8 W
■ CE Certificate	Ready
■ Response Time	ON $\rightarrow$ OFF: 180 μ s, OFF $\rightarrow$ ON: 1.2 μ s
■ Switch Capacity	Single channel 500 mA; Full channels 50 mA at 100% duty cycle



1

Software & Utilities

2

DAQ

3

PXI

4

Modular Instruments

5

GPIB & Bus Expansion

6

Motion Control

7

Real-time Distributed I/O

8

PAC

9

Remote I/O

10

Communications

11

Vision

12

Fanless Embedded Computers

13

cPCI & Industrial Computers

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADLINK Technology:](#)

[HSL-DI16DO16-DB-NN](#) [HSL-DI16DO16-DB-NP](#) [HSL-DI16DO16-DB-PN](#) [HSL-DI16DO16-DB-PP](#)