


Fuse holder terminal blocks for 5 x 20 mm and 5 x 25 mm fuses

Compression clamp

  **DIN 1 - DIN 3**

M 4/8.SN

Spacing 8 mm (.315")



M 4/8.SF with disconnect link bar locked on blue grip.



G.L. CE

Color	Type	Part numbers
Grey body/Blue grip	 M 4/8.SN	0115 659.07
Beige body/Blue V0 grip	 M 4/8.SN.V0	0195 659.00

Characteristics

Wire size

		IEC	DIN	UL	CSA
Compression	Solid wire	0,5-4 mm²		22-12 AWG	24-12 AWG
clamp	Stranded wire	0,5-4 mm²		22-12 AWG	24-12 AWG

Voltage

Rated	630 V (1)	600 V (1)	250 V
Pulse	8 kV		
Pollution degree	3		

Current


Rated	6,3 A	10 A	10 A
-------	-------	------	------

Wire size

Rated / Gauge	4 mm² / A4	12 AWG	12 AWG
Wire stripping length	Recomm. screwdriver	Recomm. torque	Protection
9,5 mm .37"	4 mm .157"	0,5-0,8 Nm 4,4-7 lb.in	IP 20 (2) NEMA 1

M 4/8.SNT

Spacing 8 mm (.315")



M 4/8.SF with disconnect link bar locked on blue grip, equipped with 2 test sockets DIA. 2 mm/.079".



G.L. CE

Color	Type	Part numbers
Grey body/Blue grip	 M 4/8.SNT	0115 668.00
Beige body/Blue V0 grip	 M 4/8.SNT.V0	0195 668.01

Characteristics

Wire size

		IEC	DIN	UL	CSA
Compression	Solid wire	0,5-4 mm²		22-12 AWG	24-12 AWG
clamp	Stranded wire	0,5-4 mm²		22-12 AWG	24-12 AWG

Voltage

Rated	400 V (1)	600 V (1)	250 V
Pulse	4 kV		
Pollution degree	3		

Current

Rated	6,3 A	10 A	10 A
-------	-------	------	------

Wire size

Rated / Gauge	4 mm² / A4	12 AWG	12 AWG
Wire stripping length	Recomm. screwdriver	Recomm. torque	Protection
9,5 mm .37"	4 mm .157"	0,5-0,8 Nm 4,4-7 lb.in	IP 20 (2) NEMA 1


End stop		th. 9,1 mm	BADL	V0	0199 408.02
End stop		th. 9,1 mm	BAM		0103 002.26
Other end stops : See Accessories section					
Rail		35 x 7,5 x 1	PR30	prepunched	0173 220.05
Rail		35 x 15 x 2,3	PR4		0168 500.12
Rail		35 x 15 x 1,5	PR5	prepunched	0101 598.26
Rail		32 x 15	PR122		0163 050.04
Other rails : See Accessories section					

Notes


The use of some accessories may decrease the block's voltage rating. For more information, consult us.

Block matching fuse terminal block
M 4/8.SF for line, fuse applications,
see page 137.

Type Part number
M 4/8 **0115 523.07**



Accessories



1	End section	grey orange beige
2	Test plug	
3	Comb-type jumper bar	35 A
4	IDC jumper	
5	Assembly rod	
6	Assembly ring	

Type			Part numbers
FEM8S	V2	th. 1,5 mm	0116 951.15
FEM8S	V2	th. 1,5 mm	0103 923.15
FEM8S	V0	th. 1,5 mm	0196 951.16
PC81	35 A	10 poles	0173 523.11
AD2,5	24 A		0114 205.20
TGA8		2 poles	0168 672.11
		3 poles	0168 773.12
		4 poles	0168 674.13
ANT			0168 675.14

Type			Part numbers
FEM8S	V2	th. 1,5 mm	0116 951.15
FEM8S	V2	th. 1,5 mm	0103 923.15
FEM8S	V0	th. 1,5 mm	0196 951.16
FC2		DIA. 2 mm	0007 865.22
PC81	35 A	10 poles	0173 523.11
AD2,5	24 A		0114 205.20
TGA8		2 poles	0168 672.11
		3 poles	0168 773.12
		4 poles	0168 674.13
ANT			0168 675.14



R See section on markers
marking method

(6) RC610 on lever (17) RC810 on side

(6) RC610 on lever (17) RC810 on side

Note : (1) Insulation voltage of terminal block - operating voltage : in accordance with fuse rating.
(2) Protection index given for closed block.