








THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.

Rating		20A125V AC 1/3HP	Mounting Hole		Circuit Diagram												
Contact Resistance		50m ohm Max.			Switch off, red LED lighten												
Insulation Resistance		DC 500V 100M ohm Min.															
Dielectric Strength		AC 1500V 1 minute															
Operation Temperature		-25°C~85°C.															
Switch Function		4P DPST ON-OFF Lamp Dependent	<table><tr><td>Thickness</td><td>X</td><td>Y</td></tr><tr><td>0.75...1.25</td><td>30.2-0.1</td><td>22.2+0.1</td></tr><tr><td>1.25...2</td><td>30.4-0.1</td><td>22.2+0.1</td></tr><tr><td>2...4</td><td>30.8-0.1</td><td>22.2+0.1</td></tr></table>		Thickness	X	Y	0.75...1.25	30.2-0.1	22.2+0.1	1.25...2	30.4-0.1	22.2+0.1	2...4	30.8-0.1	22.2+0.1	
Thickness	X	Y															
0.75...1.25	30.2-0.1	22.2+0.1															
1.25...2	30.4-0.1	22.2+0.1															
2...4	30.8-0.1	22.2+0.1															
Lamp Type	LED 125VAC 110V w/resistor				Switch on, green LED lighten												



***MATERIAL:**
 Frame: Black, Nylon 66 (94-V2)
 Actuator: Clear, PC (94-V2)
 Terminals: Silver plated, Copper alloy
 Waterproof Rubber: Silicone
 Tolerance: ±0.3mm unless otherwise specified
***Waterproof: IP-65**

RoHS Compliant

2 Added Dependent to function, dated code to drawing and Lamp Type. 12/18/2011.

1 IP-65 WAS IP56. 1/11/11

CW INDUSTRIES
 Southampton, Pa. 18966
 Tel 215.355.7080/www.cwind.com

Date Drawn: 9/19/08

Rev. 2

Unit: mm

Checked By: *G. Gold*

Title: **ROCKER SWITCH**

CW P/N: **GRB285A8L101GR4**