



TIN LEAD PART NUMBER					
SHELL	A±0.38	B±0.12	C±0.10	D±0.25	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96 D09S24A.GX00
15	39.14	33.32	25.18	24.54	19.18 D15S24A.GX00
25	53.03	47.04	39.12	38.25	33.12 D25S24A.GX00
37	69.32	63.50	55.68	54.71	49.68 D37S24A.GX00


Plating: 4 --> flash AU
Plating: 6 --> 0.76µ AU

LEAD FREE PART NUMBER					
SHELL	A±0.38	B±0.12	C±0.10	D±0.25	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96 D09S24A.GX00LF
15	39.14	33.32	25.18	24.54	19.18 D15S24A.GX00LF
25	53.03	47.04	39.12	38.25	33.12 D25S24A.GX00LF
37	69.32	63.50	55.68	54.71	49.68 D37S24A.GX00LF


Plating: 4 --> flash AU
Plating: 6 --> 0.76µ AU

rev	ecn no	dr	date
B	-	JAR	1999/10/18
D	LS05-001	MPE	2005/03/14
E	LS05-0056	MPE	2005/06/28
F	LS06-0019	LGO	2006/02/07
G	LS06-0097	LGO	2006/07/28
H	110-0059	NG	2010-02-23
-	-	-	-

PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0000

www.fciconnect.com			surface		tolerance std		projection		mm			
			ISO 1302		ISO 406 ISO 1101							
			TOLERANCES UNLESS OTHERWISE SPECIFIED									
Dr	JOUBERT	1996/09/10	ANGULAR		0.X		±0.1		size	A3	Scale	2
Eng	PESSON	1996/09/10	LINEAR		0.XX		±0.1					
Chr	NIRMAL GEORGE	2010-02-23	0.XX ± 2°		0.XXX		±0.1		ECN	110-0059		
Appr	SUDHIR VARMA	2010-02-23	Product family				D-SUB		Spec ref -			
			FEMALE CONNECTOR STD EURO				no dwg		C01-8646-0495			Rev.
title			straight solder type for						CUSTOMER			
catalog no							-		sheet 1 of 1			