



Solid State Devices, Inc.

14701 Firestone Blvd * La Mirada, Ca 90638
 Phone: (562) 404-4474 * Fax: (562) 404-1773
 ssdi@ssdi-power.com * www.ssdi-power.com

SUM60UF thru SUM90UF and SUM60UFSMS thru SUM90UFSMS

Designer's Data Sheet

Part Number/Ordering Information ^{1/}

SUM

— — —

Screening ^{2/}

— = Not Screened

TX = TX Level

TXV = TXV

S = S Level

Package Type

— = Axial Leaded

SMS = Surface Mount Square Tab

Voltage/Family

60UF = 6,000V

70UF = 7,000V

80UF = 8,000V

90UF = 9,000V

400 mA

6,000 thru 9,000 VOLTS

60 ns ULTRA FAST RECOVERY
RECTIFIER

FEATURES:

- PIV to 9,000 Volts
- Hermetically Sealed Axial and Square Tab Surface Mount Package
- Ultra Fast Recovery 60 nsec Maximum ^{4/}
- Void Free Construction
- Metallurgically Bonded
- 175°C Maximum Operating Temperature
- TX, TXV, and S-Level Screening Available ^{2/}
- Also Available in Fast Versions, Consult Factory

MAXIMUM RATINGS ^{3/} ^{6/}

RATING		SYMBOL	VALUE	UNIT
Peak Inverse Voltage	SUM60UF and SUM60UFSMS SUM70UF and SUM70UFSMS SUM80UF and SUM80UFSMS SUM90UF and SUM90UFSMS	PIV	6000 7000 8000 9000	Volts
Average Rectified Current	T _A = 25°C T _A = 100°C	I _{O1} I _{O2}	400 250	mA
Surge Current (1 Cycle)		I _{FSM}	25	Amps
Operating & Storage Temperature ^{5/}		T _J and T _{STG}	-65 to +175	°C

NOTES:

^{1/} For Ordering Information, Price, Operating Curves, and Availability- Contact Factory.

^{2/} Screened to MIL-PRF-19500.


^{3/} Unless Otherwise Specified, All Electrical Characteristics @25°C.

^{4/} I_F = 500mA, I_R = 1A, I_{RR} = 250mA, T_A = 25°C


^{5/} Maximum lead/end temperature for soldering is 250°C, 3/8" from case for 5 sec. maximum.

^{6/} Operating and testing over 10,000 V/inch may require encapsulation or immersion in suitable dielectric material.

Axial Leaded



SMS



NOTE: All specifications are subject to change without notification.
 SCD's for these devices should be reviewed by SSDI prior to release.

DATA SHEET #: RC0039C

DOC



Solid State Devices, Inc.

14701 Firestone Blvd * La Mirada, Ca 90638
Phone: (562) 404-4474 * Fax: (562) 404-1773
ssdi@ssdi-power.com * www.ssdi-power.com

**SUM60UF thru SUM90UF
and
SUM60UFSMS thru SUM90UFSMS**



ELECTRICAL CHARACTERISTICS ^{3/ 6/}

CHARACTERISTICS	SYMBOL	VALUE	UNIT
Maximum Forward Voltage (300μs pulse minimum) $I_F = 400 \text{ mA}$	V_F	15	Vdc
Maximum Reverse Leakage Current ($V_R = \text{Rated}$) $(T_A = +25^\circ\text{C})$ $(T_A = +100^\circ\text{C})$	I_{R1} I_{R2}	1.0 15	μA μA
Maximum Junction Capacitance $V_R = 100 \text{ Vdc}$, $f = 1\text{MHz}$, $T_A = 25^\circ\text{C}$	C_J	8	pF
Maximum Reverse Recovery Time $I_F = 500\text{mA}$, $I_R = 1\text{A}$, $I_{RR} = 250\text{mA}$, $T_A = 25^\circ\text{C}$	t_{rr}	60	ns
Typical Thermal Impedance Junction to Lead for Axial, $L = .375"$ Junction to End Tab for Surface Mount	$R_{\theta JL}$ $R_{\theta JE}$	18 18	$^\circ\text{C/W}$

NOTES:

- 1/ For Ordering Information, Price, Operating Curves, and Availability- Contact Factory.
2/ Screened to MIL-PRF-19500.
3/ Unless Otherwise Specified, All Electrical Characteristics @25°C.
4/ $I_F = 500\text{mA}$, $I_R = 1\text{A}$, $I_{RR} = 250\text{mA}$, $T_A = 25^\circ\text{C}$
5/ Maximum lead/end temperature for soldering is 250°C, 3/8" from case for 5 sec. maximum.
6/ Operating and testing over 10,000 V/inch may require encapsulation or immersion in suitable dielectric material.

Package Outlines:

DIMENSIONS (inches)			DIMENSIONS (inches)		
DIM.	Minimum	Maximum	DIM	Minimum	Maximum
A	.065	.165	A	.170	.180
B	---	.350	B	.330	.380
C	.047	.053	C	.020	.030
D	1.00	---	D	.002	---
AXIAL 			SMS 		

NOTE: All specifications are subject to change without notification.
SCD's for these devices should be reviewed by SSDI prior to release.

DATA SHEET #: RC0039C

DOC