

NOTES:

1. MATERIALS AND FINISHES:

BODY - BRASS, NICKEL PLATING

CONTACT - BRASS & PHOSPHOR BRONZE, GOLD PLATING

INSULATOR - PTFE, NATURAL

2. ELECTRICAL:

A. IMPEDANCE: 50 OHM

B. FREQUENCY RANGE: DC-11 GHz

C. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN.

3. MECHANICAL:

A. DURABILITY: 500 CYCLES MIN.


B. TEMPERATURE RANGE: - 65°C to +165°C

THIRD ANGLE PROJ.



REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	12-Feb-03	--	TONY
B	UPDATED FORMAT\RD--DM10090201T1	09-Sep-10	48265	SH

**CUSTOMER OUTLINE DRAWING**

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:
<0.5mm ±0.05mm 0.5 - 6mm ±0.1mm 6 - 30mm ±0.2mm 30 - 120mm ±0.3mm ANGLES ±1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL	DRAWN T.DENG ENGINEER C.WANG APPROVED S.HSIEH CAD FILE F:\DWG\T\5072A1\50\NT3G-BSZ	DATE 09-Sep-10 DATE 09-Sep-10 DATE 09-Sep-10	TITLE TNC MALE TO FEMALE R/A ADAPTOR		Amphenol RF Danbury CT USA, Tainan Taiwan, Shenzhen China www.amphenolrf.com
REFERENCE EAR595 GEN# ASSY1_TNC	FINISH		SCALE: 3/1	SHEET 2 OF 2	DRAWING NO. T5072A1-NT3G-50
			DWG SIZE B	REV B	ITEM NO. 025072AABA1NA5F
					PART NO. 79125-RFX