




- | | |
|---|--|
| ① | CAVITY I.D. AND AMP INFO. MARKED PER MIL-STD-130. |
| ② | TO MATE WITH AMP LGH-1/2 RECEPTACLE WITH .53 [13.5] BARREL DEPTH. |
| ③ | TO MATE WITH AMP LGH-1/2L RECEPTACLE WITH .89 [22.6] BARREL DEPTH. |

868566-1	F	WHITE	— —	14.40±.25 [365.8±6.4]
	E	BLACK	— —	15.50±.25 [393.7±6.4]
	D	BLUE	— —	6.10±.25 [154.9±6.4]
	C	GREEN	13.80±.25 [350.5±6.4]	— —
	B	RED	15.50±.25 [393.7±6.4]	— —
	A	BROWN	5.50±.25 [139.7±6.4]	— —
PART NO.	POSN	WIRE COLOR	A DIM	B DIM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 7-6-93		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .03 [0.8] 3 PLC ± .015 [0.38] 4 PLC ± ± - ANGLES		CHK D.EABY 9-16-93 APVD D.EABY 9-16-93 PRODUCT SPEC — APPLICATION SPEC —	
		NAME PLUG ASSY, 6 POSN WITH FLYING MOLDED END LEADS, LGH —		RESTRICTED TO	
MATERIAL SEE CALLOUTS		FINISH —		SIZE A2 CAGE CODE 00779 DRAWING NO C-868566	
SEE CALLOUTS		WEIGHT —		SCALE 4:1 SHEET 1 OF 1 REV F	
CUSTOMER DRAWING					