





THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

REVISION			
REV.	DESCRIPTION	DATE	APPROVED
B	Added Dimensions	09-09-08	LY



PANEL CUTOUT



NOTES:

RATING: 12A 125-250V AC/32V DC
PANEL THICKNESS: 0.8mm~2.5mm
APPROVALS: UL, cUL, VDE, CCC, CE
RoHS COMPLIANT

CONTROLLED

Dim range (mm)	Tolerance +/- (mm)	Qualtek Electronics Corp. PPC DIVISION			
		Part Number: QMB-122-00ENN-3BA	RoHS Compliant		
0-1	0.15	Description: CIRCUIT BREAKER			
1-6	0.20				
6-18	0.30		UNIT: mm	REV. B	
18-50	0.50				
50-120	0.70		Drawn / Date	Checked / Date	Approved / Date
120-250	0.90		R.Nuti 06-03-08	06-03-08	LY / 06-03-08
250-500	1.20				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Qualtek:](#)

[QMB-122-00ENN-3BA](#)