

Current refinements (click  to remove)

[Search Tips](#) 
 Region  USA  Product Family  Fork Terminal, Vinyl Insulated – Funnel Entry  Text Search: 'PV14-10F-M'

**Your search criteria matched only one product, shown below.**


- Fork design provides for fast and easy installation, without the need to remove fastener
- Insulation support helps to prevent wire damage in bending applications
- Brazed seam protects terminal barrel from splitting during the crimp process
- UL Flammability UL 94V-0, maximum insulation temperature 221°F (105°C)
- Internal barrel serrations assure good wire contact and maximum tensile strength
- UL and CSA rated up 600 V per UL 486

‡UL and CSA approved tooling/product combinations.

Note: Wire sizes #26 – #22 AWG, are not UL Listed or CSA Certified.

|                         |   |
|-------------------------|---|
| Part Number:            | PV14-10F-M  |
| RoHS Compliancy Status: | Compliant   |
| Part Description:       | Fork Terminal, vinyl insulated, funnel entry, 16 – 14 AWG, #10 stud size. |
| Product Type:           | Terminals   |
| Length (In.):           | .92   |
| Width (In.):            | .34   |
| Clearance:              | .24   |
| Max. Ins.:              | .170  |
| Panduit Color Code:     | Blue  |
| Stock:                  | .03   |
| Stud Size:              | #10   |
| Tool:                   | CT-100A‡, CT-600-A‡, CT-1550‡, CT-1551‡, CT-2500‡                         |
| Wire Range:             | 16 – 14 AWG   |
| Min. Order UOM:         | PC  |
| Min. Order Qty.:        | 1000  |
| BOM Qty. (# of Pkgs.)   |   |
| Add to My Catalog       |   |


 Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT PART NUMBER | STUD SIZE | DIMENSIONS in. |               |               |               |               |
|---------------------|-----------|----------------|---------------|---------------|---------------|---------------|
|                     |           | A ±.03         | W ±.01        | C ±.02        | M ±.03        | H ±.01        |
| PV14-6F             | #6        | .84<br>(21,3)  | .28<br>(7,11) | .19<br>(4,83) | .70<br>(17,8) | .15<br>(3,81) |
| PV14-6FN            | #6        | .84<br>(21,3)  | .24<br>(6,10) | .19<br>(4,83) | .70<br>(17,8) | .15<br>(3,81) |
| PV14-8F             | #8        | .90<br>(22,9)  | .31<br>(7,87) | .23<br>(5,84) | .74<br>(18,8) | .17<br>(4,32) |
| PV14-10F            | #10       | .92<br>(23,4)  | .34<br>(8,64) | .24<br>(6,10) | .76<br>(19,3) | .20<br>(5,08) |
| PV14-10FN           | #10       | .92<br>(23,4)  | .31<br>(7,87) | .24<br>(6,10) | .76<br>(19,3) | .20<br>(5,08) |
| PV14-14F            | 1/4"      | 1.09<br>(26,7) | .44<br>(11,2) | .32<br>(8,13) | .84<br>(21,3) | .27<br>(6,86) |

NOTES:

- UL LISTED & CSA CERTIFIED FOR
  - 600 V. MAX. VOLTAGE RATING (1000 V. MAX. IN SIGNS, FIXTURES AND LUMINAIRES.)
  - 16-14 AWG SOLID OR STRANDED COPPER WIRE & 221°F (105°C) MAX. TEMP RATING WITH THE CT-100, CT-1550, CT-1551 INSTALLATION TOOLS.
- MATERIAL:
  - STAMPING - .03 (.08) THK COPPER, TIN PLATED
  - HOUSING - VINYL, BLUE
- STRIP LENGTH 5/16 <sup>+1/32</sup> .0
- PACKAGE QTY:
  - C=100
  - M=1000
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS.



LISTED  
587H  
E52164



CERTIFIED  
LR31212

A41193\_03

|     |       |     |     |  |       |      |      |  |              |               |                       |
|-----|-------|-----|-----|--|-------|------|------|--|--------------|---------------|-----------------------|
| 03  | 10/00 | EJS |     | ADDED PART PV14-14F, REMOVED CT-500, CT-550, ADDED CT-1550, CT-1551 TO NOTE 1-B    |       |      |      | <p>PANDUIT CORP. TINLEY PARK, ILLINOIS</p> <p>2PC, VINYL INSULATED, #16-14 BARREL, FORKS</p> |              |               |                       |
| 02  | 1/97  | TM  | RLS | TEMP RTG. FOR CT-100 WAS 167°F (75°C) REMOVED CT-250, FILESPEC WAS N41193AA_PCD_01 | 05469 | LA   | TJBU |  |              |               |                       |
| 01  | 10/94 | MS  | RLS | UPDATED NOTES AND DIMENSIONS   |       | LA   | TKE  |  |              |               |                       |
| R   | 3/88  | FS  | LM  | RELEASED   |       | LA   | JRB  |  |              |               |                       |
| REV | DATE  | BY  | CHK | DESCRIPTION  | ECN # | CUST | PM   | DRAWN BY<br>FES  | CHK'D<br>FES | SCALE<br>NONE | DRAWING NO.<br>A41193 |