


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS - in.					TOOLS
		A ± .03	W ± .01	C ± .02	M ± .03	H ± .01	
PV14-6LF	#6	.90 (22.86)	.25 (6.35)	.22 (5.59)	.68 (17.27)	.14 (3.56)	*CT-100A **CT-600-A (CT-500CH) **CT-600-A (CT-550CH) **CT-1550 **CT-1551 **CT-2500 (CT-2550CH)
PV14-6LFW	#6	.90 (22.86)	.29 (7.37)	.22 (5.59)	.68 (17.27)	.14 (3.56)	
PV14-8LF	#8	.97 (24.64)	.29 (7.37)	.25 (6.35)	.73 (18.54)	.16 (4.06)	
PV14-10LF	#10	.97 (24.64)	.33 (8.38)	.25 (6.35)	.73 (18.54)	.19 (4.83)	
PV14-10LFN	#10	.97 (24.64)	.29 (7.37)	.25 (6.35)	.73 (18.54)	.19 (4.83)	

NOTES:

*USED FOR #16-14 AWG SOLID OR STRANDED COPPER WIRE
& 167° F (75° C) MAX TEMP. RATING
 **USED FOR #18-14 AWG SOLID OR STRANDED COPPER WIRE
& 221° F (105° C) MAX TEMP. RATING

1. cULus LISTED FOR:
A. 600V MAX. BLDG WIRE
(1000 V MAX. IN SIGNS, FIXTURES & LUMINARIES)
2. SEE WWW.PANDUIT.COM FOR PACKAGE QUANTITIES
3. MATERIAL:
A. STAMPING - .032" THK, COPPER
TIN PLATED
B. HOUSING - VINYL, BLUE
C. SLEEVE - BRASS, TIN PLATED
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
5. WIRE STRIP LENGTH: $5/16 + 1/32$ (7.9 + .8)
- 0 - 0



						TITLE	
						#16-14 BARREL FUNNELED VINYL INSULATED LOCKING FORK, .175 [4.45] MAX. WIRE INSULATION DIAMETER	
						CUSTOMER DRAWING	
						ITEM REVISION NAME	
						N41296BB/10	
						DATASET FILE NAME	
						N41296BB/10	MATERIAL: SEE NOTES DRAWING NUMBER: A41296
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	
						.X ± .XX ± 	
						.XXX ± ANGLES ± THIRD ANGLE PROJECTION	SHT 1 OF 1 A
						DRAWN BY DAW	
						DATE CHK CJH SCALE NONE	
10	07/14	MBY	JHNU	RGB	REVISED NOTES, MOVED TOOLS TO TABLE, REVISED CERTIFICATION, UPDATED BORDER	N41296BB-A41296	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	